


4, 5 and 8-Wire M12 *euromast*® Field Wireable Connectors, Standard and Reverse Key

- Right Angle Male Connectors
- IEC IP 67 Protection



Drawing	Part Number	Housing Specs.	Application	Pinout
	BS 8241-0	PBT, Black PG 7 cable gland accepts 4-6 mm cable diameter Screw terminals accepts up to 18 AWG conductors 85°C 60 V, 4 A	Mates with <i>standard key 4-pin cordsets and receptacles</i>	
	BS 8241-0/PG 9	PBT, Black PG 9 cable gland accepts 6-8 mm cable diameter Screw terminals 85°C 60 V, 4 A	Mates with <i>standard key 4-pin cordsets and receptacles</i>	
	BS 8251-0/PG 9	PBT, Black PG 9 cable gland accepts 6-8 mm cable diameter Screw terminals accepts up to 18 AWG conductors 85°C 125 V, 4 A	Mates with <i>standard key 5-pin cordsets and receptacles</i>	
	BSWS 8241-0	PBT, Black PG 9 cable gland accepts 6-8 mm cable diameter Screw terminals accepts up to 18 AWG conductors 85°C 250 V, 4 A	Mates with <i>reverse key 4-pin cordsets and receptacles</i>	
	BSWS 8251-0	PBT, Black PG 9 cable gland accepts 6-8 mm cable diameter Screw terminals accepts up to 18 AWG conductors 85°C 125 V, 4 A	Mates with <i>reverse key 5-pin cordsets and receptacles</i>	
	BS 8281-0	Nylon, Black PG 9 cable gland accepts 6-8 mm cable diameter Screw terminals accepts up to 18 AWG conductors 85°C 30 VAC/ 75 VDC, 2 A	Mates with <i>standard key 8-pin cordsets and receptacles</i>	

Field Wireables