

Features:

Brand:	AMP
Government/Industry Qualification:	No
Terminal Shape:	Ring Tongue
Receptacle Style:	Straight
Body Style:	PIDG
Barrel Type:	Closed Barrel
Wire/Cable Type:	Regular Wire
Wire Range (mm [AWG]):	2.70-6.60 ² [12-10]
Wire Range (CMA):	5,180 – 13,100
Insulation:	Yes
Insulation Support:	Insulation Support
Insulation Diameter (mm [in]):	6.30 [.248] Max.
Stud Size:	M5
Stud Diameter (mm [in]):	6.70 [0.264]
Shape:	RING-041
Heavy Duty:	Standard
Packaging Method:	Loose Piece
Material:	Copper
Finish:	Tin

Other Properties:

Voltage (VAC):	300
Stock Thickness (mm [in]):	1.02 [0.040]
Color:	Yellow
Insulation Sleeve Material:	Nylon
Temperature Range (°C):	105
CERTI-CRIMP Hand Tool:	59239-4, 525692-0 (Great Britain Tool)
CERTI-LOK Hand Tool Frame Assembly:	169400
CERTI-LOK Die Assembly:	169404
Comment:	Available On-Tape for Automatic Termination.

Terminals and Splices

↳ Ring and Spade Tongue Terminals

AMP 130171

(Tyco Electronics P/N: 130171)