

1 2 3 4 5 6 7 8

A

B

C

D



E

F

SPECIFICATION

Sound

- 1. Resonant Frequency 2.6 ± 0.3 kHz
- 2. Static Capacitance $150000 \pm 30\%$ (pF) at 100 Hz
- 3. Resonant Impedance 150 Max (Ω)
- 4. Input Voltage 30 Vp-p Max
- 5. Operating Temperature -20 ~ $+70$ ($^{\circ}\text{C}$)
- 6. Storage Temperature -20 ~ $+80$ ($^{\circ}\text{C}$)
- 7. Metal Material Brass



技术要求:

- 1, 带标记点一面为正极面, 标记点直径1.0mm
- 2, 银层上焊点直径控制在 2.3 ± 0.5 mm,
- 3, 2-GJ 1x4铜绞线; L=80 \pm 5 mm,

				NINGBO VOISE ELECTRONICS CO.,LTD http://www.nbvoise.com	
No.	DESCRIPTION	APPROVED	DATE	Piezoelectric Element VS27T26ASL80	
TOLERANCES UNLESS NOTED OTHERWISE		APPROVALS	DATE		
.X ±		DRAWN		UNIT	DWG NO.
.XX ±		CHECKED		mm	VS20200709013
.XXX ±		APPROVED	20.07.09	SCALE	SHEET
90° FORMED +2° ANGLES -1°					VER 1.0

1 2 3 4 5 6 7 8