


PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0762910038](#)
Status: **Active**
Overview: [EdgeLine High-Speed Connectors](#)
Description: EdgeLine CoPlanar Connector, 6 Gbps, 0.75mm Pitch, 1.57mm PCB Thickness, 38 Circuits

Documents:

Drawing (PDF)	Application Specification AS-76291-002-001 (PDF)
Product Specification PS-76291-001-001 (PDF)	Packaging Specification PK-76291-001-001 (PDF)
Application Specification AS-76291-0001-001 (PDF)	RoHS Certificate of Compliance (PDF)
Application Specification AS-76291-001-001 (PDF)	



Series image - Reference only

Application tooling part link

Application Tooling Part Link	62100-7100
Application Tooling Part Link	62202-2803

General

Product Family	Edge Card Connectors
Series	76291
Component Type	Edgecard to PCB
Data Rate	5.0-12.0 Gbps
Edge Card Thickness	1.57mm
High Power Bay (30.0A or more)	No
Orientation	Coplanar
Overview	EdgeLine High-Speed Connectors
Product Name	EdgeLine
Standard Based	General
UPC	883906112738

Physical

(p)ower-(s)ignal Configuration	38s - 0p
Circuit Size Range	1-64 Circuits
Circuits (Loaded)	38
Circuits (maximum)	38
Color - Resin	Black
Durability (mating cycles max)	200
Entry Angle	N/A
Keying to Mating Part	N/A
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	5.752/g
PCB Locator	No
PCB Thickness - Recommended	2.79mm
Packaging Type	Tray
Pitch - Mating Interface	0.75mm
Pitch - Termination Interface	0.75mm
Plating min - Mating	0.762µm
Plating min - Termination	0.762µm
Polarized to Mating Part	Yes
Temperature Range - Operating	-40° to +85°C
Termination Interface: Style	Through Hole - Compliant Pin

Electrical

Current - Maximum per Contact	1.5A
Voltage - Maximum	50V AC (RMS)/DC

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[76291 Series](#)

Material Info**Reference - Drawing Numbers**

Application Specification	AS-76291-0001-001, AS-76291-001-001, AS-76291-002-001
Packaging Specification	PK-76291-001-001
Product Specification	PS-76291-001-001
S-Parameter Model	SP-76291-0002-001
Sales Drawing	SD-76291-001-001

This document was generated on 01/11/2022

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[76291-0038](#)