


PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0877159105](#)
Status: **Active**
Overview: [PCIe PCI-X Connectors](#)
Description: 1.00mm Pitch, PCI Express Connector, 64 Circuits, Nylon 4/6 Glass-filled, Black Housing, Phosphor Bronze, 0.38µm Gold Solder-tail, Lead-Free

Documents:

3D Model	Packaging Specification PK-87715-207-001 (PDF)
Drawing (PDF)	Test Summary TS-87715-207-001 (PDF)
3D Model (PDF)	RoHS Certificate of Compliance (PDF)
Product Specification PS-87715-200-001 (PDF)	



Agency Certification

CSA	LR19980
UL	E29179

General

Product Family	Edge Card Connectors
Series	87715
Comments	PCI 4 lanes
Component Type	Edgecard to PCB
Data Rate	8.0 Gbps
Edge Card Thickness	1.57mm
Electrical Model	Yes
High Power Bay (30.0A or more)	No
Orientation	Vertical
Overview	PCIe PCI-X Connectors
Product Name	PCI Express
Standard Based	PCIe
UPC	822348685479

Physical

(p)ower-(s)ignal Configuration	64s - 0p
Circuit Size Range	1-64 Circuits
Circuits (Loaded)	64
Circuits (maximum)	64
Durability (mating cycles max)	50
Entry Angle	Vertical (Top Entry)
Flammability	94V-0
Keying to Mating Part	Yes
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Net Weight	3.866/g
PC Tail Length	3.00mm
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	2.40mm
Packaging Type	Tray
Pitch - Mating Interface	1.00mm
Pitch - Termination Interface	1.00mm
Plating min - Mating	0.381µm
Polarized to Mating Part	Yes
Temperature Range - Operating	-55° to +85°C
Termination Interface: Style	Through Hole

Electrical

Current - Maximum per Contact	1.1A
-------------------------------	------

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[87715 Series](#)

Mates With

PCI Express Card

Voltage - Maximum 50V AC (RMS)/DC

Solder Process Data

Lead-free Process Capability WAVE
Process Temperature max. C 245

Material Info

Reference - Drawing Numbers

Electrical Model Document EE-87715-004-001, EE-87715-011-001,
EE-87715-012-001, EE-87715-013-001,
EE-87715-014-001
Packaging Specification PK-87715-207-001
Product Specification PS-87715-200-001
S-Parameter Model SP-87715-004-001, SP-87715-011-001,
SP-87715-012-001, SP-87715-013-001,
SP-87715-014-001
Sales Drawing SD-87715-207-001
Test Summary TS-87715-207-001

This document was generated on 08/19/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[87715-9105](#)