

UM-PRO 108 COVER-R BK - Lateral element



2200156

<https://www.phoenixcontact.com/us/products/2200156>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Lateral element (right) with mounting foot for DIN rails UM-PRO profiles for PCB width of 108 mm



Your advantages

- Tailor-made housing length, can be cut to length with millimeter precision
- Easy integration of large electronics components, thanks to the open design
- Heat-resistant UM-PRO made from polyamide with UL approval up to 100°C
- Easy device mounting thanks to snap-mount principle (the sides are fixed without the aid of tools)
- High degree of flexibility, thanks to freely positionable covering hoods

Commercial data

Item number	2200156
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	AC13
Product key	ACHDAA
Catalog page	Page 749 (C-1-2013)
GTIN	4046356547383
Weight per piece (including packing)	17.92 g
Weight per piece (excluding packing)	17.57 g
Customs tariff number	39269097
Country of origin	PL

UM-PRO 108 COVER-R BK - Lateral element



2200156

<https://www.phoenixcontact.com/us/products/2200156>

Technical data

Notes

General	Refer to the data sheet for the range in the download area.
---------	---

Product properties

Product type	Panel mounting base side part
Housing series	UM-PRO
Product family	UM-PRO 108
Type	Side element (right) with mounting foot for the DIN rail
Housing type	Press-drawn section housings

Dimensions

Width	19.5 mm
Height	127.8 mm
Depth	39.45 mm
Depth from top edge of DIN rail	32.45 mm

PCB design

PCB thickness	1.4 mm ... 1.8 mm
---------------	-------------------

Material specifications

Color (Housing)	black (RAL 9005)
Flammability rating according to UL 94	V0
Surface characteristics	untreated
Housing material	Polyamide

Environmental and real-life conditions

Glow-wire test

Specification	IEC 60695-2-11:2014-02
Temperature	850 °C
Time of exposure	30 s

Thermal stability / ball thrust test

Specification	IEC 60695-10-2:2014-02
Temperature	125 °C
Test duration	1 h
Force	20 N

Mechanical strength / tumbling barrel

Specification	IEC 60068-2-31:2008-05
Height of fall	50 cm
Frequency	50

Degree of protection (IP code)

UM-PRO 108 COVER-R BK - Lateral element



2200156

<https://www.phoenixcontact.com/us/products/2200156>

Specification	IEC 60529:1989-11 + AMD 1:1999-11 + AMD 2:2013-08
---------------	---

Ambient conditions

Max. IP code to attain	IP20
Ambient temperature (operation)	-40 °C ... 105 °C (depending on power dissipation)
Ambient temperature (storage/transport)	-40 °C ... 55 °C
Ambient temperature (assembly)	-5 °C ... 100 °C
Relative humidity (storage/transport)	80 %

PCB data

Number of PCB holders	3
Type of PCB mount	Insertion/securing with additional elements
PCB surface	700 mm ² ... 1200 mm ² (per basic profile cm)
Thickness of the PCB	1.4 mm ... 1.8 mm

Mounting

Mounting type	DIN rail mounting/wall mounting (with optional mounting flange)
---------------	---

Packaging specifications

Type of packaging	packed in cardboard
Outer packaging type	Carton

UM-PRO 108 COVER-R BK - Lateral element



2200156

<https://www.phoenixcontact.com/us/products/2200156>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2200156>



UL Recognized

Approval ID: FILE E 240868

UM-PRO 108 COVER-R BK - Lateral element



2200156

<https://www.phoenixcontact.com/us/products/2200156>

Classifications

ECLASS

ECLASS-11.0	27182701
ECLASS-13.0	27190602

ETIM

ETIM 9.0	EC002779
----------	----------

UNSPSC

UNSPSC 21.0	31261500
-------------	----------

UM-PRO 108 COVER-R BK - Lateral element



2200156

<https://www.phoenixcontact.com/us/products/2200156>

Environmental product compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

UM-PRO 108 COVER-R BK - Lateral element



2200156

<https://www.phoenixcontact.com/us/products/2200156>

Mandatory accessories

UM-PRO PROFILE - Profile

2200148

<https://www.phoenixcontact.com/us/products/2200148>

Press-drawn section housings, Latching with side elements, latching with foot element, Basic profile, profile length (configurable): 3 cm ... 200 cm, depth: 19.8 mm, Note: required profile length = PCB length - 16.2 mm



UM-PRO 108 COVER-L BK - Lateral element

2200155

<https://www.phoenixcontact.com/us/products/2200155>

Lateral element (left) with mounting foot for DIN rails for UM-PRO profiles with a PCB width of 108 mm



Accessories

UM-PRO 108 COVER-R BK - Lateral element



2200156

<https://www.phoenixcontact.com/us/products/2200156>

SZF 0-0,4X2,5 - Screwdriver

1204504

<https://www.phoenixcontact.com/us/products/1204504>



Actuation tool, for ST terminal blocks, also suitable for use as a bladed screwdriver, size: 0.4 x 2.5 x 75 mm, 2-component grip, with non-slip grip

UM-PRO PE CONTACT L1 - Functional ground contact

2200161

<https://www.phoenixcontact.com/us/products/2200161>



PE contact for UM-PRO panel mounting base for connecting the PCB to the DIN rail at level 1

UM-PRO 108 COVER-R BK - Lateral element



2200156

<https://www.phoenixcontact.com/us/products/2200156>

UM-PRO PE CONTACT L2 - Functional ground contact

2200162

<https://www.phoenixcontact.com/us/products/2200162>



PE contact for UM-PRO panel mounting base for connecting the PCB to the DIN rail at level 2

UM-PRO PE CONTACT L3 - Functional ground contact

2200163

<https://www.phoenixcontact.com/us/products/2200163>



PE contact for UM-PRO panel mounting base for connecting the PCB to the DIN rail at level 3

UM-PRO 108 COVER-R BK - Lateral element



2200156

<https://www.phoenixcontact.com/us/products/2200156>

UM-PRO PCB S-LOCK BK - Locking

2200168

<https://www.phoenixcontact.com/us/products/2200168>



Locking element for locking the top PCB onto UM-PRO housing close to the edge

UM-PRO PCB C-LOCK L1 BK - Locking

2200164

<https://www.phoenixcontact.com/us/products/2200164>



Locking element for locking the PCB onto UM-PRO housing at level 1

UM-PRO 108 COVER-R BK - Lateral element



2200156

<https://www.phoenixcontact.com/us/products/2200156>

UM-PRO PCB C-LOCK L2 BK - Locking

2200165

<https://www.phoenixcontact.com/us/products/2200165>



Locking element for locking the PCB onto UM-PRO housing at level 2

UM-PRO PCB C-LOCK L3 BK - Locking

2200166

<https://www.phoenixcontact.com/us/products/2200166>



Locking element for locking the PCB onto UM-PRO housing at level 3

UM-PRO 108 COVER-R BK - Lateral element



2200156

<https://www.phoenixcontact.com/us/products/2200156>

UM-PRO MOUNT BK - Mounting flange

2200171

<https://www.phoenixcontact.com/us/products/2200171>

Foot element for mounting UM-PRO DIN rail-mount bases directly onto the mounting panel



UM-PRO 108 FOOT BK - Foot element

2200157

<https://www.phoenixcontact.com/us/products/2200157>

Press-drawn section housings, DIN rail mounting, Base element for the DIN rail, for mounting below UM-PRO PROFILE (width: 108 mm), Foot element



UM-PRO 108 COVER-R BK - Lateral element



2200156

<https://www.phoenixcontact.com/us/products/2200156>

UM-PRO A/U N 73 CM - Covering hood

2200310

<https://www.phoenixcontact.com/us/products/2200310>



Press-drawn section housings, Latching, Cover, width: 73 mm, profile length (configurable): 3 cm ... 100 cm, height: 24 mm, Note: max. length of the cover = PCB length - 19 mm

UM-PRO A/U 73 CM - Covering hood

2200311

<https://www.phoenixcontact.com/us/products/2200311>



Press-drawn section housings, Latching, Cover, width: 73 mm, profile length (configurable): 3 cm ... 100 cm, height: 63.2 mm, Note: max. length of the cover = PCB length - 19 mm

UM-PRO 108 COVER-R BK - Lateral element

2200156

<https://www.phoenixcontact.com/us/products/2200156>



UM-PRO A/U 92 CM - Covering hood

2200312

<https://www.phoenixcontact.com/us/products/2200312>



Press-drawn section housings, Latching, Cover, width: 92 mm, profile length (configurable): 3 cm ... 100 cm, height: 34 mm, Note: max. length of the cover = PCB length - 19 mm

UM-PRO LID-73N BK - Lateral element

2200174

<https://www.phoenixcontact.com/us/products/2200174>



Press-drawn section housings, Latching, Side element for low U-shaped profile cover, width: 10.35 mm, height: 78.43 mm, depth: 29.75 mm

UM-PRO 108 COVER-R BK - Lateral element

2200156

<https://www.phoenixcontact.com/us/products/2200156>



UM-PRO LID-73 BK - Lateral element

2200173

<https://www.phoenixcontact.com/us/products/2200173>



Press-drawn section housings, Latching, Side element for U-shaped profile cover, width: 10.35 mm, height: 78.49 mm, depth: 68.95 mm

UM-PRO LID-92 BK - Lateral element

2200172

<https://www.phoenixcontact.com/us/products/2200172>



Press-drawn section housings, Latching, Side element for U-shaped profile cover, width: 10.35 mm, height: 97.51 mm, depth: 39.7 mm

Phoenix Contact 2024 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com