

SGGFT Attack Alarm & Torch

SURE

Overview

SUREGUARD Window Shock Alarm

- Simple installation
- Simple rip cord activation
- Strobe function
- Torch function
- 140+ dB ear piercing siren
- Clip for fastening to belts/pockets
- Mounting bracket for doors, sheds etc.
- Extra heavy duty battery included
- 10 year guarantee
- Customisation available (logo printing)



SGGFT - Attack Alarm & Torch

Key Features and Benefits

The SUREGUARD SGGFT Attack Alarm & Torch incorporates a strobe effect independent torch with a 140+ dB alarm, and is supplied with the battery fitted.

This sturdy, robust alarm includes a key ring attachment to secure unit to handbag/luggage for protection against mugging. A spring-loaded clip ensures that the alarm fits securely to belt or waistband.

This alarm includes mounting bracket which secures alarm to door frame, shed or garage for property security. Therefore this alarm is not just a personal attack alarm, it can be used for many different types of security.

The alarm is operated with a ripcord action and the strobe light flashes to attract attention. Extremely loud siren 140 + dB. The Torch can be used independently to light key holes for quick entry to cars, homes etc. or to light the way.

RoSH Compliant

SURE

SURE24 Limited • 2 Moorbridge Court • Moorbridge Road East • Bingham • Nottinghamshire • NG13 8GG
Tel +44 (0) 1949 836 990 • Fax +44 (0) 1949 836 991 • Web www.sure24.co.uk • Email sales@sure24.net

Copyright 2009 SURE24 Limited • All rights reserved • SURE is a registered trademark.

Product Design



Specification

Feature / Function	Value / Data
Light	High Intensity Strobe Bulb
Operation	Simple Rip Cord Activation / Button For Torch
Test Button	Torch Button Doubles as Battery Test Facility
Settings	Torch / Strobe Light On Alarm
Fixing	Key-Ring attachment / Clip / Mounting Bracket
Battery	9v PP3 Battery (Extra Heavy Duty Battery Included)
Battery Life	Up to 4 Hours Continuous Alarm And Strobe
Alarm	140+ dB Ear Piercing Siren
Case	High Impact ABS Plastic
Guarantee	10 Years
Dimensions	58 mm / 70 mm / 24 mm (W/H/D) w/o Clip/Bracket
Weight	117g
Approvals	CE Certified
Standards	ISO9000