

High Current Toroidal Inductors

Vertical PCB Mounting

Key Features


- Vertical PC Mounting for Board Layout Optimization.
- Wide Range Of Inductance and Current ratings.
- Distributed Air Gap For High Energy Storage.
- High Efficiency Reduced Core Loss.
- Self-Shielding For Low Magnetic Radiation.
- High Current Carrying Capability.

Applications

- SMPS Energy Storage Inductors.
- EMI/RFI Filtering Inductors.
- DC-DC Converter Chokes.

Notes




- (1) Dimensions are in inches.
- (2) Current causing 30°C max temperature rise.
- (3) Operating Temperature Range of -55 to +105°C.
- (4) Leads tinned to within 1/16 of an inch above Mounting Plane.
- (5) Lead Length of 0.50 inches



Electro-Mechanical Characteristics

Part Number	L (u H) ±15% @ 1KHz	L(u H) ±15% @ I-rated	DC Resistance Ω MAX	I-rated DC Current Amps (2)	Dimension A (inches) Nominal	Dimension B (inches) Nominal
HCTI-10-20.0	10	6.7	0.005	20.0	0.56	0.066
HCTI-12-19.1	12	7.8	0.005	19.1	0.56	0.066
HCTI-15-18.0	15	9.5	0.006	18.0	0.56	0.066
HCTI-18-17.2	18	11.1	0.006	17.2	0.56	0.066
HCTI-22-16.4	22	13.2	0.007	16.4	0.56	0.066
HCTI-27-15.6	27	15.7	0.008	15.6	0.56	0.066
HCTI-33-11.7	33	21.3	0.013	11.7	0.53	0.053
HCTI-39-11.2	39	24.7	0.014	11.2	0.53	0.053
HCTI-47-10.7	47	29.0	0.016	10.7	0.53	0.053
HCTI-56-10.2	56	33.7	0.017	10.2	0.53	0.053
HCTI-68-7.7	68	45.2	0.030	7.70	0.52	0.042
HCTI-100-7.0	100	63.1	0.037	7.00	0.52	0.042
HCTI-120-6.7	120	73.9	0.040	6.70	0.52	0.042
HCTI-150-5.0	150	101.4	0.071	5.00	0.51	0.034
HCTI-180-4.8	180	118.9	0.078	4.80	0.51	0.034
HCTI-220-5.8	220	123.8	0.054	5.80	0.56	0.042
HCTI-270-5.5	270	147.2	0.060	5.50	0.56	0.042
HCTI-330-5.2	330	174.1	0.067	5.20	0.56	0.042
HCTI-390-5.0	390	200.2	0.072	5.00	0.56	0.042
HCTI-470-3.8	470	271.4	0.130	3.80	0.54	0.034
HCTI-560-3.6	560	314.8	0.140	3.60	0.54	0.034
HCTI-680-3.4	680	370.7	0.150	3.40	0.54	0.034
HCTI-820-2.6	820	500.9	0.270	2.60	0.53	0.027
HCTI-1000-2.4	1000	593.6	0.300	2.40	0.53	0.027

Custom versions available upon request.



500 Bayview Avenue
Inwood, NY 11096 USA
sales@signaltransformer.com
techhelp@signaltransformer.com

Tel +1 516.239.5777
Fax +1 516.239.7208
Toll Free +1 866.239.5777
signaltransformer.com