

SPECIFICATION


1. SCOPE

This specification is applied to the piezo-element.

2. SPECIFICATION

(at 25°C)

2.1 Resonant Frequency	:	9.0± 1.0KHz
2.2 Resonant Resistace	:	500 Ω max
2.3 Capacitance	:	9000pF± 30% at 100Hz
2.4 Input Voltage	:	30Vp-p max
2.5 Operating Temperature	:	-20~+50°C
2.6 Storage Temperature	:	-20~+60°C
3. DIMENSION	:	as per figure



<p>TOLERANCES UNLESS NOTED OTHERWISE</p> <p>.X ±</p> <p>.XX ±</p> <p>.XXX ±</p> <p>90° FORMED +2°</p> <p>ANGLES -1°</p> <p>FIRST ANGLE PROJECTION</p>	DRAWN		KEPO MODEL NO.	CUSTOMER				
	DESIGN		MFT-10.5T-9.0AL2	QUARTZ-1				
	CHECKED			CUSTOMER NO.				
	APPROVED		DWG NO.		VER	1.0	SCALE	
	DATE	04.10.08	OEM1287					
	CONTRACT NO.		KEPO CO.,LTD.		TEL:(+86)574-88370330			
	AGENCY APPROVAL				FAX:(+86)574-88370329			