

## Within Series Adaptor 53\_SMA-50-0-51/199\_N

### Description

L-adaptor plug/jack  
SMA plug (male) / SMA jack (female)

Interface standard  
Series SMA - IEC 60169-15\_MIL-STD-348A/310\_CECC 22110



### Technical Data

#### Electrical Data

Impedance	50 Ω
Interface frequency max.	18 GHz
VSWR	DC - 14 GHz ≤ 1.02 + 0.03 f (GHz)

#### Mechanical Data

Number of matings	500
Weight	0.0051 kg

#### Environmental Data

Operating temperature	-65 °C to 165 °C
2011/65/EC (RoHS)	not compliant

#### Material Data

Interface - SMA plug (male)

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Stainless Steel	Passivated (Plating)
Body	Stainless Steel	Passivated (Plating)
Insulator	PFA / PTFE	
Coupling nut	Stainless Steel	Passivated (Plating)
Gasket	VMQ (Silicone rubber)	

Interface - SMA jack (female)

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Stainless Steel	Passivated (Plating)
Body	Stainless Steel	Passivated (Plating)
Insulator	PFA / PTFE	

### Related Documents

Catalogue drawing	DCA-00013411
-------------------	--------------

### Ordering Information

Single package	53_SMA-50-0-51/199_NE
----------------	-----------------------