

Tool Header Informations



E238



M Machine Tap Spiral Flute 40°, Back Tapered, Blue Shark

NEW
2013.02



■ 2.1 2.2 2.3
● 1.5 1.6

M	P mm	l ₁ mm	l ₂ mm	d ₂ Ø mm	a mm	l ₃ mm	z		l ₄ mm	e-Code	GBP
3	0.50	56	6	3.5	2.7	6	3	2.5	18	E238M3	28.20
4	0.70	63	7	4.5	3.4	6	3	3.3	21	E238M4	28.60
5	0.80	70	8	6.0	4.9	8	3	4.2	25	E238M5	30.15
6	1.00	80	10	6.0	4.9	8	3	5.0	30	E238M6	30.35
8	1.25	90	13	8.0	6.2	9	3	6.8	33	E238M8	34.70
10	1.50	100	15	10.0	8.0	11	3	8.5	39	E238M10	42.15
12	1.75	110	18	9.0	7.0	10	4	10.3	-	E238M12	53.90
14	2.00	110	20	11.0	9.0	12	4	12.0	-	E238M14	75.40
16	2.00	110	20	12.0	9.0	12	4	14.0	-	E238M16	77.30
18	2.50	125	25	14.0	11.0	14	4	15.5	-	E238M18	112.00
20	2.50	140	25	16.0	12.0	15	4	17.5	-	E238M20	118.00
22	2.50	140	25	18.0	14.5	17	4	19.8	-	E238M22	166.00
24	3.00	160	30	18.0	14.5	17	4	21.0	-	E238M24	156.00
27	3.00	160	30	20.0	16.0	19	4	24.0	-	E238M27	224.00
30	3.50	180	36	22.0	18.0	21	4	26.5	-	E238M30	264.00