


GL-2030E

Aliases (UNFGL2030EXXXX)

KEMET, GL, EMI/RFI Filters, Noise Suppression, 250 VAC



Click here for the 3D model.

Dimensions		
L	41.7mm NOM	
W	52mm NOM	
Н	26mm NOM	

Packaging Specifications		
Packaging	Tray, Box	
Packaging Quantity	40	
Component Weight	40 g	

General Information		
Series	GL	
Style	Metal Box	
Description	Noise Filters	
RoHS	Yes	
Qualifications	UL, CSA, TUV	
Miscellaneous	30 K Self-Temperature Rise Max.	

Specifications	
Voltage AC	250 VAC
Voltage	1500 VAC Withstanding Voltage 1 Min. Line to Ground
Rated Current	3 A (AC/DC)
Rated Temperature	55°C
Temperature Range	-25/+55°C
Leakage Current	0.5 mA MAX (250 V 60 Hz)
Resistance	300 MOhms MIN Insulation 500 VDC 1 Min. Line To Ground

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.