


A-3A-F 系列

型號 Model No.	額定動作溫度 Rated functioning temp. (Tf)	實測動作溫度 Fusing-off temperature (°C)	保持溫度 Holding temperature (Th)	極限溫度 Maximum temp. limit (Tm)	額定電流 Rated current (Ir)	額定電壓 Rated voltage (Ur)	安規認證 Safety approval						
							UL	CSA	CUL	TUV	VDE	PSE	CCC
A0-3A-F	84°C	82+/-2°C	40°C	180°C	3A	250Vac	●		●		●	●	●
A1-3A-F	102°C	98+/-2°C	63°C	180°C	3A	250Vac	●		●		●	●	●
A2-3A-F	115°C	112+/-3°C	75°C	180°C	3A	250Vac	●		●		●	●	●
A3-3A-F	125°C	120+/-3°C	85°C	180°C	3A	250Vac	●		●		●	●	●
A4-3A-F	130°C	126+/-2°C	90°C	180°C	3A	250Vac	●		●		●	●	●
A5-3A-F	135°C	131+/-3°C	90°C	180°C	3A	250Vac	●		●		●	●	●
A7-3A-F	138°C	135+/-2°C	93°C	180°C	3A	250Vac	●		●		●	●	●
A8-3A-F	150°C	145+/-3°C	105°C	180°C	3A	250Vac	●		●		●	●	●
A12-3A-F	145°C	140+/-2°C	102°C	180°C	3A	250Vac					●	●	

Dimension (A-3A-F series)

a	b	c	d	e
6.2±0.5	6.3±0.5	2.5±0.3	∅0.6±0.02	70±3



A-5A-F 系列

型號 Model No.	額定動作溫度 Rated functioning temp. (Tf)	實測動作溫度 Fusing-off temperature (°C)	保持溫度 Holding temperature (Th)	極限溫度 Maximum temp. limit (Tm)	額定電流 Rated current (Ir)	額定電壓 Rated voltage (Ur)	安規認證 Safety approval						
							UL	CSA	CUL	TUV	VDE	PSE	CCC
A0-5A-F	84°C	82+/-2°C	40°C	180°C	5A	250Vac	●		●		●	●	●
A1-5A-F	102°C	98+/-2°C	63°C	180°C	5A	250Vac	●		●		●	●	●
A2-5A-F	115°C	112+/-3°C	75°C	180°C	5A	250Vac	●		●		●	●	●
A3-5A-F	125°C	120+/-3°C	85°C	180°C	5A	250Vac	●		●		●	●	●
A4-5A-F	130°C	126+/-2°C	90°C	180°C	5A	250Vac	●		●		●	●	●
A5-5A-F	135°C	131+/-3°C	90°C	180°C	5A	250Vac	●		●		●	●	●
A7-5A-F	138°C	135+/-2°C	93°C	180°C	5A	250Vac	●		●		●	●	●
A8-5A-F	150°C	145+/-3°C	105°C	180°C	5A	250Vac	●		●		●	●	●
A12-5A-F	145°C	140+/-2°C	102°C	180°C	5A	250Vac					●	●	●

Dimension (A-5A-F series)

a	b	c	d	e
6.6±0.5	8.0±0.5	2.6±0.3	∅0.6±0.02	70±3

