




Tank adaptor type 050 PVC-U
Union with solvent cement socket metric

Model:

- Gaskets: flat gaskets EPDM
- Washer: PP
- Run-out holes: two holes in octagonal head
- FKM flat gaskets available for tank adaptor type 050



d (mm)	PN (bar)	Code	SP	Weight (kg)
16	16	161 050 245	1	0.064
20	16	161 050 246	1	0.070
25	16	161 050 247	1	0.100
32	16	161 050 248	1	0.196
40	16	161 050 249	1	0.328
50	16	161 050 250	1	0.395
63	16	161 050 251	1	0.530

d (mm)	L (mm)	L2 (mm)	L1 (mm)	D (mm)	L3 max (mm)	Diameter of bore in tank side (mm)	S1 (mm)	L4 (mm)	d2 (mm)	D1 (mm)	S (mm)	G (inch)
16	77	11	58	44	19	28	40	14	5	29	32	3/4
20	83	12	61	54	17	35	50	16	5	35	40	1
25	90	13	65	60	18	43	55	19	5	42	50	1 1/4
32	95	13	67	69	19	49	65	22	5	49	56	1 1/2
40	104	13	72	84	16	61	80	26	5	59	69	2
50	113	15	76	92	16	67	85	31	5	70	76	2 1/4
63	128	15	84	108	19	83	100	38	5	82	95	2 3/4

The technical data are not binding. They neither constitute expressly warranted characteristics nor guaranteed properties nor a guaranteed durability. They are subject to modification. Our General Terms of Sale apply.

Georg Fischer Piping Systems Ltd, Postfach, CH-8201 Schaffhausen/Switzerland

Phone +41 -(0)52-631 1111

e-mail: info.ps@georgfischer.com

Internet: <http://www.gfps.com>