



WINSTA® MIDI

Intermediate Couplers and h-Distribution Connectors, 3-Pole

250 V/4 kV/3 I _N 25 A ② Approvals	250 V/4 kV/3 I _N 25 A ② Approvals	250 V/4 kV/3 I _N 25 A ② Approvals
--	--	--



Color	Item No.	Pack. Unit	Color	Item No.	Pack. Unit	Color	Item No.	Pack. Unit
Intermediate coupler, 1 x plug/1 x socket			h-distribution connector, bi-directional, plug - socket/socket			h-distribution connector, unidirectional, plug/socket - socket		
● black	770-603	100	● black	770-633	50	● black	770-634	50
○ white	770-653	100	○ white	770-683	50	○ white	770-684	50
						● red	770-934	50
			for "flying leads", with 3rd locking lever			for "flying leads", with 3rd locking lever		
			● black	770-635	50	● black	770-636	50
			○ white	770-685	50	○ white	770-686	50
						● red	770-936	50

Item-Specific Accessories

Lockout cap, for socket, separable, 12-pole  black 770-201 100 white 770-221 100	Mounting plate, for distribution connectors  black 770-623 25 white 770-673 25	Mounting plate, for distribution connectors  black 770-623 25 white 770-673 25
Lockout cap, for plug, separable, 5-pole  yellow 770-360 100	Fixing pin, for mounting plates  ③ black 890-601 250 ④ black 770-601 250	Fixing pin, for mounting plates  ③ black 890-601 250 ④ black 770-601 250
Lockout cap, for socket, separable, 12-pole  black 770-201 100 white 770-221 100	Lockout cap, for socket, separable, 12-pole  black 770-201 100 white 770-221 100	

Dimensions

