



Product Specification

Part Number		FT-27T-4.6B1L120
Resonance Frequency	kHz	4.6±0.5
Resonance Impedance	Ω	≤300
Free Capacitance	pF	20000 ±30% (at 100Hz)
Coaxial degree	mm	0.6
Insulation Resistance	MΩ	≥100 (at50V DC)
Input Voltage	Vp-p	<30
Operating Temperature	℃	-20 ~ +70
Storage Temperature	℃	-30 ~ +80
Metal Plate Diameter	D--mm	27±0.2
Ceramic Disc Diameter	d--mm	20±0.5
Metal Plate Thickness	t--mm	0.25±0.02
Total Thickness	T--mm	0.50±0.03
Metal Material		Brass

SHAPE:

