



1 2 3 4 5 6 7 8

REV	DESCRIPTION	BY	DATE
C	REDRAWN-REV. NOTES	EJH	8/28/85
D	ADD STAND-OFFS. & REDRAW FROM IGES FILES	JGS	11/10/89

REV	DESCRIPTION	BY	DATE
C	REDRAWN-REV. NOTES	EJH	8/28/85
D	ADD STAND-OFFS. & REDRAW FROM IGES FILES	JGS	11/10/89

PRODUCT NO  
SEE TABLE




**CONTROLLED DOCUMENT**

CUSTOMER COPY	CODE IDENT	DATE	TITLE
	22326	11/29/89	IX 100 CARD CONNECTOR
DR	J. SHREINER	ENGR	M. HANEN
CHK	SEE NOTES	APPR	M. HANEN
DATE	11/29/89	SCALE	10/1 D 6/730
SCALE	10/1 D 6/730	SHEET	1 OF 3

ISSUE	SH NO	DATE	DESCRIPTION
1	1	11/29/89	INITIALS
2	2		
3	3		

DO NOT SCALE DRAWING	TOLERANCE UNLESS OTHERWISE NOTED	FINISH
0.010, .25/.001, .01	0.010, .13/.000, .005	XXX
LINEAR	0.000, 0.001, .0000, .0020	XXX
ANGLES ±2°		

NOTE: This part is the property of and subject to the proprietary rights of the DuPont Company. No part of this drawing shall be used in any way without the written consent of DuPont Electronics, Inc.





**CONTROLLED DOCUMENT**

CUSTOMER COPY	CODE IDENT	DATE	TITLE
	22926	11/13/89	1X.100 CARD CONNECTOR
DR	J. SHREINER	CHK	XXXX
ENGR	M. HAHN	APPR	M. HAHN
SCALE	SIZE	TUNG	ING
XXX	D	67230	SHEET 3

ISSUE SHEET INDEX	SH NO	1	DO NOT SCALE DRAWING	MM	INCH
MODEL	XXXX		DO NOT SCALE UNLESS OTHERWISE NOTED	MM/INCH	
TOLERANCE	UNLESS OTHERWISE NOTED		LINEAR	0.0010, 0.13/0.0001, 0.05	
FINISH			THIRD ANGLE PROJECTION	MM	INCH
ANGLES	12° 0'				
TABULATION SHEETS REQUIRED	YES	NO			

NOTE: This part is the property of and subject to the proprietary rights of the DuPont Company. No part of this design shall be used in any way without the written consent of DuPont Electronics, Inc., Columbia, PA.

8	7	6	5	4	3	2	1
PRODUCT NO	NO. OF POS.	DIM. A ± .51/.020	DIM. B MAX.	NO. OF POS.	DIM. A ± .51/.020	DIM. B MAX.	REVISIONS
REV	DESCRIPTION	BY	DATE				
67230-001	1X1	.007/0.00	2.54/1.00	1X51	127.00/5.000	129.54/5.100	D
-002	1X2	2.54/1.00	5.08/2.00	1X52	129.54/5.100	132.08/5.200	
-003	1X3	5.08/2.00	7.62/3.00	1X53	132.08/5.200	134.62/5.300	
-004	1X4	7.62/3.00	10.16/4.00	1X54	134.62/5.300	137.16/5.400	
-005	1X5	10.16/4.00	12.70/5.00	1X55	137.16/5.400	139.70/5.500	
-006	1X6	12.70/5.00	15.24/6.00	1X56	139.70/5.500	142.24/6.100	
-007	1X7	15.24/6.00	17.78/7.00	1X57	142.24/6.100	144.78/7.100	
-008	1X8	17.78/7.00	20.32/8.00	1X58	144.78/7.100	147.32/8.100	
-009	1X9	20.32/8.00	22.86/9.00	1X59	147.32/8.100	149.86/9.100	
-010	1X10	22.86/9.00	25.40/10.00	1X60	149.86/9.100	152.40/10.100	
-011	1X11	25.40/10.00	27.94/11.00	1X61	152.40/10.100	154.94/11.100	
-012	1X12	27.94/11.00	30.48/12.00	1X62	154.94/11.100	157.48/12.100	
-013	1X13	30.48/12.00	33.02/13.00	1X63	157.48/12.100	160.02/13.100	
-014	1X14	33.02/13.00	35.56/14.00	1X64	160.02/13.100	162.56/14.100	
-015	1X15	35.56/14.00	38.10/15.00	1X65	162.56/14.100	165.10/15.100	
-016	1X16	38.10/15.00	40.64/16.00				
-017	1X17	40.64/16.00	43.18/17.00				
-018	1X18	43.18/17.00	45.72/18.00				
-019	1X19	45.72/18.00	48.26/19.00				
-020	1X20	48.26/19.00	50.80/20.00				
-021	1X21	50.80/20.00	53.34/21.00				
-022	1X22	53.34/21.00	55.88/22.00				
-023	1X23	55.88/22.00	58.42/23.00				
-024	1X24	58.42/23.00	60.96/24.00				
-025	1X25	60.96/24.00	63.50/25.00				
-026	1X26	63.50/25.00	66.04/26.00				
-027	1X27	66.04/26.00	68.58/27.00				
-028	1X28	68.58/27.00	71.12/28.00				
-029	1X29	71.12/28.00	73.66/29.00				
-030	1X30	73.66/29.00	76.20/30.00				
-031	1X31	76.20/30.00	78.74/31.00				
-032	1X32	78.74/31.00	81.28/32.00				
-033	1X33	81.28/32.00	83.82/33.00				
-034	1X34	83.82/33.00	86.36/34.00				
-035	1X35	86.36/34.00	88.90/35.00				
-036	1X36	88.90/35.00	91.44/36.00				
-037	1X37	91.44/36.00	93.98/37.00				
-038	1X38	93.98/37.00	96.52/38.00				
-039	1X39	96.52/38.00	99.06/39.00				
-040	1X40	99.06/39.00	101.60/40.00				
67230-041	1X41	101.60/40.00	104.14/41.00				