

# B 221306 PC-V0 7024




Bocube  
 Enclosures, polycarbonate UL 94 V0, single-coloured

Order no.: 96015224

<b>Colour</b>	Graphite grey
<b>Colour of enclosure group</b>	Graphite grey, similar to RAL 7024; light grey, similar to RAL 7035; special colours on request
<b>Protection class</b>	IP 66/IP 67 DIN EN 60529
<b>Enclosure material</b>	ABS or PC UL 94 V0 (material is suitable for outdoor use; f1-listing according to UL 746C), foamed seal; for details please see Technical Information

Scope of delivery: Lid and base, hinged quick-release catches



<b>A</b>	231 mm
<b>B</b>	125 mm
<b>C</b>	60 mm
<b>a1</b>	192 mm
<b>a2</b>	194,4 mm
<b>b1</b>	113 mm
<b>b2</b>	118,4 mm
<b>c1</b>	52 mm

<b>Technical drawings</b>	Basic drawing for processing work: <a href="#">96015224_B-221306-PC-V0-7024-G.dxf</a> (3.1 MB) 3D product data in STEP format: <a href="#">Registration necessary</a> Catalogue drawing in DXF format: <a href="#">96015224_B-221306-PC-V0-7024.dxf</a> (3.8 MB) Catalogue drawing in PDF format: <a href="#">96015224_B-221306-PC-V0-7024.pdf</a> (257 KB)
---------------------------	--

<b>Chapter download</b>	<a href="#">Bocube_GB.pdf</a> (459 KB) <a href="#">Highlights_Bocube.pdf</a> (3.8 MB)
-------------------------	--

# Accessories



## Hinged quick-release catches (Set), polycarbonate UL 94 V0 or ABS

96310203	<a href="#">B SC 13 PC-V0 1023</a>	For B 1413.., B 2213.. Traffic yellow
96310205	<a href="#">B SC 13 PC-V0 7035</a>	For B 1413.., B 2213.. Light grey
96310204	<a href="#">B SC 13 PC-V0 7024</a>	For B 1413.., B 2213.. Graphite grey
96310209	<a href="#">B SC 13 PC-V0 6029</a>	For B 1413.., B 2213.. Mint green
96310202	<a href="#">B SC 13 PC-V0 5002</a>	For B 1413.., B 2213.. Ultramarine blue
96310200	<a href="#">B SC 13 PC-V0 3000</a>	For B 1413.., B 2213.. Flame red



## Hand-operated hinged catch (set), polycarbonate UL 94 V0 or ABS

96910203	<a href="#">B SC HB 13 PC-V0</a>	For B 1413.., B 2213.. Traffic yellow
96910205**	<a href="#">B SC HB 13 PC-V0</a>	For B 1413.., B 2213.. Light grey
96930205**	<a href="#">B SC HB 13 ABS 7035</a>	For B 1413.., B 2213.. Light grey
96910204**	<a href="#">B SC HB 13 PC-V0</a>	For B 1413.., B 2213.. Graphite grey
96910209	<a href="#">B SC HB 13 PC-V0</a>	For B 1413.., B 2213.. Mint green
96910202	<a href="#">B SC HB 13 PC-V0</a>	For B 1413.., B 2213.. Ultramarine blue
96910200	<a href="#">B SC HB 13 PC-V0</a>	For B 1413.., B 2213.. Flame red



## Wall brackets

96510004	<a href="#">B WL 7024</a>	For B 08... - B 26... Graphite grey
96510005	<a href="#">B WL 7035</a>	For B 08... - B 26... Light grey




## Mounting panels, laminated paper, 2 mm

96605200	<a href="#">B M 2213</a>	For B 2213..
----------	--------------------------	--------------



## Front panels, 2 mm, natural-coloured anodised aluminium

96705200	<a href="#">B FP 2213</a>	For B 2213.., front panel thickness 2.0 mm
----------	---------------------------	--



## Sets of screws

96700000	<a href="#">B FP-SHR</a>	A (for fixing front panels)
96600010	<a href="#">B M-SHR</a>	C (for fixing mounting panels B M 1008-2617)
96300000	<a href="#">B SHR</a>	D (for optional screwing of enclosures B 0808 - 2617)




## Distance bolts



96728000 [DIBLZ AK](#)  
96726000 [DIBLZ AK](#)


ND = 2.4 - 2.6, for B...06  
ND = 2.4 - 2.6, for B...06 if a mounting plate is used



**Blanking plugs to determine the hinge side**

96410004 [B VS 7024](#)  
96410005 [B VS 7035](#)  
96410000 [B VS 3000](#)

Graphite grey  
Light grey  
Flame red



**DIN rails DIN EN 60715 TH 15**

22151901 [TS 15](#)

For EM/ET 214, EM/ET 221-223, EM/ET 232,  
EM/ET 237, BCD 200, B 2213..



**DIN rails DIN EN 60715 G 32**

22321901 [TS 32](#)

For EM/ET 214, EM/ET 221-223, EM/ET 232,  
EM/ET 237, B 22130.



**DIN rails DIN EN 60715 TH 35**

22351901 [TS 35](#)

For EM/ET 214, EM/ET 221-223, EM/ET 232,  
EM/ET 237, BCD 200, B 2213..

\* = Available on request