

DEWALT®

**POWER TOOLS
ACCESSORIES**



www.DEWALT.com

GUARANTEED TOUGH.®

CONTENTS

DRILL BITS, POINTS AND CHISELS Page 6

Concrete, Masonry, Metal and Wood

HOLE SAWS Page 46

Metal, Wood and Masonry

SCREWDRIVING Page 54

Screwdriving

CIRCULAR SAW BLADES Page 70

Wood, Metal, Plastic and Composite Materials

JIGSAW BLADES Page 82

Wood, Metal, Plastic

RECIPROCATING AND ALLIGATOR SAW BLADES Page 90

Wood, Metal and Insulation

WOOD SHAPING Page 102

Router Bits and Planer Blades

COATED ABRASIVES Page 106

Abrasive Mesh, Sanding Sheets, Sanding Belts and Flap Discs

BONDED ABRASIVES Page 122

Discs, Wire Brushes and Wheels

DIAMOND CUTTING, GRINDING AND DRILLING ACCESSORIES Page 130


Diamond Discs, Grinding Cups, Core Drills and Bits

MULTI-TOOL ACCESSORIES Page 144

Multi-Tool Accessories

SETS Page 150

Sets and Mixed Sets

**Complete Solutions**

DeWALT® is a market-leading manufacturer of premium power tools, accessories and anchors and fixings that provide a fully integrated system solution for applications in concrete, masonry, metal and wood.

Manufacturing

To ensure maximum performance and customer satisfaction, DeWALT® drill bits undergo the most rigorous manufacturing and testing procedures, and the most advanced production and quality management process.

Product Development

Through extensive and continuous field research, DeWALT® has gained a comprehensive knowledge of user needs and applications. Its world class development facility utilises the latest Catia CAD system and automated test equipment to develop and test all drill bits prior to and during manufacture.

Quality Control

DeWALT® is a long standing member of PRUF GEMEINSCHAFT MAUERBOHRER (PGM), an internationally recognised organisation that verifies the suitability of drill bits for use in anchor fixing. To test drill bit life and durability, 1 million holes are drilled into 350 tonnes of concrete each year. If there is any variability in quality, it is detected before the products are delivered to the end user. All drill bits are certified to the latest ISO 9001:2000 quality standards.



Drill Bits, Points and Chisels

INTRODUCTION

DeWALT® professional accessories offer concrete and masonry drill bits for any task level. Whether it's light duty, occasional use, heavy duty, or continuous use in the toughest concrete, DeWALT® offers the right accessory for the job. You've bought the best masonry drill, now buy the best masonry or concrete drill bit.

RECOMMENDED MATERIALS



Carbide Tip

Solid piece carbide with four cutting faces to prevent jamming in rebar. Provides cleaner, more concentric holes and constant high drilling speed.

The carbide tip and body are brazed together via an innovative welding technique creating a strong durable bond.

Reduced Vibration

Impact force spread over four cutting faces.

Durability

Optimised heat treatment for maximum strength.

Speed

4 flute helix maximises debris removal for fast drilling and clear holes. Long helix length with optimised free space for faster debris removal.



Optimum Impact Transmission

Maximised central core enables more efficient energy transmission to the drill bit head.

Core Reinforcement

For optimum impact and breakage stability. Enables more efficient energy transmission to the drill bit head.

Carbide Tip

The solid two cutter head is flanked by two individual cutting tips delivering a fast and efficient drilling speed. These carbide tips and body are brazed together to create a strong and durable bond.

Speed

4 flute helix with maximum flute entry enables faster debris removal.



Carbide Drill Head

Optimised drill head design with 2 cutting edges

Core Reinforcement

For optimum impact energy transmission and breakage resistance.

2 Flute Helix

For efficient debris removal.

XLR SDS-max® CARBIDE DRILL BITS

SPEED

4 flute helix maximises debris removal for fast drilling and clear holes. Long helix length with optimised free space for faster debris removal.

REDUCED VIBRATION

Impact force spread over four cutting faces.

DURABILITY

Optimised heat treatment for maximum strength.

CARBIDE TIP

Solid piece carbide with four cutting faces to prevent jamming in rebar. Provides cleaner, more concentric holes and constant high drilling speed. The carbide tip and body are brazed together via an innovative welding technique creating a strong durable bond.



EXTREME® SDS-max® CARBIDE DRILL BITS

SPEED

4 flute helix with maximum flute entry enables faster debris removal.

CORE REINFORCEMENT

For optimum impact and breakage stability. Enables more efficient energy transmission to the drill bit head.

OPTIMUM IMPACT TRANSMISSION

Maximised central core enables more efficient energy transmission to the drill bit head.

CARBIDE TIP

The solid two cutter head is flanked by two individual cutting tips delivering a fast and efficient drilling speed. These carbide tips and body are brazed together to create a strong and durable bond.



APPLICATIONS

For drilling (reinforced) concrete, masonry, natural and artificial stone.



FOR USE WITH

SDS-max® concrete drill bits, (Hilti type F, G, or Y) for anchor, fixing or clearance holes in masonry, concrete, brick or block work.



Made in Germany.



SINGLE PACKS

Cat. No.	Ø mm	Total length mm	Working length mm	Cutters	Pack Qty.
DT60809-QZ	16	340	190	4	1
DT60810-QZ	16	540	390	4	1
DT60811-QZ	18	340	190	4	1
DT60812-QZ	18	540	390	4	1
DT60813-QZ	19	340	190	4	1
DT60814-QZ	19	540	390	4	1
DT60815-QZ	19	670	520	4	1
DT60816-QZ	20	340	210	4	1
DT60817-QZ	20	540	410	4	1
DT60818-QZ	20	920	790	4	1
DT60819-QZ	22	340	210	4	1
DT60820-QZ	22	540	410	4	1
DT60821-QZ	22	920	790	4	1
DT60822-QZ	24	340	210	4	1
DT60823-QZ	24	540	410	4	1
DT60824-QZ	25	340	210	4	1
DT60825-QZ	25	540	410	4	1
DT60826-QZ	25	920	790	4	1
DT60827-QZ	26	340	210	4	1
DT60828-QZ	26	540	410	4	1
DT60829-QZ	28	380	250	4	1
DT60830-QZ	28	570	440	4	1
DT60831-QZ	28	670	540	4	1
DT60832-QZ	30	380	250	4	1
DT60833-QZ	30	570	440	4	1
DT60834-QZ	32	380	250	4	1
DT60835-QZ	32	570	440	4	1
DT60836-QZ	32	920	790	4	1
DT60837-QZ	35	380	250	4	1
DT60838-QZ	35	570	440	4	1
DT60839-QZ	35	670	540	4	1
DT60840-QZ	36	570	430	4	1
DT60842-QZ	38	570	440	4	1
DT60844-QZ	40	380	250	4	1
DT60845-QZ	40	570	440	4	1
DT60846-QZ	40	920	790	4	1
DT60847-QZ	42	570	440	4	1



APPLICATIONS

For drilling (reinforced) concrete, masonry, natural and artificial stone.



FOR USE WITH

SDS-max® concrete drill bits, (Hilti type F, G, or Y) for anchor, fixing or clearance holes in masonry, concrete, brick or block work.



Made in Germany.



SINGLE PACKS

Cat. No.	Ø mm	Total length mm	Working length mm	Cutters	Pack Qty.
DT9400-QZ	12	340	200	2	1
DT9401-QZ	12	540	400	2	1
DT9405-QZ	14	340	200	2	1
DT9406-QZ	14	540	400	2	1
DT9409-QZ	16	340	200	4	1
DT9410-QZ	16	540	400	4	1
DT9411-QZ	18	340	200	4	1
DT9412-QZ	18	540	400	4	1
DT9416-QZ	20	340	200	4	1
DT9417-QZ	20	540	400	4	1
DT9418-QZ	20	920	800	4	1
DT9419-QZ	22	340	200	4	1
DT9420-QZ	22	540	400	4	1
DT9421-QZ	22	920	800	4	1
DT9422-QZ	24	340	200	4	1
DT9423-QZ	24	540	400	4	1
DT9424-QZ	25	340	200	4	1
DT9425-QZ	25	540	400	4	1
DT9426-QZ	25	920	800	4	1
DT9428-QZ	26	540	400	4	1
DT9429-QZ	28	380	250	4	1
DT9430-QZ	28	570	450	4	1
DT9431-QZ	28	670	550	4	1
DT9433-QZ	30	570	450	4	1
DT9434-QZ	32	380	250	4	1
DT9435-QZ	32	570	450	4	1
DT9436-QZ	32	920	800	4	1
DT9438-QZ	35	570	450	4	1
DT9439-QZ	35	670	550	4	1
DT9440-QZ	36	570	450	4	1
DT9442-QZ	38	570	450	4	1
DT9445-QZ	40	570	450	4	1
DT9446-QZ	40	920	800	4	1
DT9447-QZ	42	570	450	4	1
DT9448-QZ	45	570	450	4	1
DT9449-QZ	50	570	450	4	1
DT9450-QZ	52	570	450	4	1



EXTREME SDS-max[®] HOLLOW DRILL BITS **NEW**

PERFORM PROTECT

HOLLOW SHAFT
Vacuum assisted dust extraction means less dust, reduced resistance, faster drilling, and less hole cleaning. Fit with a M class vacuum to remove 98% of drilling dust from the drill tip area

FAST DRILLING IN CONCRETE
Resistance is reduced as drilling dust is routed internally

SDS-max
Compatible with SDS-max[®] fitment hammer drills

AIRLOCK[™] ADAPTOR
Connects directly to DeWALT's Airlock[™] System forming a secure connection between bit and dust extractor

Y-CUTTER CARBIDE
For exact positioning of SDS-max[®] drill bit diameters, delivering accurate starting and durability



APPLICATIONS

Fast drilling into concrete with less dust. Ideal for interior applications. Less hole cleaning required. Please refer to anchor ETA for correct installation information.

FOR USE WITH
SDS-max[®] hammer drills.

Made in Germany.



SINGLE PACKS

Cat. No.	Ø mm	Total length mm	Working length mm	Cutters	Pack Qty.
DT60230-QZ	16	400	600	4	1
DT60231-QZ	18	400	600	4	1
DT60232-QZ	20	400	600	4	1
DT60233-QZ	24	400	600	4	1
DT60234-QZ	28	400	600	4	1
DT60235-QZ	32	400	600	4	1



XLR SDS-plus[®]

SPEED
4 flute helix maximises debris removal for fast drilling and clear holes. Long helix length with optimised free space for faster debris removal.

DURABILITY
Optimised heat treatment for maximum strength. The drill tip and body are unbreakably connected to each other by using the resistance welding method.

CARBIDE TIP
Solid piece carbide with four cutting faces to prevent jamming in rebar. Provides cleaner, more concentric holes and constant high drilling speed. The carbide tip and body are brazed together via an innovative welding technique creating a strong durable bond.



APPLICATIONS

Suitable for drilling plug and anchor holes in masonry, all types of stone and concrete.

FOR USE WITH
SDS-plus[®] fitment hammer drills (cordless and corded).

Made in Germany.



SET

Cat. No.	Description	Ø mm
DT8976-QZ	7 piece hammer drill bits in metal cassette	5 / 6 / 8 (110mm) / 6 / 8 / 10 / 12 (160mm)

SINGLE PACKS

Cat. No.	Ø mm	Total length mm	Working length mm	Pack Qty.
DT8907-QZ	5	110	50	1
DT8908-QZ	5	160	100	1
DT8909-QZ	5	210	150	1
DT8910-QZ	5.5	110	50	1
DT8911-QZ	5.5	160	100	1
DT8912-QZ	6	110	50	1
DT8913-QZ	6	160	100	1
DT8914-QZ	6	210	150	1
DT8915-QZ	6	260	200	1
DT8916-QZ	6.5	160	100	1
DT8917-QZ	6.5	210	150	1
DT8918-QZ	6.5	260	200	1
DT8919-QZ	6.5	310	250	1
DT8920-QZ	7	160	100	1
DT8921-QZ	7	210	150	1
DT8922-QZ	8	110	50	1
DT8923-QZ	8	160	100	1
DT8924-QZ	8	210	150	1
DT8925-QZ	8	260	200	1
DT8926-QZ	8	310	250	1
DT8927-QZ	8	460	400	1
DT8928-QZ	10	160	100	1
DT8929-QZ	10	210	150	1
DT8930-QZ	10	260	200	1
DT8931-QZ	10	310	250	1
DT8932-QZ	10	460	400	1
DT8933-QZ	12	160	100	1
DT8934-QZ	12	200	150	1
DT8935-QZ	12	260	200	1
DT8936-QZ	12	310	260	1
DT8937-QZ	12	460	400	1
DT8938-QZ	14	160	100	1
DT8939-QZ	14	200	150	1
DT8940-QZ	14	260	200	1
DT8941-QZ	14	310	250	1
DT8942-QZ	14	460	400	1

BULK PACKS

Cat. No.	Ø mm	Total length mm	Working length mm	Pack Qty.
DT8950-QZ	5	110	50	10
DT8951-QZ	5	160	100	10
DT8955-QZ	6	110	50	10
DT8956-QZ	6	160	100	10
DT8957-QZ	6	210	150	10
DT8961-QZ	6.5	260	200	10
DT8965-QZ	8	160	100	10
DT8982-QZ	8	160	100	25
DT8966-QZ	8	210	150	10
DT8983-QZ	8	310	250	25
DT8967-QZ	10	160	100	10
DT8968-QZ	10	210	150	10
DT8969-QZ	10	260	200	10
DT8971-QZ	12	160	100	10
DT8972-QZ	12	200	150	10
DT8973-QZ	14	200	150	10



EXTREME[®] SDS-plus[®] 4 CUTTER

MAXIMISED CENTRAL CORE
Enables more efficient energy transmission to the drill bit head.

4 FLUTE SPIRAL
with maximum flute entry enables faster debris removal.

CARBIDE TIP
The solid two cutter head is flanked by two individual cutting tips delivering a fast and efficient drilling speed. These carbide tips and body are brazed together to create a strong and durable bond.




EXTREME[®] SDS-plus[®] 2 CUTTER

4 FLUTE HELIX
The 4 flute spiral incorporates a maximised central core for increased durability and energy transmission.

CORE REINFORCEMENT
Hardened steel body for extra strength and reduced breakage.

CARBIDE TIP
The solid two cutter head is flanked by two individual cutting tips delivering a fast and efficient drilling speed. These carbide tips and body are brazed together to create a strong and durable bond.



APPLICATIONS
For fixing holes and through holes 16mm - 30mm.



FOR USE WITH
SDS-plus[®] hammer drills, (corded and cordless).

Made in Germany.



SINGLE PACKS

Cat. No.	Ø mm	Total length mm	Working length mm	Pack Qty.
DT9680-QZ	16	250	200	1
DT9681-QZ	16	450	400	1
DT9682-QZ	18	250	200	1
DT9683-QZ	18	450	400	1
DT9684-QZ	20	250	200	1
DT9685-QZ	20	450	400	1
DT9686-QZ	22	250	200	1
DT9687-QZ	22	450	400	1
DT9688-QZ	24	250	200	1
DT9689-QZ	24	450	400	1
DT9690-QZ	25	250	200	1
DT9691-QZ	25	450	400	1
DT9692-QZ	26	450	400	1
DT9693-QZ	28	250	200	1
DT9694-QZ	28	450	400	1
DT9695-QZ	30	250	200	1
DT9696-QZ	30	450	400	1

SET

Cat. No.	Description	Ø mm
DT9674-QZ	10 pack SDS-plus [®] Extreme [®] 2 Cutter drill bits plus thermal mug	6mm
DT9675-QZ	10 pack SDS-plus [®] Extreme [®] 4 Cutter drill bits plus thermal mug	7mm



APPLICATIONS
Suitable for fast drilling of plug, anchor or clearance holes in masonry, stone, concrete and brick/block work.



FOR USE WITH
SDS-plus[®] fitment hammer drills (cordless and corded).

Made in Germany.



SINGLE PACKS

Cat. No.	Ø mm	Total length mm	Working length mm	Pack Qty.
DT9625-QZ	3	135	75	1
DT9500-QZ	3.5	110	50	1
DT9502-QZ	4	110	50	1
DT9503-QZ	4	160	100	1
DT9504-QZ	5	110	50	1
DT9505-QZ	5	160	100	1
DT9506-QZ	5	210	150	1
DT9507-QZ	5	310	250	1
DT9620-QZ	5	460	400	1
DT9508-QZ	5.5	110	50	1
DT9509-QZ	5.5	160	100	1
DT9510-QZ	5.5	210	150	1
DT9511-QZ	5.5	260	200	1
DT9512-QZ	5.5	310	250	1
DT9513-QZ	5.5	460	400	1
DT9514-QZ	6	110	50	1
DT9515-QZ	6	160	100	1
DT9516-QZ	6	210	150	1
DT9517-QZ	6	260	200	1
DT9621-QZ	6	310	250	1
DT9518-QZ	6	460	400	1
DT9520-QZ	6.5	160	100	1
DT9521-QZ	6.5	210	150	1
DT9522-QZ	6.5	260	200	1
DT9523-QZ	6.5	310	250	1
DT9524-QZ	7	110	50	1
DT9525-QZ	7	160	100	1
DT9526-QZ	7	210	150	1
DT9527-QZ	7	260	200	1
DT9528-QZ	8	110	50	1
DT9529-QZ	8	160	100	1
DT9530-QZ	8	210	150	1
DT9531-QZ	8	260	200	1
DT9532-QZ	8	310	250	1
DT9533-QZ	8	410	350	1
DT9534-QZ	8	460	400	1
DT9535-QZ	8	600	540	1
DT9536-QZ	9	160	100	1
DT9537-QZ	9	210	150	1
DT9539-QZ	10	110	50	1
DT9540-QZ	10	160	100	1
DT9541-QZ	10	210	150	1
DT9542-QZ	10	260	200	1
DT9543-QZ	10	310	250	1
DT9544-QZ	10	350	300	1
DT9545-QZ	10	460	400	1
DT9546-QZ	10	600	550	1
DT9547-QZ	10	1000	950	1
DT9548-QZ	11	160	100	1
DT9549-QZ	11	210	150	1
DT9552-QZ	12	160	100	1
DT9553-QZ	12	200	150	1
DT9554-QZ	12	260	200	1
DT9555-QZ	12	300	250	1
DT9556-QZ	12	350	300	1





EXTREME[®] SDS-plus[®] 2 CUTTER

SINGLE PACKS (CONTINUED)

Cat. No.	Ø mm	Total length mm	Working length mm	Pack Qty.
DT9557-QZ	12	450	400	1
DT9558-QZ	12	600	550	1
DT9559-QZ	12	1000	950	1
DT9560-QZ	13	160	100	1
DT9566-QZ	14	160	100	1
DT9567-QZ	14	200	150	1
DT9568-QZ	14	260	200	1
DT9569-QZ	14	300	250	1
DT9570-QZ	14	450	400	1
DT9571-QZ	14	600	550	1
DT9572-QZ	14	1000	950	1
DT9573-QZ	15	160	100	1
DT9574-QZ	15	200	150	1
DT9575-QZ	15	260	200	1
DT9576-QZ	15	300	250	1
DT9578-QZ	16	160	100	1
DT9579-QZ	16	200	150	1
DT9580-QZ	16	260	200	1
DT9581-QZ	16	300	250	1
DT9582-QZ	16	450	400	1
DT9583-QZ	16	600	550	1
DT9584-QZ	16	800	750	1
DT9585-QZ	16	1000	950	1
DT9587-QZ	18	200	150	1
DT9588-QZ	18	250	200	1
DT9589-QZ	18	300	250	1

Cat. No.	Ø mm	Total length mm	Working length mm	Pack Qty.
DT9590-QZ	18	450	400	1
DT9591-QZ	18	600	550	1
DT9592-QZ	18	800	750	1
DT9593-QZ	18	1000	950	1
DT9597-QZ	20	200	150	1
DT9598-QZ	20	300	250	1
DT9599-QZ	20	450	400	1
DT9600-QZ	20	600	550	1
DT9601-QZ	20	1000	950	1
DT9602-QZ	22	250	200	1
DT9603-QZ	22	300	250	1
DT9604-QZ	22	450	400	1
DT9605-QZ	22	600	550	1
DT9606-QZ	22	800	750	1
DT9607-QZ	22	1000	950	1
DT9609-QZ	24	250	200	1
DT9610-QZ	24	450	400	1
DT9611-QZ	25	250	200	1
DT9612-QZ	25	300	250	1
DT9613-QZ	25	450	400	1
DT9614-QZ	25	1000	950	1
DT9615-QZ	26	250	200	1
DT9616-QZ	26	450	400	1
DT9617-QZ	26	800	750	1
DT9618-QZ	30	250	200	1
DT9619-QZ	30	450	400	1

BULK PACKS

Cat. No.	Ø mm	Total length mm	Working length mm	Pack Qty.
DT9800-QZ	5	110	50	10
DT9803-QZ	5	160	100	10
DT9812-QZ	6	110	50	10
DT9815-QZ	6	160	100	10
DT9816-QZ	6	160	100	50
DT9818-QZ	6	210	150	10
DT9846-QZ	6.5	210	150	10
DT9827-QZ	8	160	100	10
DT9830-QZ	8	210	150	10
DT9834-QZ	10	160	100	10
DT9835-QZ	10	160	100	50
DT9837-QZ	10	210	150	10
DT9838-QZ	10	260	200	10
DT9839-QZ	12	160	100	10
DT9840-QZ	12	160	100	50
DT9841-QZ	12	200	150	10
DT9842-QZ	12	260	200	10
DT9843-QZ	14	200	150	10

SETS

Cat. No.	Description	Ø mm
DT9700-QZ	4 piece drill bit set in plastic cassette	5 / 6 / 8 / 10mm
DT9701-QZ	7 piece set in metal cassette	5 / 6 / 8 (110mm) 6 / 8 / 10 / 12 (160mm)
DT9702-QZ	4 piece set in plastic cassett	5.5 / 7 / 8 / 10mm
DT9735B-QZ	10 piece set in plastic ToughCase™	5 / 2x 6 (110mm) 2x 6 / 7 / 8 / 9 / 10 / 12 (160mm)
DT9399-QZ	5 piece set	5mm, 2 x 6mm, 2 x 8mm (110mm)



EXTREME[®] SDS-plus[®] HOLLOW DRILL BITS **NEW**



PERFORM PROTECT

SDS-plus[®]
Compatible with SDS-plus[®] fitment hammer drills

HOLLOW SHAFT
Vacuum assisted dust extraction means less dust, reduced resistance, faster drilling, and less hole cleaning. Fit with a M class vacuum to remove 98% of drilling dust from the drill tip area

AIRLOCK™ ADAPTOR
Connects directly to DeWALT's Airlock™ System forming a secure connection between bit and dust extractor

FAST DRILLING IN CONCRETE
Resistance is reduced as drilling dust is routed internally

2-CUTTER CARBIDE
For exact positioning of SDS-plus[®] drill bit diameters, delivering accurate starting and durability



APPLICATIONS

Fast drilling into concrete with less dust. Ideal for interior applications. Less hole cleaning required. Please refer to anchor ETA for correct installation information.

FOR USE WITH
SDS-plus[®] hammer drills.

Made in Germany.



SINGLE PACKS

Cat. No.	Ø mm	Total length mm	Working length mm	Cutters	Pack Qty.
DT60340-QZ	12	200	320	4	1
DT60341-QZ	14	250	370	4	1
DT60342-QZ	16	250	370	4	1
DT60343-QZ	18	250	370	4	1



SDS-plus® FITMENT

DURABILITY
Additional core reinforcement for optimum impact energy transmission and breakage stability.

FLUTE DESIGN
2 flute helix: specially developed drilling helix for efficient removal of dust

CARBIDE TIP
Optimised drill head design with 2 cutting edges.



APPLICATIONS
Suitable for fast drilling of plug, anchor or clearance holes in masonry, stone, concrete and brick/block work.

FOR USE WITH
SDS-plus® hammer drills, (cordless and corded).



SINGLE PACKS

Cat. No.	Ø mm	Total length mm	Working length mm	Pack Qty.
DT9630-QZ	4	110	50	1
DT9662-QZ	5	110	50	1
DT9631-QZ	5	160	100	1
DT9632-QZ	5	210	150	1
DT9633-QZ	5.5	160	100	1
DT9634-QZ	5.5	210	150	1
DT9663-QZ	6	110	50	1
DT9635-QZ	6	160	100	1
DT9636-QZ	6	210	150	1
DT9637-QZ	6.5	160	100	1
DT9638-QZ	6.5	210	150	1
DT9639-QZ	7	160	100	1
DT9640-QZ	7	210	150	1
DT9664-QZ	8	110	50	1
DT9641-QZ	8	160	100	1
DT9642-QZ	8	210	150	1
DT9643-QZ	8	310	250	1
DT9665-QZ	10	110	50	1
DT9644-QZ	10	160	100	1
DT9645-QZ	10	210	150	1
DT9646-QZ	10	310	250	1
DT9647-QZ	12	160	100	1
DT9648-QZ	12	210	150	1
DT9649-QZ	12	310	250	1
DT9650-QZ	14	160	100	1
DT9651-QZ	14	210	150	1
DT9652-QZ	14	310	250	1
DT9653-QZ	16	210	150	1
DT9654-QZ	16	460	400	1
DT9655-QZ	18	210	150	1
DT9656-QZ	18	460	400	1
DT9657-QZ	20	210	150	1
DT9658-QZ	20	460	400	1
DT9659-QZ	22	460	400	1
DT9660-QZ	24	460	400	1
DT9661-QZ	25	460	400	1

SETS

Cat. No.	Description	Ø mm
DT60301-QZ	5 piece SDS-plus® drill bit set in plastic cassette	5 / 2x 6 / 8 / 10mm
DT60302-QZ	6 piece SDS-plus® drill bit set in plastic cassette	2x 6 / 2x 8 / 2x 10mm
DT9679-QZ	15 piece SDS-plus® drill bit and chisel set + 4 chisels in aluminium case	5 / 5.5 / 2x 6 / 7 / 2x 8 / 2x 10 / 12 / 14mm

SDS-max® CORE CUTTERS



APPLICATIONS
For clean round holes in blocks, bricks and light concrete.



FOR USE WITH
For drilling holes in concrete or masonry from 50 to 80mm diameter



To be used with heavy duty SDS-max® core drills in conjunction with a pilot bit.



CARBIDE CORE CUTTERS - SINGLE PACKS

Cat. No.	Ø Size	Total length mm	Pack Qty.
DT6762-QZ	65	107	1
DT6763-QZ	80	107	1
DT6766-QZ	125	107	1

CORE ADAPTERS AND PILOT BITS

Cat. No.	Description	Ø Size	Total length mm	Pack Qty.
DT6770-QZ	Adapter SDS-max®	180	1	1
DT6771-QZ	Adapter SDS-max®	400	1	1
DT6772-QZ	Pilot drill 12mm	155	1	1

SINGLE PACKS

Cat. No.	Description	Pack Qty.
DT6830-QZ	SDS-max® to SDS-plus®	1
DT7030-QZ	SDS-plus® 1/2" x 20 UNF (chuck adapter)	1


SDS-plus® CORE CUTTERS



APPLICATIONS
For fitting drainage and water pipes, heating pipes, switches, junction and distribution boxes.



FOR USE WITH
To be used with light duty SDS-plus® core drills, must be used with a pilot bit.



CARBIDE CORE CUTTERS - SINGLE PACKS

Cat. No.	Ø mm	Total length mm	Pack Qty.
DT6745-QZ	68	72	1
DT6747-QZ	80	72	1

CORE BITS AND PILOT DRILLS - SINGLE PACKS

Cat. No.	Description	Ø Size	Total length mm	Pack Qty.
DT6750-QZ	Adapter SDS-plus®	110	1	1
DT6751-QZ	Adapter SDS-plus®	300	1	1
DT6753-QZ	Pilot drill bit 9mm	120	1	1

SDS-max® SINGLE PIECE CARBIDE CORE BITS

APPLICATIONS
For fitting drainage and water pipes, heating pipes, switches, junction and distribution boxes.

FOR USE WITH
To be used with light duty SDS-plus® drills, must be used with a pilot bit.

CORE BITS AND PILOT DRILLS - SINGLE PACKS

Cat. No.	Description	Ø Size	Total length mm	Pack Qty.
DT6789-QZ	SDS-max® core drill bit	68	300	1
DT6784-QZ	SDS-max® core drill bit	80	300	1
DT6785-QZ	Replacement pilot drill	12	128	1

XLR POINTS and CHISELS



LIFE/PRODUCTIVITY

High durability shock resistant steel minimises breakage and increases durability

WEAR RESISTANT

Strong, wear resistant steel to maintain impact face longer

SPEED/PRODUCTIVITY

Optimised tip geometry maintain breaking speed

STEEL POINTS AND CHISELS

Fully hardened steel point/chisel face for high wear resistance and increased productivity. The special 'Stay Sharp' chisel tip ensures a long-lasting sharpness of the chisel and thus an extended durability.

XLR SDS-max® POINTS and CHISELS



APPLICATIONS

For heavy duty chiselling, channelling and demolition tasks in concrete/rebar and hard stone.

The new XLR chisels combined with D-WALT® demolition hammers are ideal for even the toughest environments.



SINGLE PACKS

Cat. No.	Description	Width mm	Length mm	Pack Qty.
DT6888-QZ	Pointed chisel	-	300	1
DT6889-QZ	Pointed chisel	-	400	1
DT6811-QZ	Flat chisel	25	300	1
DT6812-QZ	Flat chisel	25	400	1
DT6818-QZ	Flat chisel	50	400	1
DT6980-QZ	Pointed chisel	75	400	1

SDS-max® POINTS and CHISELS



APPLICATIONS

For heavy duty chiselling, channelling, and demolition tasks in concrete, stone (medium hardness), floor and wall tiles, general masonry and mortar.



FEATURES AND BENEFITS

Specially toughened steel and micro-processor controlled heat treatment ensures consistent tough bits with long life.



SINGLE PACKS

Cat. No.	Description	Width mm	Total length mm	Pack Qty.
DT6820-QZ	Pointed chisel	-	300	1
DT6821-QZ	Pointed chisel	-	400	1
DT8087-QZ	Pointed chisel	-	600	1
DT6822-QZ	Flat chisel	25	300	1
DT6823-QZ	Flat chisel	25	400	1
DT6824-QZ	Flat chisel	50	360	1
DT6825-QZ	Flat chisel	80	300	1
DT8088-QZ	Flat chisel	25	600	1
DT6826-QZ	Hollow chisel	26	300	1
DT6834-QZ	Flat chisel	80	300	1
DT6837-QZ	TCT comb chisel	38	280	1
DT6838-QZ	Bush hammer	45	240	1
DT8090-QZ	Clay spade	110	400	1
DT8091-QZ	Asphalt cutter	90	400	1
DT8093-QZ	Earth rod driver	16.5	260	1



XLR SDS-plus® POINTS and CHISELS



SINGLE PACKS

Cat. No.	Description	Width mm	Total length mm	Pack Qty.
DT6978-QZ	Pointed chisel	-	300	1
DT6979-QZ	Flat chisel	20	300	1
DT6984-QZ	Flat chisel	40	300	1



SDS-plus® FITMENT POINTS and CHISELS



APPLICATIONS

Suitable for use in SDS-plus® hammer drills, with rotation stop for light chiselling applications in plaster, masonry, tiles etc.

FOR USE WITH

SDS-plus® hammer drills.



SINGLE PACKS

Cat. No.	Description	Width mm	Total length mm	Pack Qty.
DT6801-QZ	Pointed chisel	-	250	1
DT6802-QZ	Flat chisel	20	250	1
DT6803-QZ	Flat chisel	40	250	1
DT6804-QZ	Flat chisel	22	250	1
DT6805-QZ	Hollow chisel	22	240	1
DT6806-QZ	Flat chisel	40	250	1
DT6810-QZ	HM-joints chisel	32	200	1



HEXAGONAL SHANK POINTS and CHISELS



19mm HEX CHISELS

Cat. No.	Description	Width mm	Length mm	Pack Qty.
DT6940-QZ	Pointed	-	400	1
DT6941-QZ	Pointed	-	600	1
DT6942-QZ	Flat	25	400	1
DT6943-QZ	Flat	25	600	1
DT6945-QZ	Flat	60	450	1
DT6953-QZ	Pointed	-	400	1
DT6958-QZ	Flat	25	400	1

28mm HEX CHISELS

Cat. No.	Description	Width mm	Length mm	Pack Qty.
DT6927-QZ	Hexagon point	-	400	1
DT6928-QZ	Bull point	140	584	1
DT6929-QZ	Cold chisel	32	521	1
DT6932-QZ	Scaling tool	75	521	1
DT6934-QZ	Steel asphalt cutter	127	445	1

30mm HEX CHISELS

Cat. No.	Description	Width mm	Length mm	Pack Qty.
DT6808-QZ	Pointed	-	410	1
DT6809-QZ	Spade	36	420	1





SDS-plus® FITMENT DRILLING and CHISELING SETS

DRILLING AND CHISELING SETS

Cat. No.	Description
DT60330-QZ	3 piece set: 250mm point chisel 20mm x 250 and 40mm x 250mm flat chisel
DT9679-QZ	15 Piece SDS-plus® drill bit and chisel set in aluminium case 5, 5.5, 6, 6, 7, 8, 8, 10, 10, 12, 14mm 4 chisels





EXTREME® ROUND SHANK PERCUSSION

ANTI-SLIP SHANK
Three ridged chamfered edges prevent rotation of the drill bit in the chuck.

HARDENED STEEL BODY
With core reinforcement and a large-volume machined spiral. For maximum tensile strength combined with very high drilling progress.

UNIQUE HARD METAL
With low-stress high-temperature copper soldering, optimised for maximum durability and break-out safety.



APPLICATIONS

Typically used for drilling anchor, plastic plug, fixing or pipework clearance holes.



Suitable for masonry, brick, stone, tiles and light concrete.



FOR USE WITH

Percussion drills and cordless hammer drills.

Made in Germany.



SINGLE PACKS


Cat. No.	Ø mm	Total length mm	Working length mm	Pack Qty.
DT6695-XJ	3	110	70	1
DT6671-XJ	4	75	50	1
DT6672-XJ	5	85	50	1
DT6673-XJ	5	150	100	1
DT6674-XJ	5.5	85	50	1
DT6675-XJ	6	100	60	1
DT6676-XJ	6	150	100	1
DT6677-XJ	6	200	150	1
DT6678-XJ	6.5	100	60	1
DT6679-XJ	6.5	150	100	1
DT6680-XJ	7	100	60	1
DT6681-XJ	7	150	100	1
DT6682-XJ	8	120	80	1
DT6683-XJ	8	200	150	1
DT6684-XJ	9	120	80	1
DT6685-XJ	10	120	80	1
DT6686-XJ	10	200	150	1
DT6687-XJ	12	150	100	1
DT6688-XJ	12	200	150	1
DT6689-XJ	13	150	100	1
DT6690-XJ	14	150	100	1
DT6691-XJ	14	200	150	1
DT6692-XJ	16	150	100	1
DT6693-XJ	16	200	150	1

SETS

Cat. No.	Description	mm
DT6956-QZ	5 piece set in plastic cassette	4 / 5 / 6 / 8 / 10mm
DT70712-QZ	19 piece set in small ToughCase™ with EXTREME® masonry drill bits Bits 25mm: 4x Ph2, 4x Pz2 50mm: Ph2, Pz2, SL5.5 Magnetic holder	4 / 5 / 5.5 / 6 / 7 / 8mm




ROUND SHANK PERCUSSION



FEATURES AND BENEFITS

- Rotary/percussion masonry drill bit 130° Douglas form carbide tip.
- Shank diameter of drill bits 10-13mm is reduced to 9.5mm.
- Shank diameter of drill bits larger than 13mm is reduced to 12.7mm.



APPLICATIONS

For drilling into concrete, masonry, natural and artificial stone, brick, etc

FOR USE WITH

Heavy duty corded and cordless hammer drills.



SINGLE PACKS

Cat. No.	Ø mm	Total length mm	Working length mm	Pack Qty.
DT6500-QZ	3	60	28	1
DT6504-QZ	4	75	38	1
DT6505-QZ	5	85	44	1
DT6552-QZ	5	150	82	1
DT6502-QZ	5.5	85	44	1
DT6506-QZ	6	100	54	1
DT6556-QZ	6	150	82	1
DT6606-QZ	6	200	135	1
DT6503-QZ	6.5	100	54	1
DT6507-QZ	7	100	54	1
DT6557-QZ	7	150	82	1
DT6508-QZ	8	120	67	1
DT6558-QZ	8	150	82	1
DT6608-QZ	8	200	135	1
DT6708-QZ	8	400	230	1
DT6509-QZ	9	120	67	1
DT6510-QZ	10	120	67	1
DT6560-QZ	10	150	80	1
DT6610-QZ	10	200	135	1
DT6710-QZ	10	400	230	1
DT6732-QZ	10	600	400	1
DT6562-QZ	12	150	82	1
DT6612-QZ	12	200	135	1
DT6712-QZ	12	400	230	1
DT6733-QZ	12	600	400	1
DT6563-QZ	13	150	82	1
DT6564-QZ	14	150	82	1
DT6714-QZ	14	400	230	1
DT6566-QZ	16	150	82	1
DT6716-QZ	16	400	230	1
DT6718-QZ	18	400	230	1
DT6720-QZ	20	400	230	1

SETS

Cat. No.	Description
DT6952-QZ	5 piece set in plastic cassette 4 / 5 / 6 / 8 / 10mm

EXTREME[®] DIAMOND TILE DRILL BITS

ROBUST DIAMOND CUT

Resistant and extremely hard. Allows easy drilling into the material at 45° and suitable for almost all degrees of hardness of ceramic tile.

DIAMOND GRIT EDGED HEAD

Tough and hard wearing, enables 'easy start' drilling at 45° into material and copes with almost any hardness of tile.

ROUNDED SHANK

For mounting in quick-clamping chuck.

EJECTION SLOT

Enables easy removal of material 'core' after drilling in deeper tiles.

WATER BEARING HELIX

Open head design helps more effective cooling with water.




APPLICATIONS

Clean concentric holes in all wall and floor tiles (up to and including Class 5 hardness), porcelain, marble, granite and slate.

Ideal for installing fixtures and fittings in bathrooms and kitchens.

FOR USE WITH

Corded and cordless drills.



DIAMOND DRILL BITS - SINGLE PACKS

Cat. No.	Ø mm	Pack Qty.
DT6037-QZ	5	1
DT6038-QZ	6	1
DT6039-QZ	7	1
DT6040-QZ	8	1
DT6041-QZ	10	1
DT6042-QZ	12	1
DT6043-QZ	15	1
DT6044-QZ	20	1
DT6045-QZ	25	1

SETS

Cat. No.	Description	Size mm
DT6049-QZ	4 piece set diamond tile drill bits in plastic box with water supply system	6 / 8 / 10 / 15mm
DT6046-QZ	5 piece set diamond tile drill bits in plastic box with water supply system	5 / 6 / 7 / 8 / 10mm



MULTI MATERIAL DRILL BITS



FEATURES AND BENEFITS

- CrNiMo steel for optimal power transmission and breakage stability even in the toughest applications.
- Carbide tip with unique 120° tip grind for maximum sharpness, faster drilling and extended life.
- Robust diamond cut.
- Resistant and extremely hard.
- Allows easy drilling into the material at 45° and suitable for almost all degrees of hardness of ceramic tile.
- Anti slip shank with 3 milled clamping surfaces prevent rotation of the drill bit in the chuck.

APPLICATIONS

Suitable for wood, plastics, mild steel and non ferrous metals and masonry.

FOR USE WITH

Corded and cordless drills.



FEATURES AND BENEFITS

- Carbide head design allows faster drilling and longer durability.

APPLICATIONS

Suitable for wood, plastics, concrete, brick, light building materials, multi-layer materials and masonry.

FOR USE WITH

Drills and hammer drills (cordless and corded). Impact drivers and screwdrivers with bit holder or chuck.



MULTI MATERIAL DRILL BITS

SINGLE PACKS

Cat. No.	Ø mm	Total length mm	Working length mm	Pack Qty.
DT6515-QZ	3	113	83	1
DT6516-QZ	3.5	113	83	1
DT6517-QZ	4	103	73	1
DT6518-QZ	5	113	83	1
DT6527-QZ	5.5	113	83	1
DT6528-QZ	5.5	200	170	1
DT6519-QZ	6	123	93	1
DT6529-QZ	6	200	170	1
DT6520-QZ	6.5	123	93	1
DT6530-QZ	6.5	200	170	1
DT6521-QZ	7	123	93	1
DT6522-QZ	8	134	104	1
DT6531-QZ	8	200	170	1
DT6523-QZ	9	134	104	1
DT6524-QZ	10	134	104	1
DT6533-QZ	10	200	170	1
DT6525-QZ	12	153	123	1
DT6526-QZ	13	160	130	1



IMPACT READY MULTI MATERIAL DRILL BITS

SINGLE PACKS

Cat. No.	Ø mm	Total length mm	Working length mm	Pack Qty.
DT60000-QZ	4	103	73	1
DT60001-QZ	5	113	83	1
DT60003-QZ	6	123	93	1
DT60004-QZ	8	200	170	1

SET


Cat. No.	Description	Ø mm	Pack Qty.
DT60099-QZ	5 piece set Impact Ready multi-purpose drill bits	4 / 5 / 5.5 / 6 / 8mm	5





Metal Drill Bits

RECOMMENDED MATERIALS



HSS-CO
 For use in high-alloyed steels up to 1100 N/mm² tensile strength, grey and malleable, acid and heat-resistant and stainless steels.
 Ground drill bit, made of cobalt-alloyed high-speed steel (5% cobalt) for maximum temperature resistance and wear resistance.



HSS-G
 For use in alloyed and unalloyed steels up to 900 N/mm² tensile strength, sheet metal and thin-walled profile materials, wood and plastics.
 Ground drill bit made of one piece for an increased resistance to breakage and clean holes.



HSS-TiN
 For use in alloyed and unalloyed steels up to 900 N/mm² tensile strength, sheet metal and thin-walled profile materials, wood and plastics.
 Ground drill bit with titanium coating reduces friction, lowers drilling temperature and increases product life.
 In addition the titanium coating is both wear resistant and corrosion resistant.



HSS-R
 For use in alloyed and unalloyed steels up to 900 N/mm² tensile strength, sheet metal and thin-walled profile materials, wood and plastics.
 Rolled drill bit made of one piece.

EXTREME[®] INDUSTRIAL COBALT HSS-CO

LONG LASTING

5% cobalt content maintains a sharper cutting edge and delivers 4 x longer life (vs HSS-R).

SIZE INDICATORS

Away from abrasion and, located outside of grip zone, positioning ensures easy readability (from 5mm diameter and up).

NO-WALK TIP

The 'no walk' tip allows for easier penetration of all surfaces (5mm and above). Cleaner, more accurate, burr-free holes due to recessed cutting wings.

NO-SLIP SHANK

Spin proof 3 sided shaft for optimal grip in drill chuck (diameters 5mm and above only).

STRONG CENTRAL CORE

Increasing in thickness towards the chuck, the central core improves fracture stability, particularly in freehand use (4.8mm diameter and up).

FASTER DRILLING

The optimised tip and flute geometry delivers 4 x the penetration speed (vs HSS-R). It also removes debris faster and reduces heat build up.



APPLICATIONS

Suitable for portable or stationary drilling of high alloy content steels and metals with a tensile strength up to 1100N/mm² e.g. heat and acid proof steel, cast iron, bronze, welded seams, stainless and chrome nickel steels.

Made in Germany.



PACKS

Cat. No.	Ø mm	Total length mm	Working length mm	Pack Qty.
DT4958-QZ	1	34	12	2
DT4959-QZ	1.5	40	18	2
DT4900-QZ	2	49	24	2
DT4901-QZ	2.5	57	30	2
DT4902-QZ	3	61	33	2
DT4960-QZ	3.3	65	36	2
DT4903-QZ	3.5	70	39	2
DT4904-QZ	4	75	43	2
DT4961-QZ	4.2	75	43	1
DT4905-QZ	4.5	80	47	1
DT4906-QZ	5	86	52	1
DT4907-QZ	5.5	93	57	1
DT4908-QZ	6	93	57	1
DT4909-QZ	6.5	101	63	1
DT4910-QZ	6.8	109	66	1
DT4911-QZ	7	109	69	1
DT4962-QZ	7.5	109	66	1
DT4912-QZ	8	117	75	1
DT4963-QZ	8.5	117	75	1
DT4913-QZ	9	125	81	1
DT4964-QZ	9.5	125	78	1
DT4914-QZ	10	133	87	1
DT4965-QZ	10.5	133	87	1
DT4915-QZ	11	142	94	1
DT4966-QZ	11.5	142	91	1
DT4916-QZ	12	151	101	1
DT4967-QZ	12.5	151	98	1
DT4917-QZ	13	151	101	1

EXTREME[®] INDUSTRIAL COBALT HSS-CO



BULK PACKS

Cat. No.	Ø mm	Total length mm	Working length mm	Pack Qty.
DT4918-QZ	2	49	24	10
DT4919-QZ	2.5	57	30	10
DT4920-QZ	3	61	33	10
DT4921-QZ	3.2	65	36	10
DT4922-QZ	3.3	65	36	10
DT4923-QZ	3.5	70	39	10
DT4924-QZ	4	75	43	10
DT4925-QZ	4.1	75	43	10
DT4926-QZ	4.2	75	43	10
DT4927-QZ	4.5	80	47	10
DT4928-QZ	4.8	86	52	10
DT4929-QZ	5	86	52	10
DT4930-QZ	5.1	86	52	10
DT4931-QZ	5.2	86	52	10
DT4932-QZ	5.5	93	57	10
DT4933-QZ	6	93	57	10
DT4934-QZ	6.5	101	63	10
DT4935-QZ	6.8	109	66	10
DT4936-QZ	7	109	69	10
DT4937-QZ	7.5	109	66	10
DT4938-QZ	8	117	75	10
DT4939-QZ	8.5	117	75	10
DT4940-QZ	9	125	81	10
DT4941-QZ	9.5	125	81	10
DT4942-QZ	10	133	87	10
DT4943-QZ	10.2	133	87	10
DT4944-QZ	10.5	133	87	5
DT4945-QZ	11	142	94	5
DT4946-QZ	11.5	142	91	5
DT4947-QZ	12	151	101	5
DT4948-QZ	12.5	151	98	5
DT4949-QZ	13	151	98	5



SETS

Cat. No.	Description	Ø mm
DT4956-QZ	6 piece set of metal drills HSS-Co in plastic cassette	2 / 3 / 4 / 5 / 6 / 8mm
DT4957-QZ	29 piece of metal drills HSS-Co in index cassette	1 / 1.5 / 2 / 2.5 / 3 / 3.2 / 3.3 / 3.5 / 4 / 4.2 / 4.5 / 4.8 / 5 / 5.5 / 6 / 6.5 / 7 / 7.5 / 8 / 8.5 / 9 / 9.5 / 10 / 10.5 / 11 / 11.5 / 12 / 12.5 / 13mm



EXTREME[®] HSS-G

INCREASED DURABILITY AND SPEED
Up to 50% stronger (vs HSS-R).
Up to 4X faster drilling (vs HSS-R).

NO-WALK TIP
Cleaner, more accurate,
burr-free holes due to
recessed cutting wings.

NO-SLIP SHANK
With 3 flat sides eliminates slipping
in the chuck (diameters 5.0mm and
above only).

STRONG CENTRAL CORE
Innovative tapered web greatly reduces
breakage. Gold ferrous oxide coating prevents
overheating for longer bit life.



APPLICATIONS

Suitable for portable drilling of
steel, alloyed and non-alloyed
up to 900 N/mm².



FOR USE WITH

Drilling sheet or thin
materials (suitable for use
in wood and plastics).



PACKS

Cat. No.	Ø mm	Total length mm	Working length mm	Pack Qty.
DT5034-QZ	1	34	12	2
DT5035-QZ	1.5	40	18	2
DT5036-QZ	2	49	24	2
DT5037-QZ	2.5	57	30	2
DT5038-QZ	3	61	33	2
DT5039-QZ	3.2	65	36	2
DT5040-QZ	3.3	65	36	2
DT5041-QZ	3.5	70	39	2
DT5042-QZ	4	75	43	2
DT5063-QZ	4.1	75	43	1
DT5043-QZ	4.2	75	43	1
DT5044-QZ	4.5	80	46	1
DT5045-QZ	4.8	86	46	1
DT5046-QZ	5	86	46	1
DT5047-QZ	5.5	93	57	1
DT5048-QZ	6	93	57	1
DT5049-QZ	6.5	101	58	1
DT5067-QZ	6.8	109	66	1
DT5050-QZ	7	109	66	1
DT5051-QZ	7.5	109	66	1
DT5052-QZ	8	117	72	1
DT5053-QZ	8.5	117	72	1
DT5054-QZ	9	125	78	1
DT5055-QZ	9.5	125	78	1
DT5056-QZ	10	133	84	1
DT5057-QZ	10.5	133	84	1
DT5058-QZ	11	142	91	1
DT5059-QZ	11.5	142	91	1
DT5060-QZ	12	151	98	1
DT5061-QZ	12.5	151	98	1
DT5062-QZ	13	151	98	1

EXTREME[®] 2 HSS-G



BULK PACKS

Cat. No.	Ø mm	Total length mm	Working length mm	Pack Qty.
DT5535-QZ	1	34	12	10
DT5536-QZ	1.5	40	18	10
DT5537-QZ	2	49	24	10
DT5538-QZ	2.5	57	30	10
DT5539-QZ	3	61	33	10
DT5540-QZ	3.2	65	36	10
DT5541-QZ	3.3	65	36	10
DT5542-QZ	3.5	70	39	10
DT5543-QZ	4	75	43	10
DT5566-QZ	4.1	75	43	10
DT5544-QZ	4.2	75	43	10
DT5545-QZ	4.5	80	46	10
DT5546-QZ	4.8	86	46	10
DT5547-QZ	5	86	46	10
DT5567-QZ	5.1	86	46	10
DT5568-QZ	5.2	86	46	10
DT5548-QZ	5.5	93	57	10
DT5549-QZ	6	93	57	10
DT5550-QZ	6.5	101	58	10
DT5551-QZ	7	109	66	10
DT5552-QZ	7.5	109	66	10
DT5553-QZ	8	117	72	10
DT5554-QZ	8.5	117	72	10
DT5555-QZ	9	125	78	10
DT5556-QZ	9.5	125	78	10
DT5557-QZ	10	133	84	10
DT5558-QZ	10.5	133	84	10
DT5559-QZ	11	142	91	10
DT5560-QZ	11.5	142	91	10
DT5561-QZ	12	151	98	10
DT5562-QZ	12.5	151	98	10
DT5563-QZ	13	151	98	10


SETS

Cat. No.	Description and Contents	Ø mm
DT70710-QZ	13 piece set in small ToughCase™ with EXTREME [®] 2 HSS-G Metal Drill Bits in Blister Packaging	1.5 / 2 / 2.5 3 / 3.2 / 3.5 4 / 4.5 / 5 / 5.5 6 / 6.5 / 7mm
DT70711-QZ	19 piece set in small ToughCase™ with EXTREME [®] 2 HSS-G metal drill bits drill bits 25mm: 4x Ph2, 4x Pz2 50mm: Ph2, Pz2, SL5.5 Magnetic holder	2 / 3 / 4 / 5 / 6 / 8mm
DT7926-XJ	29 piece set in index cassette with EXTREME [®] 2 HSS-G metal drill bits	1 / 1.5 / 2 / 2.5 3 / 3.2 / 3.3 / 3.5 4 / 4.2 / 4.5 / 4.8 5 / 5.5 / 6 / 6.5 / 7 / 7.5 8 / 8.5 / 9 / 9.5 / 10 / 10.5 11 / 11.5 / 12 / 12.5 / 13mm
DT7938B-QZ	36 piece set in small ToughCase™ with EXTREME [®] 2 HSS-G metal drills drill bits 25mm: Pz1 / 2x Pz2 / Pz3 / Ph1 / Ph2 / Ph3 / T20 / T25 50mm: Pz2 / Ph2 70mm: T20 / T25 Magnetic holder (60mm) 10 Pack HSS-G drill bits mix + mug	1 / 1.5 2 / 2.5 3 / 3.2 / 3.3 / 3.5 4 / 4.2 / 4.5 / 4.8 5 / 5.5 6 / 6.5 7 / 7.5 8 10 12mm





HSS-G HIGH PERFORMANCE



FEATURES AND BENEFITS

- Special steel made from high-performance, high-speed steel (HSS) manufactured to DIN 33 for longer life.
- Spiral groove ground from solid stock right hand cutting, type N flute, precision ground at 118° point angle. Drills above 13mm (1/2") have a shank reduced to 12.7mm.
- Milled shaft. Drill bit diameter over 13mm manufactured with shaft milled at 12.7mm.
- Precision ground twist for rapid drilling, long life and excellent concentricity. Diameter tolerance to H8.

APPLICATIONS

Suitable for portable or stationary drilling in steel cast steel, alloyed and non-alloyed material, grey cast-iron, spherical-graphite cast iron, sintered iron, nickel, brass etc up to 900N/mm².



PACKS

Cat. No.	Ø mm	Total length mm	Working length mm	Pack Qty.
DT5201-QZ	1	34	12	2
DT5202-QZ	1.5	40	18	2
DT5203-QZ	2	49	24	2
DT5204-QZ	2.5	57	30	2
DT5205-QZ	3	61	33	2
DT5206-QZ	3.2	65	36	2
DT5208-QZ	3.5	70	39	2
DT5209-QZ	4	75	43	2
DT5211-QZ	4.2	75	43	1
DT5212-QZ	4.5	80	47	1
DT5213-QZ	4.8	86	52	1
DT5214-QZ	5	86	52	1
DT5215-QZ	5.5	93	57	1
DT5216-QZ	6	93	57	1
DT5217-QZ	6.5	101	63	1
DT5218-QZ	7	109	69	1
DT5219-QZ	8	117	75	1
DT5220-QZ	8.5	117	75	1
DT5221-QZ	9	125	81	1
DT5222-QZ	10	133	87	1
DT5224-QZ	11	142	94	1
DT5226-QZ	12	151	101	1
DT5227-QZ	13	151	101	1
DT5228-QZ	14	160	108	1
DT5229-QZ	15	169	114	1
DT5230-QZ	16	178	120	1


SETS

Cat. No.	Description	Ø mm
DT5921-QZ	10 piece set in plastic case	1 / 2 / 3 / 4 / 5 / 6 / 7 / 8 / 9 / 10mm
DT5922-QZ	13 piece set in plastic case	1.5 / 2 / 2.5 / 3.2 / 3 / 3.5 / 4 / 4.5 / 2x 5 / 5.5 / 6 / 6.5mm
DT5923-QZ	19 piece set in plastic case	1 / 1.5 / 2 / 2.5 / 3 / 3.5 / 4 / 4.5 / 5 / 5.5 / 6 / 6.5 / 7 / 7.5 / 8 / 8.5 / 9 / 9.5 / 10mm
DT5929-QZ	29 piece set in plastic case	1 / 1.5 / 2 / 2.5 / 3 / 3.2 / 3.3 / 3.5 / 4 / 4.2 / 4.5 / 4.8 / 5 / 5.5 / 6 / 6.5 / 7 / 7.5 / 8 / 8.5 / 9 / 9.5 / 10 / 10.5 / 11 / 11.5 / 12 / 12.5 / 13mm

BULK PACKS

Cat. No.	Ø mm	Total length mm	Working length mm	Pack Qty.
DT5301-QZ	1	34	12	10
DT5311-QZ	2	49	24	10
DT5321-QZ	3	61	33	10
DT5332-QZ	4	75	43	10
DT5342-QZ	5	86	52	10
DT5352-QZ	6	93	57	10
DT5362-QZ	7	109	69	10
DT5372-QZ	8	117	75	10
DT5377-QZ	8.5	117	75	10
DT5382-QZ	9	125	81	10
DT5387-QZ	9.5	125	81	10
DT5392-QZ	10	133	87	10
DT5393-QZ	10.5	133	87	10
DT5394-QZ	11	142	94	5
DT5396-QZ	12	151	101	5

HSS-R HIGH PERFORMANCE



FEATURES AND BENEFITS

- Non alloyed black oxide precision ground twist drill bit for rapid drilling, long life and excellent concentricity.
- Ground from solid stock right hand cutting, type N flute, precision ground 118° point angle.

SUITABLE FOR

Portable or stationary drilling in steel, alloyed and non alloyed material, cast iron, sintered iron, nickel, brass, etc. (up to 900N/mm²).



PACKS

Cat. No.	Ø mm	Total length mm	Working length mm	Pack Qty.
DT5101-QZ	1	34	12	2
DT5106-QZ	1.5	40	18	2
DT5110-QZ	2	49	24	2
DT5116-QZ	2.5	57	30	2
DT5121-QZ	3	61	33	2
DT5123-QZ	3.2	65	36	2
DT5124-QZ	3.25	70	39	2
DT5127-QZ	3.5	75	43	2
DT5132-QZ	4	75	43	1
DT5134-QZ	4.2	80	47	1
DT5137-QZ	4.5	86	52	1
DT5142-QZ	5	86	52	1
DT5147-QZ	5.5	93	57	1
DT5152-QZ	6	93	57	1
DT5157-QZ	6.5	101	63	1
DT5162-QZ	7	109	69	1
DT5167-QZ	7.5	109	69	1
DT5172-QZ	8	117	75	1
DT5177-QZ	8.5	117	75	1
DT5182-QZ	9	125	81	1
DT5191-QZ	10	133	87	1
DT5193-QZ	10.5	133	87	1
DT5194-QZ	11	133	87	1
DT5196-QZ	12	151	101	1
DT5197-QZ	12.5	151	101	1
DT5198-QZ	13	151	101	1

SETS

Cat. No.	Description	Ø mm
DT5911-QZ	10 piece set in plastic case	1 / 2 / 3 / 4 / 5 / 6 / 7 / 8 / 9 / 10mm
DT5912-QZ	13 piece set in plastic case	1.5 / 2 / 2.5 / 3.2 / 3 / 3.5 / 4 / 4.5 / 2x 5 / 5.5 / 6 / 6.5mm
DT5913-QZ	19 piece set in plastic case	1 / 1.5 / 2 / 2.5 / 3 / 3.5 / 4 / 4.5 / 5 / 5.5 / 6 / 6.5 / 7 / 7.5 / 8 / 8.5 / 9 / 9.5 / 10mm
DT5930-QZ	29 piece set in plastic case	1 / 1.5 / 2 / 2.5 / 3 / 3.2 / 3.3 / 3.5 / 4 / 4.2 / 4.5 / 4.8 / 5 / 5.5 / 6 / 6.5 / 7 / 7.5 / 8 / 8.5 / 9 / 9.5 / 10 / 10.5 / 11 / 11.5 / 12 / 12.5 / 13mm

EXTREME[®] IMPACT HSS-TIN METAL


QUICK CHANGE SHANK
for rapid change of accessory

TITANIUM COATING
For increased wear resistance, corrosion resistance and up to 2 x life (vs black oxide)

OPTIMISED FLUTE GEOMETRY
Specially ground shoulder cutting flutes for milling exact circular holes with clean edges

CORE REINFORCEMENT
2 X longer life, 2 X stronger core. Constantly increasing core diameter in the direction of the shaft for increased durability. Gives maximum fracture stability.

PILOT POINT
Penetrates material faster and allows precise drilling on curved surfaces.



APPLICATIONS

For use in alloyed and unalloyed steels up to 900 N/mm² tensile strength, sheet metal and thin-walled profile material (pipes and without pre-punching), where exact and clean drilling is required.

FOR USE WITH
Impact drivers.

SINGLE PACKS

Cat. No.	Ø mm	Total length mm	Working length mm	Pack Qty.
DT50000-QZ	3	64	26	1
DT50001-QZ	3.2	67	29	1
DT50002-QZ	3.5	70	29	1
DT50003-QZ	4	71	30	1
DT50004-QZ	4.2	71	31	1
DT50005-QZ	4.5	75	31	1
DT50006-QZ	4.8	76	32	1
DT50007-QZ	5	78	33	1
DT50008-QZ	5.5	78	35	1
DT50009-QZ	6	80	37	1
DT50010-QZ	6.5	80	37	1
DT50011-QZ	7	89	45	1
DT50012-QZ	7.5	95	50	1
DT50013-QZ	8	102	50	1
DT50014-QZ	8.5	102	50	1
DT50015-QZ	9	102	50	1
DT50016-QZ	10	102	50	1
DT50017-QZ	11	102	50	1
DT50018-QZ	12	102	50	1

Cat. No.	Description	Contents
DT50050-QZ	10pc Impact Titanium Drill Bit Set	Bit tip holder, Tinted Safety Glasses
	Metal drill bits	
	Impact Titanium	



EXTREME[®] IMPACT STEP BITS QUICK CHANGE

QUICK CHANGE SHANK
for rapid change of accessory

TITANIUM COATING
For increased wear resistance, corrosion resistance and upto 2 x life (vs black oxide)

OPTIMISED GEOMETRY
Penetrates material faster. Precise drilling without walking. Specially ground shoulder cutters milling exact, circular holes with clean edges



APPLICATIONS

For enlarging drill holes. Suitable for construction steel, ferrous and non-ferrous metals, plastic, and thin-walled materials up to 3mm. For drilling and enlarging holes in metal from 4mm to 34mm.

FOR USE WITH
Impact drivers.

SINGLE PACKS


Cat. No.	Description	Size mm	Pack Qty.
DT5026-QZ	Impact step bit	4-12mm	1
DT5027-QZ	Impact step bit	6-18mm	1
DT5030-QZ	Impact step bit	14-25mm	1
DT5031-QZ	Step Bit	20-34mm	1






Wood

RECOMMENDED MATERIALS



Frame Bit

For fast, accurate and cleanest drill hole results in hard and soft wood, as well as in wet form panels.




Auger Bit

For fast, precise drilling in hard and soft wood and plywood.




Spade Bit

Pilot point and optimised outer cutting edges ensure accurate drill bit positioning, delivering a clean hole. Perfect for drilling large holes in hard, soft, and composite timbers.



Brad Point

High quality chrome vanadium alloyed drill bit with a pilot point, and two outer cutting edges. For fast and accurate holes in hard, soft and construction timbers.



Forstner

For clean and accurate boreholes in hardwood and softwood, wooden boards and more. Self feed pilot point pulls the forstner bit through the timber without the need for downward pressure.



Hinge Hole Cutter

For precise drilling in plywood, and natural hard and soft wood.



BRAD POINT DRILL BITS



FEATURES AND BENEFITS

- High quality chrome-vanadium-alloyed drills with centering point, two shoulders and peripheral cutting edges (Form B).
- Similar to DIN 7487, hardened and ground centric.



APPLICATIONS

For drilling plywood and natural hard and softwood. Particularly suitable for drilling dowel holes and through-holes.



FOR USE WITH

Corded and cordless drills.



SINGLE PACKS

Cat. No.	Ø mm	Total length mm	Working length mm	Pack Qty.
DT4503-QZ	3	70	46	1
DT4504-QZ	4	80	52	1
DT4505-QZ	5	90	60	1
DT4506-QZ	6	100	66	1
DT4507-QZ	7	110	72	1
DT4508-QZ	8	120	80	1
DT4509-QZ	9	130	84	1
DT4510-QZ	10	133	90	1
DT4511-QZ	11	150	100	1
DT4512-QZ	12	155	102	1
DT4513-QZ	13	155	102	1
DT4514-QZ	14	160	107	1
DT4516-QZ	16	165	112	1
DT4518-QZ	18	200	130	1
DT4520-QZ	20	200	130	1

SET

Cat. No.	Description	Ø mm
DT4535-QZ	5 piece set woodspiral drill bits in plastic cassette	4 / 5 / 6 / 8 / 10mm



FRAME DRILL BITS



APPLICATIONS

For fast, accurate and cleanest drill hole results in hardwood, softwood and laminate.



FOR USE WITH

Corded and cordless drills.



SINGLE PACKS

Cat. No.	Ø mm	Total length mm	Pack Qty.
DT4871-QZ	8	600	1
DT4872-QZ	10	600	1
DT4873-QZ	12	600	1
DT4874-QZ	16	600	1
DT4875-QZ	18	600	1
DT4876-QZ	20	600	1
DT4877-QZ	22	600	1



WOOD AUGER DRILL BITS



FEATURES AND BENEFITS

- Cylindrical shank. All other sizes are delivered with hexagonal shaft.
- Spiral groove shape 'LEWIS' allows maximum chip transport and high drilling progress.
- Self-pulling thread for accurate drilling.
- Periferial cutting allows clean holes with minimal spalling.



APPLICATIONS

Special wood drill for fast, precise drilling.

FOR USE WITH

Corded and cordless drills.



SINGLE PACKS

Cat. No.	Ø mm	Total length mm	Working length mm	Pack Qty.
DT4600-QZ	6	200	100	1
DT4602-QZ	8	200	100	1
DT4604-QZ	10	200	100	1
DT4606-QZ	12	200	100	1
DT4608-QZ	14	200	100	1
DT4610-QZ	16	200	100	1
DT4612-QZ	18	200	100	1
DT4614-QZ	20	200	100	1
DT4615-QZ	22	200	100	1
DT4616-QZ	24	200	100	1
DT4618-QZ	26	200	100	1
DT4619-QZ	28	200	100	1
DT4620-QZ	30	200	100	1
DT4621-QZ	32	200	100	1
DT4632-QZ	8	380	280	1
DT4634-QZ	10	380	280	1
DT4636-QZ	12	380	280	1
DT4638-QZ	14	380	280	1
DT4640-QZ	16	380	280	1
DT4642-QZ	18	380	280	1
DT4644-QZ	20	380	280	1
DT4645-QZ	22	380	280	1
DT4646-QZ	24	380	280	1
DT4648-QZ	26	380	280	1
DT4649-QZ	28	380	280	1
DT4650-QZ	30	380	280	1
DT4651-QZ	32	380	280	1

FORSTNER DRILL BITS



FEATURES AND BENEFITS

- Anti slip shank. 3 flat surfaces prevent rotation in the drill chuck and ensure maximum power transmission.
- Threaded pilot point pulls forstner bit through the material
- 2 extra sharp cutting edges for fast drilling.



APPLICATIONS

For rapid drilling of clean and accurate holes in hardwood, softwood, wooden boards and plaster boards.



FOR USE WITH

Corded and cordless drills.



SINGLE PACKS

Cat. No.	Ø mm	Pack Qty.
DT4575-QZ	25	1
DT4576-QZ	28	1
DT4577-QZ	32	1
DT4578-QZ	35	1
DT4579-QZ	38	1
DT4580-QZ	41	1
DT4581-QZ	45	1
DT4582-QZ	51	1
DT4583-QZ	54	1
DT4584-QZ	57	1
DT4585-QZ	65	1
DT4586-QZ	68	1
DT4587-QZ	74	1
DT4588-QZ	76	1
DT4589-QZ	92	1
DT4590-QZ	117	1
DT4592-QZ	Extension piece 140mm	1



EXTREME[®] IMPACT SPADE BITS

STEEL SHANK

Extra thick and robust for outstanding durability. 1/4" shank ensures easy and slip-proof clamping



BEVELLED PILOT DRILL

Bevelled outer cut edges enable precise positioning of the drill and a clean hole pattern, even in wood with nails.



APPLICATIONS

For fast and accurate results in hardwood, softwood, lumber, and wood with nails.



FOR USE WITH

Corded and cordless drills.



SINGLE PACKS

Cat. No.	Ø mm	Total length mm	Pack Qty.
DT4762-QZ	10	152	1
DT4763-QZ	12	152	1
DT4764-QZ	13	152	1
DT4765-QZ	14	152	1
DT4766-QZ	16	152	1
DT4767-QZ	18	152	1
DT4768-QZ	20	152	1
DT4769-QZ	22	152	1
DT4770-QZ	24	152	1
DT4771-QZ	25	152	1
DT4772-QZ	26	152	1
DT4773-QZ	28	152	1
DT4774-QZ	30	152	1
DT4775-QZ	32	152	1
DT4776-QZ	35	152	1
DT4777-QZ	38	152	1
DT4778-QZ	40	152	1

EXTENSION PIECE

Cat. No.	Description	Pack Qty.
DT4849-QZ	300 x 1/4"	1

SINGLE PACKS

Cat. No.	Ø mm	Total length mm	Pack Qty.
DT4780-QZ	10	406	1
DT4781-QZ	12	406	1
DT4783-QZ	14	406	1
DT4784-QZ	16	406	1
DT4785-QZ	20	406	1
DT4786-QZ	22	406	1
DT4787-QZ	24	406	1
DT4788-QZ	25	406	1
DT4789-QZ	26	406	1
DT4791-QZ	30	406	1
DT4792-QZ	32	406	1
DT4793-QZ	35	406	1

SET

Cat. No.	Description	Ø mm
DT7943B-QZ	8 piece set in mini safe with wood milling drills	12 / 16 / 18 / 20 / 22 / 25 / 28 / 32 (152mm)



HINGE BORING DRILL BITS



FEATURES AND BENEFITS

- Anti slip shank. Hexagonal shank for secure fit in drill chuck.
- Centering point and hard metal cutting edge. Enables exact holes for inserting cup hinges.



APPLICATIONS

Suitable for drilling hardboard, plywood, and natural hardwoods and softwoods.



FOR USE WITH

Corded and cordless drills.



SINGLE PACKS

Cat. No.	Ø mm	Total length mm	Pack Qty.
DT4541-QZ	26	65	1
DT4543-QZ	35	65	1

CHUCKS



KEYLESS 10-13mm - SINGLE PACKS

Cat. No.	Material	Shank	Clamping Range mm	1 or 2 Piece	Pack Qty.
DT7002-QZ	Plastic	1/2" x 20 UNF	1.5 - 13	2	1
DT7043-QZ	Metal	1/2" x 20 UNF	1.5 - 13	2	1
DT7044-QZ	Metal	1/2" x 20 UNF	1.5 - 13	2	1
DT7045-QZ	Metal	1/2" x 20 UNF	1.5 - 13	1	1
DT7046-QZ	Metal	1/2" x 20 UNF	1.5 - 13	1	1
DT7025-QZ	Plastic	1/2" x 20 UNF	1.5 - 13	2	1

KEYED 10-13mm - SINGLE PACK

Cat. No.	Shank	Clamping Range mm	Pack Qty.
DT7013-QZ	3/8" x 24 UNF	1.0 - 10	1

CHUCK KEYS



SINGLE PACK

Cat. No.	Shank	Pack Qty.
DT7021-QZ	Drill chuck key	1

SPECIAL CHUCKS AND ADAPTORS



SINGLE PACKS

Cat. No.	Shank	Clamping Range mm	Pack Qty.
DT7005-QZ	1/2" x 20 UNF keyed chuck with SDS adaptor	1.5 - 13	1
DT7030-QZ	SDS-plus® 1/2" x 20 UNF chuck adaptor / screwdriver bit	-	1
DT7018-QZ	2 sleeve metal chuck for 2kg and 4kg quick change hammer drills (eg D25404K)	1.5 - 13	1

MIXER PADDLES



FEATURES AND BENEFITS

- Universal stirring/mixing tool for hand-held drills with a 13mm chuck. Mixing effect from bottom to top.
- Suitable for DW130.
- M14 version also available.

APPLICATIONS

For disperse paints, varnishes, wall paints, wallpaper adhesives, etc.

SINGLE PACKS

Cat. No.	Shank	Ø mm	Total length mm	Pack Qty.
DT4950-QZ	Hexagonal	100	600	1
DT4951-QZ	Hexagonal	120	600	1
DT4952-QZ	M14	120	600	1



INTRODUCTION

The DEWALT® range of hole saws consists of four different types / performance levels:



Standard Bi-Metal This delivers good performance in wood, metal and plastic materials.

EXTREME® Bi-Metal This cuts through all standard materials but also includes features that improve and extend performance and life when used with metal.

EXTREME® Impact Bi-Metal For impact drivers only and used to drill through metal materials.

EXTREME® Carbide Tooth For industrial metal cutting only including stainless steel.

RECOMMENDED MATERIALS



Hole Saws



Carbide

10 X longer life (vs EXTREME® Bi-Metal)
 Carbide teeth for smooth, accurate drilling and clean cuts.
 Depth limiting shoulder prevents teeth cutting too quickly into metal and promotes product life
 Perfect for all metal types
 Single piece design ensures increased stability and durability.

EXTREME® Bi-Metal

Teeth with 8% cobalt content (M42).
 Inclined step-shaped recesses allow easy drill core removal.
 Special tooth geometry provides a strong cutting result and high resistance.

Impact Bi-Metal

Extremely sharp and impact resistant.
 Designed for fast, precise drilling with an impact driver.
 Single piece design ensures increased stability and durability.

Standard Bi-Metal

Aggressive M3 steel teeth.
 Double-tooth design for higher concentricity and additional cutting precision.

EXTREME® CARBIDE HOLE SAWS **NEW**

DURABILITY
10 x longer life (vs EXTREME® Bi-Metal)
Single piece design ensures increased stability and durability.

INTEGRATED MANDREL
Anti slip shank prevents rotation in the chuck and ensures optimum force transmission.

CARBIDE TEETH
Provides smooth, clean cuts and 10 x longer life.

DRILL WITH CENTRE POINT
Easy penetration into all materials; prevents the hole saw walking on base material.

EJECTION SPRING
Quick and easy plug removal.

EXTREME® IMPACT HOLESAWS

ONE-PIECE HOLE SAW
Single piece design ensures increased stability and durability.

OPTIMISED TOOTH GEOMETRY
For fast clean cuts and more holes per charge.

DRILL WITH CENTRE POINT
Prevents walking of the pilot drill bit when starting and allows work without pre-drilling.

EJECTION SPRING
Quick and easy removal of the drill core.

Thin walled design for optimum efficiency in cutting thin materials.

APPLICATIONS
For cutting stainless steel, ferrous and non-ferrous metals.

FOR USE WITH
Corded and cordless drills.



SINGLE PACKS

Cat. No.	Ø mm	Cutting depth mm	Pack Qty.
DT8364-QZ	14	13	1
DT8331-QZ	19	13	1
DT8365-QZ	20	13	1
DT8366-QZ	21	13	1
DT8332-QZ	22	13	1
DT8333-QZ	25	13	1
DT8367-QZ	27	13	1
DT8334-QZ	29	13	1
DT8335-QZ	30	13	1
DT8368-QZ	31	13	1
DT8336-QZ	32	13	1
DT8338-QZ	35	13	1
DT8339-QZ	38	13	1
DT8369-QZ	40	13	1
DT8340-QZ	41	13	1
DT8341-QZ	44	13	1
DT8370-QZ	48	13	1
DT8342-QZ	51	13	1
DT8344-QZ	54	13	1
DT8346-QZ	57	13	1
DT8348-QZ	60	13	1
DT8349-QZ	64	13	1
DT8371-QZ	65	13	1
DT8350-QZ	67	13	1
DT8372-QZ	68	13	1
DT8373-QZ	70	13	1
DT8351-QZ	73	13	1
DT8352-QZ	76	13	1
DT8374-QZ	79	13	1
DT8353-QZ	83	13	1
DT8354-QZ	89	13	1
DT8355-QZ	92	13	1

PILOT DRILL BIT - SINGLE PACK

Cat. No.	Description
DT8362-QZ	Pilot drill bit for carbide hole saws

SET

Cat. No.	Description
DT8360-QZ	4 piece set in mini strong safe. 3 x hole saws Ø22 / 29 / 35mm. 1x pilot drill bit.

APPLICATIONS
Ideal for cutting holes in thin metals, plastics and fibreglass board.

FOR USE WITH
Impact drivers, corded and cordless drills.



SINGLE PACKS

Cat. No.	Ø mm	Cutting depth mm	Pack Qty.
DT8253-QZ	19	20	1
DT8254-QZ	22	20	1
DT8255-QZ	25	20	1
DT8256-QZ	29	20	1
DT8257-QZ	32	20	1
DT8258-QZ	35	20	1
DT8259-QZ	38	20	1





EXTREME[®] HSS BI-METAL

IMPROVES DURABILITY
Hardened tooth design with 8% additional cobalt (M42) provides 2 x life (vs standard Bi-Metal)

TOOTH GEOMETRY
Double tooth design with a combination of shallow and deep shoulders to efficiently remove debris.

THIN WALLED DESIGN
The high quality and thin walled steel body is designed for easier cutting in any material.

EASY PLUG REMOVAL
Angled plug removal slots to make plug ejection easier.



HSS BI-METAL



FEATURES

- Solid construction. The high quality steel body is welded to the base plate for longer durability.
- Thinner design for fast, clean cuts in various materials.
- Hardened tooth design (M3) enables rapid chip ejection and increased working speed.
- Double tooth design with extra deep tooth rack for greater concentricity and cutting precision.

APPLICATIONS

For cutting steel, aluminum, brass, copper, zinc, tin, wood, plasterboard and plastics.

FOR USE WITH

Corded and cordless drills.



SINGLE PACKS

Cat. No.	Diameter mm	Cutting depth mm	Pack Qty.
DT83014-QZ	14	37	1
DT83016-QZ	16	37	1
DT83017-QZ	17	37	1
DT83019-QZ	19	37	1
DT83020-QZ	20	37	1
DT83021-QZ	21	37	1
DT83022-QZ	22	37	1
DT83024-QZ	24	37	1
DT83025-QZ	25	37	1
DT83027-QZ	27	37	1
DT83029-QZ	29	37	1
DT83030-QZ	30	37	1
DT83032-QZ	32	37	1
DT83033-QZ	33	37	1
DT83035-QZ	35	37	1
DT83037-QZ	37	37	1
DT83038-QZ	38	37	1
DT83040-QZ	40	37	1
DT83041-QZ	41	46	1
DT83043-QZ	43	46	1
DT83044-QZ	44	46	1
DT83046-QZ	46	46	1
DT83048-QZ	48	46	1
DT83051-QZ	51	46	1
DT83052-QZ	52	46	1
DT83054-QZ	54	46	1
DT83057-QZ	57	46	1
DT83060-QZ	60	46	1
DT83064-QZ	64	46	1
DT83065-QZ	65	46	1
DT83067-QZ	67	46	1
DT83068-QZ	68	46	1
DT83070-QZ	70	46	1
DT83073-QZ	73	46	1
DT83076-QZ	76	46	1
DT83079-QZ	79	46	1
DT83083-QZ	83	46	1
DT83086-QZ	86	46	1
DT83089-QZ	89	46	1
DT83092-QZ	92	46	1
DT83095-QZ	95	46	1
DT83098-QZ	98	46	1
DT83102-QZ	102	46	1
DT83105-QZ	105	46	1
DT83108-QZ	108	46	1
DT83114-QZ	114	46	1
DT83121-QZ	121	46	1
DT83127-QZ	127	46	1
DT83140-QZ	140	46	1
DT83152-QZ	152	46	1

SETS

Cat. No.	Description	Contents
DT83001-QZ	13 piece multi-purpose hole saw set	9 hole saws Ø16, 19, 25, 32, 38, 44, 48, 51, 64mm 2x mandrel 2x pilot drill in carrying case
DT83002-QZ	11 piece electrician's hole saw set	7 hole saws Ø22, 29, 35, 38, 44, 51, 64mm 2x mandrel 2x pilot drill in carrying case
DT83003-QZ	11 piece electrician's hole saw set	7 hole saws Ø16, 20, 25, 32, 40, 51, 64mm 2x mandrel 2x pilot drill in carrying case
DT83004-QZ	11 piece electrician's hole saw set	7 hole saws Ø20, 25, 32, 35, 44, 51, 64mm 2x mandrel 2x pilot drill in carrying case

SINGLE PACKS

Cat. No.	Ø mm	Cutting depth mm	Pack Qty.
DT8114L-QZ	14	37	1
DT8116L-QZ	16	37	1
DT8117L-QZ	17	37	1
DT8119L-QZ	19	37	1
DT8120L-QZ	20	37	1
DT8121L-QZ	21	37	1
DT8122L-QZ	22	37	1
DT8124L-QZ	24	37	1
DT8125L-QZ	25	37	1
DT8127L-QZ	27	37	1
DT8129L-QZ	29	37	1
DT8130L-QZ	30	37	1
DT8132L-QZ	32	37	1
DT8133L-QZ	33	37	1
DT8135L-QZ	35	37	1
DT8137L-QZ	37	37	1
DT8138L-QZ	38	37	1
DT8140L-QZ	40	37	1
DT8141L-QZ	41	46	1
DT8143L-QZ	43	46	1
DT8144L-QZ	44	46	1
DT8146L-QZ	46	46	1
DT8148L-QZ	48	46	1
DT8151L-QZ	51	46	1
DT8152L-QZ	52	46	1

SINGLE PACKS

Cat. No.	Ø mm	Cutting depth mm	Pack Qty.
DT8154L-QZ	54	46	1
DT8157L-QZ	57	46	1
DT8160L-QZ	60	46	1
DT8164L-QZ	64	46	1
DT8165L-QZ	65	46	1
DT8167L-QZ	67	46	1
DT8168L-QZ	68	46	1
DT8170L-QZ	70	46	1
DT8173L-QZ	73	46	1
DT8176L-QZ	76	46	1
DT8179L-QZ	79	46	1
DT8183L-QZ	83	46	1
DT8186L-QZ	86	46	1
DT8189L-QZ	89	46	1
DT8192L-QZ	92	46	1
DT8195L-QZ	95	46	1
DT8198L-QZ	98	46	1
DT8202L-QZ	102	46	1
DT8205L-QZ	105	46	1
DT8208L-QZ	108	46	1
DT8214L-QZ	114	46	1
DT8221L-QZ	121	46	1
DT8227L-QZ	127	46	1
DT8240L-QZ	140	46	1
DT8252L-QZ	152	46	1

SETS

Cat. No.	Description	Contents
DT8269L-QZ	11 piece set plumbing EXTREME [®] BIM hole saws	7 hole saws Ø19 / 22 / 29 / 38 / 44 / 51 / 57mm 2x adapter 2x pilot drill in carrying case
DT8270L-QZ	11 piece set universal EXTREME [®] BIM hole saws	7 hole saws Ø22 / 29 / 35 / 44 / 51 / 64 / 68mm 2x adapter 2x pilot drill in carrying case
DT8273L-QZ	11 piece set electrician's EXTREME [®] BIM hole saws	7 hole saws Ø16 / 20 / 25 / 32 / 35 / 51 / 64mm 2x adapter 2x pilot drill in carrying case



EXTREME[®] MANDRELS QUICK CHANGE



FEATURES

- Fast, tool free changeovers.
- Quick release collar to prevent hole saw lock up
- Available as single units and in sets

FOR USE WITH

Bi-Metal hole saws



SINGLE PACKS

Cat. No.	Description	Ø Sizes mm
DT8286-QZ	EXTREME [®] Quick Release Mandrel for Hole Saws	Ø14 - 30mm
DT8288-QZ	EXTREME [®] Quick Release Mandrel for Hole Saws	Ø32 - 210mm
DT8101-QZ	EXTREME [®] Quick Release Mandrel for Hole Saws	Ø14 - 30mm from 10mm Drill Chuck
DT8102-QZ	EXTREME [®] Quick Release Mandrel for Hole Saws	Ø32 - 210mm from 13mm Drill Chuck

MANDRELS QUICK CHANGE



FEATURES

- Fast, tool free changeovers.
- Quick release collar to prevent hole saw lock up
- Available as single units and in sets


FOR USE WITH

Bi-Metal hole saws



SINGLE PACKS

Cat. No.	Description	Ø mm
DT8290-QZ	Hole Saws Extension Piece for Standard Quick Release Mandrel DT8102	330mm
DT8108-QZ	SDS-plus [®] Clamping Mandrel	For Hole Saws with Ø32 - 160mm
DT8109-QZ	Replacement Pilot Drill	6.35mm



NEW

EXTREME

Optimised torsion zone, maximising bit life and turning force when used in extreme applications



Contoured area of the bit tip flexes with the torque of the impact driver

Flex optimised to transfer maximum torque through the screw and maximise life



SCREWDRIVER BIT RANGE



Screwdriving



NEW EASY-FIT MODULAR STORAGE SETS
Improved bit holder design for easy access
Compact and versatile for site, workshop and van



EXTREME


FLEX TORQ



DEWALT® EXTREME® FLEXTORQ - FULL FIT BIT HEAD

User Benefits

- Longer bit life
- Eliminates rounded screw heads
- Eliminates wobbles



Better Fit

✓ More Surface Area
Increased Friction
Less Slippage
Less than 4° Movement

Worse Fit

✗ Less Surface Area
Less Friction
Increased Slippage
More than 4° Movement

Developed Through Measuring 3000+ Screws

EXTREME **FLEX TORQ**



PHILLIPS® SCREWDRIVER BIT PACKS

Cat. No.	Size	Total length mm	Pack Qty.
DT7993T-QZ	Ph1	25	5
DT7994T-QZ	Ph2	25	5
DT7995T-QZ	Ph3	25	5
DT7997T-QZ	Ph1	50	5
DT70532T-QZ	Ph2	50	2
DT7998T-QZ	Ph2	50	5
DT7999T-QZ	Ph3	50	5



POZI DRIVE SCREWDRIVER BIT PACKS

Cat. No.	Size	Total length mm	Pack Qty.
DT7386T-QZ	Pz1	25	5
DT7387T-QZ	Pz2	25	5
DT7388T-QZ	Pz3	25	5
DT7390T-QZ	Pz1	50	5
DT70531T-QZ	Pz2	50	2
DT7391T-QZ	Pz2	50	5
DT7392T-QZ	Pz3	50	5



TORX SCREWDRIVER BIT PACKS

Cat. No.	Size	Total length mm	Pack Qty.
DT7379T-QZ	T10	25	5
DT7380T-QZ	T15	25	5
DT7381T-QZ	T20	25	5
DT7382T-QZ	T25	25	5
DT7383T-QZ	T27	25	5
DT7384T-QZ	T30	25	5
DT7373-QZ	T40 non torsion	25	5
DT7393T-QZ	T10	50	5
DT7394T-QZ	T15	50	5
DT70533T-QZ	T20	50	2
DT7395T-QZ	T20	50	5
DT70534T-QZ	T25	50	2
DT7396T-QZ	T25	50	5
DT7397T-QZ	T27	50	5
DT7398T-QZ	T30	50	5
DT7399T-QZ	T40	50	5

EXTREME FLEX TORQ MAGNETIC SCREW LOCK



FEATURES

- The Magnetic Screw Lock™ system holders and sleeves all feature floating ring magnets with 10 x holding power. So you have stability and access for almost any project.
- The Magnetic Screw Lock™ sleeve features a floating ring magnet, so you no longer need a third hand to hold your fastener stable.



SINGLE PACK

Cat. No.	Description	Pack Qty.
DT70547T-QZ	Magnetic sleeve for 50mm EXTREME® FlexTorq screw driver bits	1

APPLICATIONS

For all screwdriving applications. Only suitable for the DeWALT® 50mm EXTREME® FlexTorq screwdriver bit.

FOR USE WITH

Impact drivers, corded and cordless drills.

EXTREME FLEX TORQ



50mm FLEXTORQ BITS WITH MAGNETIC SCREW LOCK ACCESSORY

Cat. No.	Size	Total length mm	Pack Qty.
DT70535T-QZ	Pz2	50	3
DT70536T-QZ	Ph2	50	3
DT70537T-QZ	T20	50	3
DT70538T-QZ	T25	50	3

85mm FLEXTORQ SCREWDRIVER BIT PACKS

Cat. No.	Size	Total length mm	Pack Qty.
DT70566T-QZ	Pz2	85	2
DT70567T-QZ	Ph2	85	2
DT70568T-QZ	T20	85	2
DT70569T-QZ	T25	85	2

85mm FLEXTORQ BITS WITH MAGNETIC SCREW LOCK ACCESSORY

Cat. No.	Size	Total length mm	Pack Qty.
DT70557T-QZ	T20	25	25
DT70558T-QZ	T25	25	25

SMALL BULK STORAGE SETS

Cat. No.	Size	Total length mm	Pack Qty.
DT70555T-QZ	Ph2	25	25
DT70556T-QZ	Pz2	25	25



EXTREME FLEX TORQ



FOR USE WITH

Impact drivers, corded and cordless drills.



SETS

Cat.No.	Description	Pack Qty.
DT70523T-QZ	32 Piece Set EXTREME® FlexTorq bits including magnetic bit holder 25mm: Ph1, 3x Ph2 / Ph3 2x Pz1 / 5x Pz2 / 3x Pz3 2x T10 / 2x T15 / 2x T20 / 2x T25 / T27 / T30 / T40 2x SL6 / SL8 / 2x Pr2.	1
DT70745T-QZ	32 Piece Set EXTREME® FlexTorq bits including magnetic bit holder 25mm: Ph1 / 3x Ph2 / Ph3 2x Pz1 / 5x Pz2 / 3x Pz3 2x T10 / 2x T15 / 2x T20 / 2x T25 / T27 / T30 / T40 2x SL6 / SL8 2x Pr2.	1
DT70563T-QZ	32 Piece Set EXTREME® FlexTorq bits including magnetic bit holder 25mm: Ph1 / 3x Ph2 / Ph3 2x Pz1 / 5x Pz2 / 3x Pz3 2x T10 / 2x T15 / 2x T20 / 2x T25 / T27 / T30 / T40 2x SL6 / SL8 2x Pr2.	1
DT70578T-QZ	32 Piece Set EXTREME® FlexTorq bits including magnetic bit holder 25mm: Ph1 / 3x Ph2 / Ph3 2x Pz1 / 5x Pz2 / 3x Pz3 2x T10 / 2x T15 2x T20 / 2x T25 / T27 / T30 / T40 2x SL6 / SL8 2x Pr2.	1
DT70734T-QZ	32 Piece Set EXTREME® FlexTorq bits including magnetic bit holder 25mm: Ph1 / 3x Ph2 / Ph3 2x Pz1 / 5x Pz2 / 3x Pz3 2x T10 / 2x T15 / 2x T20 / 2x T25 / T27 / T30 / T40 2x SL6 / SL8 2x Pr2.	1

EXTREME RIGHT ANGLE SCREW DRIVER BIT HOLDER



FEATURES

- 1/4" hexagonal shank
- Max. torque: 40 Nm
- Integrated magnet ring holds screw
- Includes 9 EXTREME® FlexTorq bits.

APPLICATIONS

For screwing and drilling in tight spaces and difficult to access areas.

FOR USE WITH

Impact drivers and cordless drills.



SET

Cat. No.	Description	Pack Qty.
DT71517T-QZ	90° Impact right angle attachment with 9 Pcs FlexTorq screwdriver bits EXTREME® FlexTorq bits 25mm: 2x Ph2 3x Pz2 T10 / T15 / T20 / T25	1

STANDARD SCREWDRIVER BITS

FEATURES

- High quality professional screwdriver bits.
- Flexible torsion zone absorbs torque peaks and reduces breakage.
- All bits are provided in sturdy plastic re-useable storage containers.

APPLICATIONS

For all screwdriving applications..

FOR USE WITH

Corded and cordless drills.



STANDARD BITS FOR SLOTTED SCREWS

Cat. No.	Size	Total length mm	Pack Qty.
DT7105-QZ	4.5	25	5
DT7106-QZ	5.5	25	5
DT7107-QZ	6.5	25	5



STANDARD BITS FOR PHILLIPS® CROSS-CUT SCREWS

Cat. No.	Size	Total length mm	Pack Qty.
DT7231-QZ	Ph1	25	5
DT7237-QZ	Ph1	25	20
DT7232-QZ	Ph2	25	5
DT7238-QZ	Ph2	25	20
DT7233-QZ	Ph3	25	5
DT7235-QZ	Ph2 Reduced tip	25	5
DT7245-QZ	Ph1 With extra grip 'ribs'	50	5
DT7246-QZ	Ph2 With extra grip 'ribs'	50	5
DT7204-QZ	Ph2	110	5
DT7236-QZ	Ph2 Reduced Tip	25	20



STANDARD BITS FOR PZ-CROSS-HEAD SCREWS

Cat. No.	Size	Total length mm	Pack Qty.
DT7211-QZ	Pz1	25	5
DT7212-QZ	Pz2	25	5
DT7218-QZ	Pz2	25	20
DT7213-QZ	Pz3	25	5
DT7219-QZ	Pz3	25	20
DT7226-QZ	Pz2	50	5
DT7227-QZ	Pz3	50	5
DT7203-QZ	Pz2	110	5
DT7225-QZ	Pz1 with extra grip 'ribs'	50	5

STANDARD SCREWDRIVER BITS



STANDARD BITS FOR TORX® SCREWS

Cat. No.	Size	Total length mm	Pack Qty.
DT7253-QZ	T10	25	5
DT7254-QZ	T15	25	5
DT7265-QZ	T15	25	20
DT7255-QZ	T20	25	5
DT7266-QZ	T20	25	20
DT7256-QZ	T25	25	5
DT7267-QZ	T25	25	20
DT7257-QZ	T27	25	5
DT7258-QZ	T30	25	5
DT7268-QZ	T30	25	20
DT7259-QZ	T40	25	5
DT7290-QZ	T10	70	5
DT7291-QZ	T15	70	5
DT7292-QZ	T20	70	5
DT7293-QZ	T25	70	5
DT7294-QZ	T27	70	5
DT7295-QZ	T30	70	5
DT7296-QZ	T40	70	5



STANDARD BITS FOR INTERNAL SQUARE-HEAD SCREWS

Cat. No.	Size	Total length mm	Pack Qty.
DT7170-QZ	1	25	5
DT7171-QZ	2	25	5
DT7172-QZ	3	25	5



STANDARD BITS FOR HEXAGONAL SOCKET SCREWS

Cat. No.	Size	Total length mm	Pack Qty.
DT7165-QZ	4	25	5
DT7166-QZ	5	25	5
DT7167-QZ	6	25	5
DT7168-QZ	8	25	5

STANDARD

HIGH PERFORMANCE - 25MM BITS - SLIM POCKET CASE SETS

Cat. No.	Description	Contents
DT7915-QZ	11 Piece Pocket Set	PZ1 / PZ2 / PZ3 PH1 / PH2 / PH3 SL4.5 / SL5.5 SL6.5 / SL8 Magnetic bit tip holder
DT7916-QZ	11 Piece Pocket Set	PZ1 / PZ2 / PZ3 PH1 / PH2 / PH3 T10 / T15 / T20 / T25 Magnetic bit tip holder
DT7917-QZ	11 Piece Pocket Set Torx	T7 / T8 / T9 / T10 T15 / T20 / T25 / T27 / T30 / T40 Magnetic bit tip holder
DT71570-QZ	14 Piece Pocket Set	PH1 / PH2 x2 PZ2 T10 / T15 x2 / T20 x2 / T25 x2 / T30 Magnetic drive guides x2 (compact and longer version)
DT71516-QZ	24 Piece Set	25mm: Pz1 / Pz2 / Pz3 / Ph1 / Ph2 / Ph3 T10 / T15 / T20 / T25 / T30 / T40 Hex 4 / Hex 5 / Hex 6 Nuts: 6 / 7 / 8 / 10 / 11 / 13mm Bit holder / adapter / ratchet
DT70709-QZ	33pc Screw Driving Set	25mm: Ph1 / 4x Ph2 / Ph3 / Pz1 / 6x Pz2 / 3x Pz3 T10 / T15 / T20 / 4x T25 / 2x T30 / T40 / SL5.5 / SL8 / 50mm: Ph2 / Pz2 / T25 Compact magnetic drive guide, Magnetic bit holder
DT7944-QZ	31 pcs. bit set	2x Ph1 / 2x Ph2 / Ph3 / 2x Pz1 / 3x Pz2 / Pz3 SL4.5 / SL5.5 / SL6.5 2x T10 / 2x T15 / 2x T20 / 2x T25 / 2x T30 / 2x T40 Hex 3 / 2x Hex 4 / Hex 5 Quick-change magnetic bit holder
DT7969-QZ	32 pcs. bit set in durable and impact-resistant ToughCase™ with belt clip	Ph1 / 2x Ph2 / Ph3 / Pz1 / 2x Pz2 / Pz3 SI 3 / SI 4 / SI 5 / SI 6.5 Hex3 / Hex4 / Hex5 / Hex6 T10 / T15 / T20 / T25 / T27 / T30 / T40 / TT10 / TT15 / TT20 / TT25 / TT27 / TT30 / TT40



STANDARD



SETS

Cat. No.	Description	Contents
DT71572-QZ	45 Piece bit set in ToughCase™	25mm: 2x Ph1 / 2x Ph2 / 2x Ph3 / 2x Pz2 / 2x Pz3 SL6 / 3x T10 / 3x T15 / 4x T20 / 3x T25 / 3x T30 50mm: Ph1 / 2x Ph2 / 2x Pz1 T10 / T15 / 3x T20 / 2x T25 / 2x T30 Socket wrench: 8 / 10mm / magnetic holder
DT70702-QZ	45 piece screwdriving set	25mm: PH1 x2 / PH2 x2 / PH3 x2 SL6 / SL8 PZ2 x6 / PZ3 x5 T10 x2 / T15 x2 / T25 x2 / T30 x2 50mm: PH1 / PH2 x2 PZ1 / PZ2 x3 T15 / T20 / T25 x2 / T30 x2 85mm: PH2 x2 Socket drivers: 8mm / 10mm Compact magnetic drive guide
DT70704-QZ	53 piece bit set in ToughCase™ including safety goggles	25mm: Ph1 / 2x Ph2 / Pz1 / Pz2 / Pz3 / 6x T10 / 6x T15 / 8x T20 / 8x T25 / 3x T30 / 3x T40 50mm: T20 / T25 Bit holder / adapter 1/4" hexagonal on 1/4" square / adapter 1/4" hexagonal on 3/8" square
DT71515-QZ	67 piece screwdriver and drill bit set in miniature including safety goggles	25mm: Ph1 / Ph3 / 18x Pz2 / 13x Pz3 / Pr2 3x T10 / 4x T15 / 4x T20 / 4x T25 / 4x T30 SL6 / SL8 / SL10 50mm: Ph2 / T20 / 2x Pz2 Magnetic holder / HSS-Co metal drills Ø4.5 / 5 / 5.5 / 6 / 6.5 / 7mm



DRYWALL SCREWDRIVER ACCESSORIES

FEATURES

- High quality replacement bits for the magazine attachment of the DeWALT® dry screwdriver DCF6201



PACKS

Cat. No.	Size	Total length mm	Pack Qty.
DT7205-QZ	Pr2*	153	1
DT7206-QZ	Pr2*	153	5
DT7207-QZ	Pr2*	153	20
DT7520-QZ	Magnetic bit holder for 25mm drywall screw driver bits	1	5

*Comparable to PH2, with a slightly reduced head size



EXTREME[®] IMPACT SOCKET SETS

FOR USE WITH
Impact drivers and cordless drills.



SETS

Cat. No.	Description	Pack Qty.
DT7507-QZ	9 piece Impact wrench socket set 10 / 13 / 15 / 17 / 19 / 22 / 24 / 27mm adapter 1/4" na 1/2"	9
DT7506-QZ	17 piece Impact wrench socket set 6 / 8 / 10 / 11 / 12 / 13 / 14 / 16 / 17 18 / 19 / 20 / 21 / 22 / 24 / 27mm adapter 1/4" na 1/2"	17

1/2" IMPACT SOCKETS

FEATURES

- 6-point convex pattern for increased durability.

FOR USE WITH

Industrial tested and approved on both pneumatic and battery powered impact wrenches.



1/2" IMPACT SOCKET (DEEP) PACKS

Cat. No.	Description / Size mm	Torque Nm.
DT7530-QZ	12mm	264
DT7531-QZ	13mm	264
DT7532-QZ	14mm	367
DT7533-QZ	15mm	441
DT7534-QZ	16mm	529
DT7535-QZ	17mm	618
DT7536-QZ	18mm	705
DT7537-QZ	19mm	735
DT7538-QZ	20mm	741
DT7539-QZ	21mm	741
DT7540-QZ	22mm	741
DT7541-QZ	24mm	741

EXTREME[®] IMPACT WRENCH ADAPTERS

APPLICATIONS

For all screwdriving applications.



SINGLE PACKS

Cat. No.	Description	Pack Qty.
DT7508-QZ	1/4" hex to 1/2" square Impact wrench adapter	1
DT7512-QZ	1/4" hex to 1/2" square Impact driver adapter	1



EXTREME[®] HEXAGONAL MAGNETIC SOCKET DRIVERS

FEATURES

- Magnetic socket drive

FOR USE WITH

Impact drivers and cordless drills.



SINGLE PACKS

Cat. No.	Description	Size mm	Total length mm	Pack Qty.
DT7430-QZ	Magnetic nut/socket driver	8	75	1
DT7440-QZ	Magnetic nut/socket driver	10	75	1
DT7450-QZ	Magnetic nut/socket driver	13	75	1
DT7460-QZ	Magnetic nut/socket driver	8 / 10 / 13	75	1



1/4" HEXAGON MAGNETIC SOCKET DRIVERS

FEATURES

- Easy clean permanent magnet

FOR USE WITH

Corded and cordless drills.



SINGLE PACKS

Cat. No.	Description	Size mm	Total length mm	Pack Qty.
DT7401-QZ	Magnetic nut/socket driver	7	50	1
DT7402-QZ	Magnetic nut/socket driver	8	50	1
DT7403-QZ	Magnetic nut/socket driver	10	50	1
DT7423-QZ	Magnetic nut/socket driver	11	50	1
DT7404-QZ	Magnetic nut/socket driver	13	50	1





EXTREME® IMPACT CLUTCH BIT HOLDER

APPLICATION
For use in metal to metal application where torque levels are high. Also used where the drill driver does not have its own safety clutch.

FOR USE WITH
Impact drivers, corded and cordless drills.

SETS


Cat. No.	Description	Pack Qty.
DT7513T-QZ	Magnetic hard joint Impact clutch inc. PH2 25mm EXTREME® FlexTorq bit tripping torque 5.5 Nm	1



SCREWDRIVER BIT HOLDERS

FOR USE WITH
Corded and cordless drills.

Cat. No.	Description	Total length mm	Pack Qty.
DT7501-QZ	Non-magnetic bit holder	57	1
DT7500-QZ	Magnetic bit holder	60	1
DT7511-QZ	Magnetic quick change bit holder holder	60	1
DT7515-QZ	ClicFix magnetic quick change bit holder	60	1
DT7516-QZ	Rapid load magnetic quick change bit holder	60	1
DT7521-QZ	Drywall bit holder and depth setter inc. PH2 25mm	75	2
DT7701-QZ	Magnetic bit holder with drive guide sleeve	80	1
DT7702-QZ	Magnetic bit holder with drive guide sleeve	120	1
DT7505-QZ	EXTREME® Impact pivoting bit tip holder inc. PZ2 25mm	87	2



FLIP 'N' DRIVE QUICK CHANGE SYSTEM

FEATURES

- Complete drill drive accessory system for drilling countersink and pilot holes in one action and screwdriving.
- One-handed connector release with push forward collar for easily changing between drilling and screwdriving applications.
- 5/16" (8mm) shank for added durability.

APPLICATIONS

For use in hard and soft wood, composite board and MDF.

Ideal for cabinet making, furniture assembly, remodelling and shop fitting.

FOR USE WITH

Corded and cordless drills.



QUICK-EXCHANGE UNITS

Cat. No.	Description	Size	Pack Qty.
DT7600-XJ	Connector, countersink, pilot drill bit (2.38mm) and PZ2 screw driver bit	No 6	1
DT7601-XJ	Connector, countersink, pilot drill bit (2.77mm) and PZ2 screw driver bit	No 8	1
DT7602-XJ	Connector, countersink, pilot drill bit (3.17mm) and PZ2 screw driver bit	No 10	1
DT7603-XJ	Connector, countersink, pilot drill bit (3.17mm) and PZ2 screw driver bit	No 12	1

HSS PILOT DRILL


Cat. No.	Description	Size	Pack Qty.
DT7608-XJ	Pilot drill bit (2.38mm) for 3mm screws	No 6	3
DT7609-XJ	Pilot drill bit (2.77mm) for 4mm screws	No 8	3
DT7610-XJ	Pilot drill bit (3.17mm) for 5mm screws	No 10	3

PILOT DRILL WITH COUNTERSINK

Cat. No.	Description	Size	Pack Qty.
DT7604-XJ	Pilot drill bit (2.38mm) with countersink for 3mm screws	No 6	1
DT7605-XJ	Pilot drill bit (2.77mm) with countersink for 4mm screws	No 8	1
DT7606-XJ	Pilot drill bit (3.17mm) with countersink for 5mm screws	No 10	1
DT7607-XJ	Pilot drill bit (3.17mm) with countersink for 6mm screws	No 12	1

QUICK-CHANGE SET

Cat. No.	Description	Size	Pack Qty.
DT7612-XJ	Countersink pilot bit set	No. 6, 8, 10, 12 PZ2 25mm x2 PH2 25mm x2	10



MAGBOXES



FEATURES

- Compact design for easy storage and portability
- High impact materials for optimum durability
- High strength magnets and built in hooks for increased functionality
- Versatile magnetic storage box in a practical design.

APPLICATIONS

Flexible storage solution fits most common accessories



EXTREME® IMPACT TORSION SETS


Cat. No.	Description
DT7919-QZ	20 Piece Set in Magnetic Box 25mm: PH1 / PH2 / PH3 / PZ1 / PZ2 x2 / PZ3 / T20 / T25. 50mm: PH3. EXTREME® Impact Hex Shank Metal Drill Bits: 3 / 4mm. Socket Drivers: 7 / 8 / 10mm Magnetic Bit Tip Holder

HIGH PERFORMANCE

Cat. No.	Description
DT7918-QZ	15 piece set in magnetic box 25mm: Ph1 / Ph2 / Ph3 / Pz1 / 2x Pz2 / Pz3 T20 / T25 50mm: Ph2 / Pz2 Socket drivers: 7 / 8 / 10mm Magnetic bit tip holder



RECOMMENDED MATERIALS




Circular Saw Blades



For cutting premium timbers in a workshop environment where bespoke woodworking is performed.



Optimised for cordless circular saws and stationary saws for first and second fix applications. Delivering maximum productivity from the power available. Also compatible with corded saws where specifications match.



For decorative wooden sections where cut finish is the highest priority



For rough cutting and first fix applications where durability is more important than cut finish.




A range of saw blades for cutting aluminium, steel and stainless steel.



A range of poly-crystalline diamond toothed saw blades for cutting multi materials including fibre cement.

EXTREME[®] CIRCULAR SAW BLADES
WORKSHOP



- C4 PREMIUM CARBIDE**
For extended life and up to 5 regrinds
- LASER CUT PLATE**
For improved balance
- RIM EXPANSION SLOTS**
Eliminate rim flex and maintain alignment
- HARMONIC SLOTS**
No blade ringing or scoring
- ULTRA-SHARP CARBIDE TEETH**
Reduces tear out
- OPTIMISED GRIND ANGLES**
Reduces tear out



• Designed for stationary saws - the first choice for professional workshop operation.



• The hallmark EXTREME[®] circular saw blades for stationary saws.



• Specially designed to achieve precise cutting and a high quality finish in for use in wood, coated and uncoated wood materials and plastic.



FLAT TOP GRIND (FT)

Tooth geometry, in which the cutting edge of the tooth is ground straight and without any inclination. This tooth form is used for longitudinal cuts and for universal applications if high cutting quality is less important.

TRIPLE CHIP GRIND (TCG)

Tooth geometry, in which a flat tooth is alternately arranged, followed by a slightly higher trapezoidal ground tooth. This higher tooth cuts correspondingly deeper, however, due to its upper edges which are chamfered on both sides, but somewhat narrower than the following flat tooth. This makes the splitting of brittle materials, e.g. laminate is prevented.

ALTERNATE TOP BEVEL (ATB)

Tooth geometry, in which the cutting edges of the teeth are alternately obliquely ground, the angle being from 10° to 20°. For universal use but ideal for cross cuts in hardwood and softwood.

HOLLOW GROUND (HG)

Tooth geometry, in which the teeth have been ground to a concave profile that produces clean cuts in melamine and other coated boards, without the need for scoring.

EXTREME[®] CIRCULAR SAW BLADES
WORKSHOP



SINGLE PACKS - PORTABLE

Cat. No.	Diameter mm	Arbor Diameter mm	Tooth Count	Grind Geometry	Hook Angle	KERF mm	Plate Thickness mm	Harmonic Slots
DT4057-QZ	160	20	36	ATB	10°	2.6	1.8	No
DT4084-QZ	160	20	48	TCG	-5°	2.6	1.8	No
DT1089-QZ	165	20	18	FT	18°	2.3	1.6	No
DT4026-QZ	165	20	24	ATB	25°	2.6	1.8	No
DT4027-QZ	165	30	24	ATB	25°	2.6	1.8	No
DT1091-QZ	165	20	40	ATB	-5°	1.9	1.4	No
DT1090-QZ	165	20	48	ATB	5°	2.2	1.6	No
DT1086-QZ	165	20	48	TCG	5°	2.3	1.6	No
DT4087-QZ	165	20	48	TCG	-5°	2.6	1.8	No
DT4088-QZ	165	30	48	TCG	-5°	2.6	1.8	No
DT1087-QZ	165	20	54	MTCG	0°	2.3	1.6	No
DT1088-QZ	165	20	54	TCG	-5°	2.3	1.6	No
DT4031-QZ	184	16	28	ATB	25°	2.6	1.8	No
DT4063-QZ	184	16	40	ATB	10°	2.6	1.4	No
DT4092-QZ	184	16	48	TCG	-5°	2.6	1.8	No
DT4033-QZ	190	30	28	ATB	10°	2.6	1.8	No
DT4064-QZ	190	30	40	ATB	10°	2.6	1.8	No
DT4094-QZ	190	30	48	TCG	-5°	2.6	1.8	No
DT4036-QZ	235	30	28	ATB	25°	3.2	2.2	No
DT4067-QZ	235	30	40	ATB	10°	3.2	2.2	No
DT4097-QZ	235	30	56	TCG	-5°	3.2	2.2	No

SINGLE PACKS - STATIONARY

Cat. No.	Diameter mm	Arbor Diameter mm	Tooth Count	Grind Geometry	Hook Angle	KERF mm	Plate Thickness mm	Harmonic Slots
DT4310-QZ ♦	216	30	24	ATB	-5°	2.6	1.8	Yes
DT4320-QZ ♦	216	30	48	ATB	-5°	2.6	1.8	Yes
DT4350-QZ ♦	216	30	60	ATB	-5°	2.6	1.8	Yes
DT4370-QZ ♦	216	30	60	TCG	-5°	2.6	1.8	Yes
DT4286-QZ	216	30	80	TCG	-5°	2.6	1.8	No
DT4202-QZ	250	30	24	FT	10°	2.8	1.8	No
DT4301-QZ	250	30	24	FT	10°	3.0	2.2	Yes
DT4311-QZ ♦	250	30	24	FT	10°	3.0	2.2	Yes
DT4321-QZ ♦	250	30	30	ATB	10°	3.0	2.2	Yes
DT4226-QZ	250	30	30	ATB	20°	3.0	2.2	No
DT4322-QZ	250	30	40	ATB	20°	3.0	2.2	Yes
DT4323-QZ	250	30	48	ATB	20°	3.0	2.2	Yes
DT4345-QZ	250	30	50	HG	10°	3.2	2.5	Yes
DT4351-QZ ♦	250	30	60	ATB	10°	3.0	2.2	Yes
DT4217-QZ	250	30	60	HG	10°	3.2	2.5	Yes
DT4352-QZ ♦	250	30	60	TCG	-5°	3.0	2.2	Yes
DT4353-QZ ♦	250	30	80	ATB	10°	3.0	2.2	Yes
DT4287-QZ	250	30	80	TCG	-5°	3.0	2.2	No
DT4282-QZ	250	30	96	TCG	-5°	3.0	2.2	No
DT4324-QZ ♦	260	30	48	ATB	10°	2.6	1.8	Yes
DT4280-QZ	260	30	80	TCG	-5°	2.6	1.8	No
DT4281-QZ	300	30	80	TCG	-5°	3.0	2.2	No
DT4210-QZ	305	30	32	ATB	-5°	2.6	1.8	No
DT4330-QZ ♦	305	30	36	ATB	-5°	3.0	2.2	Yes
DT4340-QZ ♦	305	30	48	ATB	10°	3.0	2.2	Yes
DT4260-QZ	305	30	60	ATB	-5°	2.6	1.8	No
DT4331-QZ	305	30	60	ATB	-5°	3.0	2.2	Yes
DT4346-QZ	305	30	60	HG	10°	3.2	2.5	Yes
DT4218-QZ	305	30	72	HG	10°	3.2	2.5	Yes
DT4283-QZ	305	30	80	TCG	-5°	2.6	1.8	No
DT4288-QZ	305	30	80	TCG	-5°	3.0	2.2	No
DT4290-QZ	305	30	96	TCG	-5°	3.0	2.2	No
DT4332-QZ ♦	315	30	48	ATB	10°	3.0	2.2	Yes
DT4305-QZ	350	30	36	FT	10°	3.0	2.2	Yes
DT4291-QZ	350	30	96	TCG	-5°	3.0	2.2	No
DT4317-QZ ♦	400	30	36	ATB	10°	3.0	2.4	Yes
DT4338-QZ	400	30	60	ATB	10°	3.0	2.4	Yes

♦ Marked saw blades have laser lines for vibration and sound insulation or corrosion-protected teeth


EXTREME® CIRCULAR SAW BLADES



- C3 NEXT GENERATION CARBIDE**
Up to 3 regrinds & 2x life (vs Construction range)
- RESIN FILLED EXPANSION SLOTS**
Dampen noise and vibration
- THIN KERF**
Ideal for cordless and less push force required
- FULL KERF**
Minimises blade deflection for a straighter cut
- ULTRA-SHARP CARBIDE TEETH**
Reduces tear out
- OPTIMISED GRIND ANGLES**
Reduces tear out



FOR USE WITH
Portable and stationary circular saws



SINGLE PACKS

Cat. No.	Blade Ø mm	Bore Ø mm	Blade thickness mm	Kerf thickness mm	Kerf Type	No of teeth	Tooth Direction	Tooth Geometry	Tooth angle	N MAX RPM
DT10300-QZ	165	20	0.99	1.65	Thin	24	Anti-clockwise	ATB	18	7000
DT10301-QZ	165	20	0.99	1.65	Thin	40	Anti-clockwise	ATB	18	7000
DT10302-QZ	184	16	0.99	1.65	Thin	24	Anti-clockwise	ATB	18	7000
DT10303-QZ	184	16	0.99	1.65	Thin	40	Anti-clockwise	ATB	18	7000
DT10304-QZ	190	30	0.99	1.65	Thin	24	Anti-clockwise	ATB	18	7000
DT10624-QZ	165	20	0.99	1.65	Thin	24	Clockwise	ATB	18	7000
DT10640-QZ	165	20	0.99	1.65	Thin	40	Clockwise	ATB	18	7000
DT1669-QZ	184	16	0.99	1.65	Thin	24	Clockwise	ATB	7	7000
DT1668-QZ	184	16	0.99	1.65	Thin	40	Clockwise	ATB	7	7000
DT1670-QZ	184	30	0.99	1.65	Thin	24	Clockwise	ATB	7	7000
DT1655-QZ	216	30	1.6	2.35	Thin	60	Clockwise	ATB	7	7000
DT1042-QZ	305	30	2	2.75	Thin	60	Clockwise	ATB	7	4800

SETS

Cat. No.	Description	Blade Ø mm	Bore Ø mm	Blade thickness mm	Kerf thickness mm	Kerf Type	No of teeth	Tooth Direction	Tooth Geometry	Tooth angle	N MAX RPM
DT10397-QZ	2 x (165 x 20 x 24T) 1 x (165 x 20 x 40T)	165	20	0.99	1.65	Thin	24, 40	Anti-clockwise	ATB	18	7000
DT10399-QZ	3 x 190 24T Corded	190	30	0.99	1.65	Thin	24	Anti-clockwise	ATB	18	7000

XR EXTREME RUNTIME® CIRCULAR SAW BLADES



- OPTIMISED FOR CORDLESS**
Up to 2x more cuts per charge and ideal for FlexVolt tools
- C3 NEXT GENERATION CARBIDE**
Up to 3 regrinds
- THIN KERF**
Ideal for cordless and less push force required
- FULL KERF**
Minimises blade deflection for a straighter cut
- EXPANSION SLOTS**
Dampen noise and vibration
- PATENTED GRIND ANGLES**
For faster cuts with lower force



FOR USE WITH
XR FlexVolt range and all compatible corded and cordless circular saws, mitre saws and table saws.



SINGLE PACKS

Cat. No.	Blade Ø mm	Bore Ø mm	Blade thickness mm	Kerf thickness mm	Kerf Type	No of Teeth	Tooth Direction	Tooth Geometry	Tooth Angle	N MAX RPM
DT99560-QZ	165	20	1.2	1.76	Thin	24	Anti-clockwise	ATB+R	10°	7000
DT99561-QZ	165	20	1.2	1.76	Thin	42	Anti-clockwise	ATB+R	10°	7000
DT99577-QZ	184	20	0.82	1.55	Thin	24	Anti-clockwise	ATB+R	25°	7000
DT99578-QZ	184	20	0.82	1.55	Thin	36	Anti-clockwise	ATB+R	25°	7000
DT99579-QZ	184	20	0.82	1.55	Thin	60	Anti-clockwise	ATB+R	25°	7000
DT99562-QZ	190	30	0.82	1.55	Thin	24	Anti-clockwise	ATB+R	25°	7000
DT99563-QZ	190	30	0.82	1.55	Thin	36	Anti-clockwise	ATB+R	25°	7000
DT99564-QZ	190	30	0.82	1.55	Thin	60	Anti-clockwise	ATB+R	25°	7000
DT99565-QZ	210	30	1.24	1.8	Thin	24	Clockwise	ATB+R	20°	7000
DT99566-QZ	210	30	1.24	1.8	Thin	36	Clockwise	ATB+R	20°	7000
DT99567-QZ	210	30	1.24	1.8	Thin	60	Clockwise	ATB+R	20°	7000
DT99568-QZ	216	30	1.6	2.16	Thin	24	Clockwise	ATB+R	7°	7000
DT99569-QZ	216	30	1.6	2.16	Thin	36	Clockwise	ATB+R	7°	7000
DT99570-QZ	216	30	1.6	2.16	Thin	60	Clockwise	ATB+R	7°	7000
DT99571-QZ	250	30	1.6	2.16	Thin	24	Clockwise	ATB+R	7°	6000
DT99572-QZ	250	30	1.6	2.16	Thin	36	Clockwise	ATB+R	7°	6000
DT99573-QZ	250	30	1.6	2.16	Thin	60	Clockwise	ATB+R	7°	6000
DT99574-QZ	305	30	1.6	2.16	Thin	42	Clockwise	ATB+R	7°	4800
DT99575-QZ	305	30	1.6	2.16	Thin	60	Clockwise	ATB+R	7°	4800
DT99576-QZ	305	30	1.6	2.16	Thin	78	Clockwise	ATB+R	7°	4800
DT99595-QZ	305	25.4	1.6	2.16	Thin	60	Clockwise	ATB+R	7°	4800
DT99596-QZ	305	25.4	1.6	2.16	Thin	78	Clockwise	ATB+R	7°	4800



MULTI MATERIAL CUTTING BLADES

NEW



ANTI-VIBRATION SLOTS
Improves cut finish and reduces resonance

APPLICATIONS

- A multi material blade designed to cut through abrasive materials such as fibre cement or laminate.
- Perfect for cutting through cement fibre board and other dense composite panels.
- In addition this blade performs extremely well on dozens of other applications including: laminated and melamine surfaces, soft and hardwoods, MDF, plywood and chipboard.

FOR USE WITH

Compatible with stationary and portable circular saws.

MULTI MATERIAL - SINGLE PACKS

Cat. No.	Ø Blade mm	Ø Bore mm	Blade thickness mm	Kerf thickness mm	Kerf Type	No of teeth	Tooth Direction	Tooth Geometry	Tooth angle	N MAX RPM
DT1470-QZ	160	20	1.4	1.8	Full	4	Anti-clockwise	FTG	12°	7000
DT1471-QZ	165	20	1.4	1.8	Full	4	Anti-clockwise	FTG	12°	7000
DT1472-QZ	190	30	1.4	1.8	Full	4	Anti-clockwise	FTG	12°	7000
DT1473-QZ	216	30	1.5	2.0	Full	8	Clockwise	FTG	12°	7000
DT1474-QZ	250	30	1.6	2.2	Full	12	Clockwise	FTG	12°	6000
DT1475-QZ	305	30	1.8	2.4	Full	16	Clockwise	FTG	12°	4800



BISCUIT JOINTER BLADES

FOR USE WITH

Jointers.

SINGLE PACKS

Cat. No.	Description	Diameter mm	Thickness mm	Bore mm	No of teeth
DT1306-QZ	Straight cutters for DW682K / DW685K	102	4	22	12
DT1307-QZ	Straight cutters for DW685K	105	2	22	30



METAL BLADES



FEATURES

Steel Cutting

- Crafted with 12% titanium carbide, DeWALT® Metal Cutting™ saw blades tackle tough steel cutting applications with ease.
- Modified ATB tooth geometry provides clean, burr-free cuts, and expansion slots dissipate heat, extending blade life. A tri-foil braze boosts the strength of each tooth tip for extreme durability.



Stainless Steel (Inox) Cutting

- Designed to power through stainless steel with ease, DeWALT® stainless steel Metal Cutting™ saw blades are crafted from carbide for long life and less chipping. Each blade is laser-etched and color-coded by material.



Aluminium Cutting

- Backed by an ultra-thin kerf blade for fast cutting and helps to increased battery life, DeWALT® Metal Cutting™ saw blades are built to power through aluminum and non-ferrous metals, including brass and copper.
- Heavy-duty tungsten carbide tips maintain a sharp edge for long life, and an anti-stick rim helps to reduce friction and gum-up.



STEEL - SINGLE PACKS

Cat. No.	Blade Ø mm	Bore Ø mm	Blade thickness mm	Kerf thickness mm	Kerf Type	No of teeth	Tooth Direction	Tooth Geometry	Tooth Angle	N MAX RPM
DT1923-QZ	140	20	1.13	1.0	Full	30	Clockwise	TCG	1.5°	4200
DT1926-QZ	355	25.4	1.95	2.31	Full	66	Clockwise	TCG	1.5°	1800
DT1927-QZ	355	25.4	1.95	2.31	Full	90	Clockwise	TCG	1.5°	1800


STAINLESS STEEL (INOX) - SINGLE PACKS

Cat. No.	Blade Ø mm	Bore Ø mm	Blade thickness mm	Kerf thickness mm	Kerf Type	No of teeth	Tooth Direction	Tooth Geometry	Tooth Angle	N MAX RPM
DT1918-QZ	140	20	1.13	1.53	Full	40	Clockwise	MTCG+R	10°	4200
DT1921-QZ	355	25.4	1.75	2.15	Full	70	Anti-clockwise	MTCG+R	10°	1800
DT1922-QZ	355	25.4	1.75	2.15	Full	90	Anti-clockwise	MTCG+R	10°	1800

ALUMINIUM - SINGLE PACKS

Cat. No.	Blade Ø mm	Bore Ø mm	Blade thickness mm	Kerf thickness mm	Kerf Type	No of teeth	Tooth Direction	Tooth Geometry	Tooth Angle	N MAX RPM
DT1910-QZ	140	20	0.99	1.49	Full	30	Clockwise	FTG	3°	7000
DT1911-QZ	165	20	0.99	1.49	Full	36	Clockwise	FTG	3°	7000
DT1912-QZ	190	30	1.6	2.1	Full	48	Anti-clockwise	TCG	-5°	7000
DT1913-QZ	235	30	1.6	2.1	Full	48	Anti-clockwise	TCG	-5°	6000
DT1914-QZ	216	30	1.8	2.6	Full	48	Clockwise	TCG	-5°	6000
DT1915-QZ	250	30	2.2	3.2	Full	60	Clockwise	TCG	-5°	6000
DT1916-QZ	305	30	2.5	3.2	Full	80	Clockwise	TCG	-5°	4800
DT1917-QZ	355	25.4	2.5	3.2	Full	100	Anti-clockwise	TCG	-5°	4800

RECOMMENDED MATERIALS



Jigsaw Blades



For increased cut control, burr free cutting, faster cutting, long life and durability.



For increased durability and performance.




CROSSED TEETH
For rough and fast cuts in hard and soft wood, plastic and aluminum.



WAVY TEETH
For fine and clean cuts in hardwood and softwood, aluminum, non-ferrous metals and plastics.



INCLINED SHARPENED, CROSSED TEETH
For fast cuts in hardwood and softwood.



STRAIGHT TEETH
For clean cuts in all wood and plastic.

EXTREME JIGSAW BLADES
PRECISION CUT

PATENTED PLUNGE POINT TIP
Specially developed hardened, aggressive front teeth enable improved, low kick-back penetration with easier chip removal, when plunge cutting



PREMIUM STEEL
For maximum durability and accessory life, reinforced blade body for the best control and precision.

CONICAL BLADE BODY
Better control and clean cutting profile with no burning of work pieces, even in narrow curve cuts

TOOTH SPACING AND GEOMETRY
Extremely sharp teeth and extra tooth depth for improved chip removal. Reduced slippage and increased cutting speed. Improved control and extended performance life.



FOR USE WITH
Jigsaws (corded and cordless).



PACKS

Cat. No.	Blade Material	Application	Total length mm	Working length mm	Teeth pitch mm	Max. cutting depth mm	Bosch Cat. No.	Pack Qty.
DT2205-QZ	HCS	Clean, precise and fast cuts in wood, plywood and joiner plates, laminates as well as plastic up to 30mm thick.	100	75	2.5	30	T101B	5
DT2207-QZ	HCS	Extremely clean, burr-free cuts in laminates and hardwood up to 40mm thick.	100	75	2.5	40	T101BR	5
DT2209-QZ	HCS	Extremely long durability (impact toothing). Clean, precise and fast cuts in wood, plywood and furniture boards, laminates and plastics to 60mm thick.	100	75	4.2	60	T101D	5
DT2210-QZ	HCS	Clean, fast accurate cutting in wood, chipboard, plywood, laminates and plastic up to 60mm thick.	100	75	4.2	60	T101D	20
DT2211-QZ	HCS	Simple, precise cuts in wood, plywood, blockboard, laminates and plastic up to 60mm thick.	100	75	3.1	60	T111C	5
DT2212-QZ	HCS	Coarse, accurate cutting in wood, chipboard, plywood, laminates and plastic up to 60mm thick.	100	75	3.1	60	T111C	20
DT2213-QZ	HCS	Fast, precise cuts in wood, plywood, blockboard, laminates and plastic up to 60mm thick.	100	75	4.2	60	T144D	5
DT2214-QZ	HCS	Fast, accurate cutting in wood, chipboard, plywood, laminates and plastic up to 60mm thick.	100	75	4.2	60	T144D	20
DT2216-QZ	HCS	Precise, clean and fast curve cuts in wood, plywood and blockboards, laminates up to 15mm strength and NOT suitable for plunge cuts.	82	54	2	15	T119B0	5
DT2217-QZ	BIM	Clean, fast and precise cuts in hard woods, plywood and blockboards, laminates and plastics up to 30mm thick. Extremely long durability.	100	75	2.5	30	T101BF	3
DT2218-QZ	BIM	Clean, fast and precise cuts in hard woods, plywood and blockboards, laminates and plastics up to 60mm thick. Extremely long durability.	100	75	4	60	T101DF	3
DT2219-QZ	BIM	Extremely clean, burr-free cuts in laminates and hardwood up to 40mm thick. Extremely long durability (impact toothing).	100	75	2.5	40	T101BRF	3
DT2220-QZ	BIM	Fast, precise cuts in hard woods, plywood and furniture boards, laminates and plastics to 60mm thickness. Extremely long durability.	100	75	4	60	T144DF	3
DT2221-QZ	BIM	Extra long life. For fast accurate cutting in aluminium up to 15mm and plastics up to 30mm	100	75	3	30	T127DF	3

SETS

Cat. No.	Description	Contents
DT2296-QZ	10 piece set	DT2209 x2 / DT2205 x2 / DT2213 x2 / DT2216 x1 / DT2218 x1 / DT2217 x1 / DT2220 x1
DT2298-QZ	14 piece set	DT2209 x4 / DT2205 x4 / DT2213 x2 / DT2216 x1 / DT2218 x1 / DT2217 x1 / DT2220 x1

EXTREME BI-METAL FOR METAL



FEATURES

- EXTREME® bi-metal jaw saw blades offer an extended durability in non-ferrous and ferro-alloyed metals.
- Coolant lubricant recommended: cutting oil, emulsion, lubricant / cooling grease (for aluminum, mild steel).

FOR USE WITH

Jigsaws (corded and cordless).



PACKS

Cat. No.	Application	Total length mm	Working length mm	Teeth pitch mm	Max. cutting depth mm	Bosch Cat. No.	Pack Qty.
DT2150-QZ	Quick cuts in steel up to 3mm, also in aluminum, copper, brass and others non-ferrous metals up to 3mm thickness	86	61	1	3	T118AF	3
DT2154-QZ	Fast cuts in steel up to 6mm, also in aluminum, copper, brass and others non-ferrous metals up to 5mm thickness	76	51	1.8	6	T118BF	3
DT2156-QZ	Fast cuts in sheet metal up to 2.5mm	76	51	0.8	2.5	T118GF	3
DT2054-QZ	Curved cuts in metal and thin steel plate	82	55	1.5	4	T1180F	5



EXTREME BI-METAL FOR WOOD AND METAL



FOR USE WITH

Jigsaws (corded and cordless).



PACKS

Cat. No.	Application	Total length mm	Working length mm	Teeth pitch mm	Max. cutting depth mm	Bosch Cat. No.	Pack Qty.
DT2059-QZ	For applications in wood up to 65mm thick as well as metal pipes and profiles of 3-10mm thick. Particularly suitable for cuts with varying material thickness (pull).	132	101	2.4 - 5	Wood 65, metal 10	T345XF	5





EXTREME[®] SPECIALIST JIGSAW BLADES





FOR USE WITH
Jigsaws (corded and cordless).



PACKS

Cat. No.	Application	Total length mm	Working length mm	Teeth pitch mm	Max. cutting depth mm	Bosch Cat. No.	Pack Qty.
DT2055-QZ	Tungsten carbide tipped blade (TCT) for stainless steel sheet metal (Inox) from 1.5-5mm thick.	82	55	1.4	5	T118EHM	1
DT2080-QZ	Clean, straight cuts in all laminates up to 15mm thickness.	82	59	1.7	15	T101BIF	5
DT2081-QZ	Clean curves in all laminates up to 15mm thick.	82	59	1.4	15	T101AOF	3
DT2101-QZ	Stitch saw blade with HM cutting edge for cuts in stainless steel (INOX) and structural steel 1.2-3 mm.	76	47	1	3	T118AHM	1
DT2102-QZ	Tungsten carbide grit blade for ceramic tiles, fibreglass and reinforced plastic up to 10mm thick.	76	50		10	T130RF	1
DT2056-QZ	Carbide-tipped teeth for cuts in GRP and the like. Plastics up to 65mm, plaster as well as cement-bound board materials (up to 80mm).	132	100	4.3	65	T341HM	1
DT2103-QZ	Carbide-tipped teeth for cuts in GRP, such as plastics up to 20mm as well as in cement-bonded board materials.	100	69	4.3	20	T141HM	1
DT2201-QZ	Knife blade for soft materials, rubber, foam & polystyrene up to 100mm thick.	152	125		100	T313AW	5
DT2084-QZ	Straight and curved sections in sandwich materials up to 120mm and medium-strength steel plates.	180	148	2	120	T718BF	5

HSS BLADES FOR METAL




FEATURES

- HSS jigsaw blades offer high durability and best cutting results in steel and non-ferrous metals
- Consisting of fully hardened, high-speed cut-to-length steel (HSS)
- Coolant lubricant: cutting oil, emulsion, lubricating / cooling grease (for aluminum, mild steel).

FOR USE WITH

Jigsaws (corded and cordless).



PACKS

Cat. No.	Application	Total length mm	Working length mm	Teeth pitch mm	Max. cutting depth mm	Bosch Cat. No.	Pack Qty.
DT2160-QZ	Straight cuts in steel sheet and non-ferrous metals	76	50	1.2	4	T118A	5
DT2161-QZ	Straight cuts in solid material (Steel and non-ferrous metals)	76	50	2	6	T118B	5
DT2162-QZ	Straight cuts in very thin steel plate and non-ferrous metals	76	50	0.7	2	T118G	5
DT2085-QZ	Straight cuts in thin steel sheet, non-ferrous metals 1.5-3mm and aluminum up to 65mm	132	108	1.2	3	T318A	5
DT2163-QZ	Fast, straight cuts in aluminum up to 15mm, steel and non-ferrous metals 3-6mm	100	72	3	ALU 15, Metal 6, Plastic 30	T127D	5
DT2058-QZ	For thin to thick sheets, thin tubes and profiles as well as aluminum up to a thickness of 1.5-10mm	100	74	1.2 - 2.6	10	T123X	5

SETS

Cat. No.	Description	Contents
DT2290-QZ	10 piece jigsaw set - wood cutting	DT2165 x2 / DT2050 x1 / DT2168 x1 / DT2177 x2 DT2166 x2 / DT2075 x2 (Bosch equivalent T101B / T119B0 / T101A0 / T111C / T144D / T144DP)
DT2292-QZ	10 piece set HSS stitch saws for metal	DT2172 x2 Straight cuts in very thin steel sheet and non-metal DT2160 x3 Straight cuts in steel sheet and non-metal DT2161 x2 Straight cuts in solid material such as steel and non-metal DT2163 x2 Fast, straight cuts in aluminum, steel, non-ferrous metal and PVC DT2054 x1 BiM - Curve cuts in metal and thin steel sheet DT2054 x1 BiM - Curve cuts in metal and thin steel sheet
DT2294-QZ	10 Piece jigsaw set - wood / metal cutting	DT2165 x2 / DT2050 x2 / DT2163 x2 DT2177 x2 / DT2160 x2 (Bosch equivalent T101B / T119B0 / T127D / T111C / T118A)





HCS CARBON STEEL BLADES FOR WOOD



FEATURES

- HCS jigsaw blades offer high durability and best cutting results
- Consisting of flexible carbon steel (HCS)
- For use in wood, plastic-coated wood fibre boards and plastics.



FOR USE WITH

Jigsaws (corded and cordless).



PACKS

Cat. No.	Application	Total length mm	Working length mm	Teeth pitch mm	Max. cutting depth mm	Bosch Cat. No.	Pack Qty.
DT2050-QZ	Especially for curved cuts in softwood, plywood, plywood and fiber boards.	76	48	2	15	T119B0	5
DT2052-QZ	Especially for curved cuts in softwood, plywood and fiber boards.	116	87	3	65	T301CD	5
DT2053-QZ	By reverse gear splinter-free cuts in wood, chipboard, plywood, fibreboard and laminate (bevel).	100	73	2.5	40	T101BR	5
DT2164-QZ	Fast, straight cuts in wood, and wood materials.	100	68	4	60	T101D	5
DT2165-QZ	Straight, fine cuts in wood, wood materials and plastics.	100	73	2.5	30	T101B	5
DT2168-QZ	Fine curve cuts in softwood, plywood and coated boards.	76	47	1.4	30	T101A0	5
DT2049-QZ	Fast, extra straight cuts in wood and chipboard.	100	68	4	60	T101DP	5
DT2051-QZ	Fast, rough cuts in wood, chipboard, plywood and fiber boards.	132	100	4	85	T301DL	5
DT2077-QZ	Fast curve cuts in wood.	100	70	4	60	T244D	5
DT2166-QZ	Fast, straight cuts in wood, chipboard, carpentry and fiber boards.	100	68	4	60	T144D	5
DT2186-QZ	Fast, straight cuts in wood, chipboard, plywood, laminated chipboard and plastic up to 60mm thick.	100	68	4	60	T144D	100
DT2169-QZ	Fast, straight cuts in wood and wood materials.	152	116	4	100	T344D	5
DT2048-QZ	For straight and cuts at accurate angles in wood, chipboard, carpentry and fiber boards	116	87	2.5	65	T301BCP	5
DT2075-QZ	Fast, extra straight and angular cuts in wood, chipboard, carpentry and fiber boards.	100	68	4	60	T144DP	5
DT2076-QZ	Fast, extra straight and angular cuts in wood, chipboard, carpentry and fiber boards.	152	116	4	100	T344DP	5
DT2057-QZ	Quick cuts in varying thicknesses in wood, chipboard, joiner and fiber boards up to 65mm.	116	91	2-3	65	T234X	5
DT2167-QZ	Fast, rough cuts in thick wooden planks up to 120mm thickness.	180	155	4	120	T744D	5
DT2060-QZ	Straight, clean cuts in wood, chipboard, plywood, fiber boards and plastics, with U-shank	100	78	2.5	30	U101B	5
DT2061-QZ	Fast cuts in wood and chipboard, with U-shank.	100	76	4	60	U144D	5
DT2074-QZ	Clean, extra straight and angled cuts in wood, plywood, carpentry and fiber boards for border flush cuts	112	74	2.3	65		1

JIGSAW BLADES - QUICK REFERENCE CHART

		Wood Blades						
		High Carbon Steel						
DOC	Pitch	Laminates / Hardwood	Curved cuts in wood	Wood	Wood / Plywood / Laminates / Plastic	Aluminium / Plastics	Softwood / Plywood / Fibre Boards	Wood / Chipboard / Plywood / Laminate / Fibre Board
15mm	15mm				DT2205			
15mm	2.0mm				DT2216		DT2050	
30mm	1.4mm						DT2168	
30mm	2.5mm				DT2217, DT2165			DT2060 (U Shank)
30mm	3.0mm					DT2221		
40mm	2.5mm	DT2207, DT2219						DT2053
60mm	3.1mm				DT2211, DT2212			
60mm	4.0mm		DT2077	DT2164, DT2049, DT2061 (U Shank)	DT2218, DT2220			DT2166, DT2075
60mm	4.2mm				DT2209, DT2210, DT2213, DT2214, DT2186			
65mm	2mm & 3mm							DT2057
65mm	2.3mm							DT2074 (Flush cut)
65mm	2.5mm							DT2048
65mm	3.0mm						DT2052	
85mm	4.0mm							DT2051
100mm	4.0mm			DT2169				DT2076
120mm	4.0mm			DT2167				


		Metal Blades			
		Bi-Metal	HSS		
DOC	Pitch	Steel / Non-Ferrous	Steel / Non-Ferrous	Aluminium / Non Ferrous	Multi Material
2.0mm	0.7mm		DT2162		
3.0mm	1.2mm			DT2085	
3.0mm	1.0mm	DT2150			
2.5mm	0.8mm	DT2156			
4.0mm	1.54mm	DT2054			
6.0mm	1.8mm	DT2154			
4.0mm	1.2mm		DT2160		
6.0mm	2.0mm		DT2161		
30mm	3mm				Alu 15mm, Metal, 6mm, Plastic 30mm

		Specialist Blades						
		TCT	TCT	Bi-Metal	TC Grit	Knife Blade	Bi-Metal	Bi-Metal
DOC	Pitch	GRP / Plastic / Plaster	Inox	Laminates	Ceramic / Fibreglass	Soft Materials / Rubber / Foam / Polystyrene	Sandwich Materials / Steel	Wood / Metal
3.0mm	1.0mm		DT2101					
5.0mm	1.4mm		DT2055					
10mm	n/a							
15mm	1.4mm			DT2081				
15mm	1.7mm			DT2080				
20mm	4.3mm	DT2103						
65/10mm	2.4-5mm							DT2059 (Wood 65mm / Metal 10mm)
65mm	4.3mm	DT2056						
100mm	n/a					DT2201		
120mm	2.0mm						DT2084	



Reciprocating and Alligator Saw Blades

RECOMMENDED MATERIALS



For metal and wood.




Optimised for cordless tools. For metal and wood.



For metal and wood.




For wood, hollow brick and insulation materials.




KNIFE BLADE DESIGN
For clean cuts in fibre insulation, polystyrene, cardboard, carpet, leather and rubber.




CROSSED TEETH
For rough and fast cuts in hard and soft wood, plastic and aluminum.



WAVY TEETH
For fine and clean cuts in hardwood and softwood, aluminum, non-ferrous metals and plastics.



INCLINED SHARPENED, CROSSED TEETH
For fast cuts in hardwood and softwood.




STRAIGHT TEETH
For clean cuts in all wood and plastic.

UNIVERSAL FITTING



Reinforced blade body with aggressive angle ensures high stability and long life.

EXTREME® BI-METAL RECIPROCATING SAW BLADES



APPLICATION PICTOGRAMS
To identify the application areas of each blade.

TOUGHCOAT™
Heat resistant coating prevents heat build up to maximise blade life

BI-METAL CONSTRUCTION
Combining an HCS body with HSS teeth

OPTIMISED TOOTH GEOMETRY
For fast effective cutting with increased cobalt content for longer cutting life.



FOR USE WITH

Corded and cordless reciprocating saws.

PACKS

Cat. No.	Application	Length mm	Pitch mm	TPI	Pack Qty.
DT2407L-QZ	For extremely hard and abrasive metals	152	1.4-1.8	14-18	5
DT2408L-QZ	For extremely hard and abrasive metals	203	1.4-1.8	14-18	5
DT2409L-QZ	For extremely hard and abrasive metals	305	1.4-1.8	14-18	5
DT2300L-QZ	For fast, rough cuts in hard and soft wood with nails, with immersion tip	152	4.2	6	5
DT2307L-QZ	For fast, rough cuts in hard and soft wood with nails, with immersion tip	228	4.2	6	5
DT2314L-QZ	For fast, rough cuts in hard and soft wood with nails, with immersion tip	305	4.2	6	5
DT2315L-QZ	For fast cuts in multi-materials	100	2.5	10	5
DT2301L-QZ	For fast cuts in multi-materials	152	2.5	10	5
DT2308L-QZ	For fast cuts in multi-materials	228	2.5	10	5
DT2316L-QZ	For fast cuts in multi-materials	305	2.5	10	5

BULK PACKS

Cat. No.	Description	Pack Qty.
DT2491-QZ	DT2307L-QZ x25	25
DT2492-QZ	DT2308L-QZ x25	25

SETS

Cat. No.	Description	Contents	Pack Qty.
DT2440L-QZ	6 Piece EXTREME® reciprocating Blade Set	DT2300L x1 / DT2301L x1 / DT2307L x1 / DT2308L x1 / DT2315L x1 / DT2407L x1	6
DT2443L-QZ	8 Piece EXTREME® reciprocating Blade Set	DT2300L x3 / DT2407L x3 / DT2308L x1 / DT2408L x1	8
DT2441L-QZ	12 Piece EXTREME® reciprocating Blade Set	DT2300L x2 / DT2301L x2 / DT2307L x2 / DT2308L x2 / DT2315L x2 / DT2407L x1 / DT2408L x1	12



XR EXTREME RUNTIME RECIPROCATING SAW BLADES



FEATURES

- Designed for cordless tools to maximise battery life and runtime. Ideally suited for FlexVolt as part of the increased power and runtime story
- High efficiency design to achieve more cuts per charge
- Full range - wood and metal cutting saw blades
- Variable tooth design (increase blade efficiency)
- ToughCoat™ reduces heat and prolongs blade life
- Up to 2x runtime
- Up to 2x longer life

FOR USE WITH
XR FlexVolt, other corded and cordless reciprocating saws



PACKS

Cat. No.	Application	Length mm	Pitch mm	TPI	Pack Qty.
DT99554-QZ	For energy efficient, fast, cutting in hard and soft wood with nails	152	4.2	6	5
DT99555-QZ	For energy efficient, fast, cutting in hard and soft wood with nails	230	4.2	6	5
DT99553-QZ	For energy efficient cutting in extremely hard and abrasive metals	152	1.4-1.8	14-18	5
DT99552-QZ	For energy efficient cutting in extremely hard and abrasive metals	230	1.4-1.8	14-18	5

SETS

Cat. No.	Description	Contents	Pack Qty.
DT99550-QZ	13 piece XR recip blade set	DT99552 x2 / DT99553 x4 / DT99554 x5 / DT99555 x2	13
DT99551-QZ	8 piece XR recip blade set	DT99552 x1 / DT99553 x3 / DT99554 x3 / DT99555 x1	8





BI-METAL RECIPROCATING SAW BLADES FOR METAL



FEATURES

- Bi-metal construction, as a combination of HCS bodies and cobalt-alloyed HSS-cutting.
- Aggressive tooth geometry with a special new angle for a fast and effective removal of material, especially for tensile and abrasive metals.
- Ideal for extreme applications as well as demolition and demolition work.

FOR USE WITH

Reciprocating saws (corded and cordless).



PACKS

Cat. No.	Application	Length mm	Pitch mm	TPI	Bosch Cat. No.	Pack Qty.
DT2385-QZ	Fine cuts in steel sheet, pipes and profiles up to 1.5mm	152	1.1	23	S922AF	5
DT2384-QZ	Fast cuts in steel sheet, pipes and profiles up to 3mm.	152	1.4	18	S1122EF	5
DT2354-QZ	Fast cuts in steel sheet, pipes and profiles up to 3mm.	203	1.4	18	S1122EF	5
DT2361-QZ	Fast cuts in metals, sheet metal, pipes and profiles (3-8mm).	152	1.8	14	S922BF	5
DT2353-QZ	Fast cuts in metals, sheet metal, pipes and profiles (3-8mm).	203	1.8	14	S1025BF	5
DT2323-QZ	Fast cuts in metals, sheet metal, pipes and profiles	203	1.8	14	S1022BF	100
DT2346-QZ	Steel and non-ferrous metals up to 3mm. Ideal for use in battery-powered devices	152	1.4	18	S922EF	5
DT2404-QZ	Progressor blade for different material thicknesses. Thin to thick sheet metal 1-8mm Thin to thick metal profiles 5-100mm	150	1.4-3.35	8-18	S123XF	5



BI-METAL RECIPROCATING SAW BLADES FOR WOOD



FEATURES

- Bi-metal construction, as a combination of HCS bodies and cobalt-alloyed HSS-cutting.
- Aggressive tooth geometry with a special new angle for a fast and effective removal of material, especially for tensile and abrasive metals.
- Ideal for extreme applications as well as demolition and demolition work.

FOR USE WITH

Reciprocating saws (corded and cordless).



PACKS

Cat. No.	Application	Length mm	Pitch mm	TPI	Bosch Cat. No.	Pack Qty.
DT2351-QZ	Fine, fast curve cuts in wood and plastic. Special immersion tip for fast and precise dipping cuts in all wood materials.	152	4.2	6	S611DF	5
DT2359-QZ	Fast cuts in wood with nails and hard plastic. Newly developed, patented immersion tip for fast and precise dipping cuts in all wood materials.	152	4.2	6	S611VF	5
DT2349-QZ	Fast cuts in wood with nails and hard plastic. Newly developed, patented immersion tip for fast and precise dipping cuts in all wood materials.	228	4.2	6	S1111VF	5
DT2320-QZ	Fast cuts in wood with nails and tough plastics. Plunge Point tip for fast and accurate plunge cutting into wood materials.	228	4.2	6	S1111VF	100
DT2350-QZ	Fast cuts in wood with nails and hard plastic. Newly developed, patented immersion tip for fast and precise dipping cuts in all wood materials.	305	4.2	6	S1411VF	5
DT2344-QZ	Fine, fast curve cuts in wood and plastic. Ideal for use in battery-powered devices	152	3.6	7	S711VF	5

BI-METAL RECIPROCATING SAW BLADES FOR UNIVERSAL USE



FEATURES

- Bi-metal construction, as a combination of HCS body and cobalt-alloyed HSS cutting.
- Cobalt-alloyed M2 HSS cutting edges for increased wear resistance.
- Reinforced tooth shoulder for improved stability.

FOR USE WITH

Reciprocating saws (corded and cordless).



HCS RECIPROCATING SAWS BLADES FOR WOOD



FEATURES

- Highly flexible carbon steel (HCS).
- For soft wood, wood materials, plastics and other soft materials
- Universal shank 1/2".

FOR USE WITH

Reciprocating saws (corded and cordless).



PACKS

Cat. No.	Application	Length mm	Pitch mm	TPI	Bosch Cat. No.	Pack Qty.
DT2348-QZ	For sandwich materials up to 100mm, metal up to 10mm	152	1.8-2.5	10-14	S922VF	5
DT2387-QZ	For sandwich materials up to 175mm, metal up to 10mm	203	1.8-2.5	10-14	S1122VF	5
DT2355-QZ	For sandwich materials up to 250mm, metal up to 10mm	305	1.8-2.5	10-14	S1222VF	5
DT2345-QZ	Universal use in wood, wood with nails, aluminum and fiberglass. Ideal for use in battery-powered devices.	152	2.5	10	S922VF	5
DT2406-QZ	Progressor blade for different material thicknesses. wood with nails/metal, chipboard 5-150mm sheet metal, aluminium profiles 3-18mm plastic, fibre glass, reinforced plastic profiles 5-150mm	203	2.4-4.6	5-10	S3456XF	5

BULK PACKS

Cat. No.	Description	Pack Qty.
DT2490-QZ	DT2406-QZ x25	25



PACKS

Cat. No.	Application	Length mm	Pitch mm	TPI	Bosch Cat. No.	Pack Qty.
DT2362-QZ	Fine, fast curve cuts in wood and plastics.	152	4.2	6	S611D	5
DT2363-QZ	Construction wood 6-150mm Chipboard and MDF 6-60mm Plywood, plastic 6-150mm Wooden walls up to 175mm Blade thickness 1.25mm.	228	4.2	6	S1544D	5
DT2364-QZ	Fine, fast cuts in wood and plastics.	305	4.2	6	S1344D	5
DT2402-QZ	Progressor blade for different material thicknesses. Construction timber 6-150mm Chipboard and MDF 6-60mm Plywood, plastic 6-150mm Wooden panels up to 175mm	203	2.4-4	6-10	S2345X	5
DT2352-QZ	For rough wood without nails 15-190mm Living wood and for grooving up to 190mm Firewood 15-190mm Sheet thickness 1.5mm	240	5 - 6.5	4-5	S1531L	5
DT2432-QZ	For rough wood without nails 20-250mm Living wood and for grooving up to 250mm Leaf thickness 1.25mm	305	8.5	3	S1617K	5

BULK PACKS

Cat. No.	Description	Pack Qty.
DT2493-QZ	DT2352-QZ x25	25

SETS

Cat. No.	Description	Contents	Pack Qty.
DT2442-QZ	8 piece recip set	DT2301-QZ x2 / DT2303-QZ x2 / DT2349-QZ x2 DT2353-QZ x2	8
DT2444-QZ	6 piece recip set	DT2345-QZ x2 / DT2349-QZ x2 / DT2353-QZ x2	6
DT2445-QZ	12 piece recip set	DT2345-QZ x1 / DT2349-QZ x3 / DT2359-QZ x2 DT2353-QZ x3 / DT2361-QZ x3	12

SPECIALIST MATERIAL SAW BLADES



FOR USE WITH
Reciprocating saws (corded and cordless).



PACKS

Cat. No.	Application	Length mm	Pitch	TPI	Bosch Cat. No.	Pack Qty.
DT2356-QZ	Bi-Metal blade for cutting plasterboard.	152	1.8	14	S628DF	5
DT2332-QZ	Carbide grit reciprocating blade for cutting of lightweight concrete, bricks, abrasive materials, ceramic, fiberglass, unalloyed soft metal and wood with nails.	152	2	13	-	1
DT2333-QZ	Wear resistant carbide grit edged blade for cutting light masonry blocks, bricks, abrasive materials, ceramics, fibreglass, mild steel and wood with nails.	228	2	13	S1130RIF	1
DT2335-QZ	Tungsten carbide toothed blade for cutting light masonry blocks, bricks, abrasive materials.	235	1	25	-	1
DT2400-QZ	Bi-metal reciprocating saw blade for pallet repair, wood with nails / metal 5-175mm, metal sheets, metal pipes, aluminum profiles 3-12mm, especially for flexible flush cuts, blade thickness 0.9mm.	225	2.5	10	S1122HF	100
DT2420-QZ	Tungsten carbide tipped blade for cutting areated concrete, red brick and fibre cement up to 150mm.	240	12.7	2	S1543HM	1
DT2421-QZ	Tungsten carbide tipped blade for cutting areated concrete, red brick and fibre cement up to 250mm.	305	12.7	2	S1243HM	1
DT2422-QZ	Aerated concrete, brick and fiber cement to 365mm, blade thickness 1.5mm.	457	12.7	2	S2243HM	1



RECIPROCATING SAW BLADES FOR INSULATION MATERIAL



FOR USE WITH
Reciprocating saws (corded and cordless).



PACKS


Cat. No.	Application	Length mm	Pitch	TPI	Bosch Cat. No.	Pack Qty.
DT2450-QZ	Precision cuts in fibre insulation material up to 100mm	225	4.2	6	S1113AWP	2
DT2451-QZ	Precision cuts in fibre insulation material up to 100mm	300	4.2	6	S1213AWP	2
DT2452-QZ	Precision cuts in fibre insulation material up to 100mm	400	4.2	6	S2013AWP	1

BREAKAWAY™ RECIPROCATING SAW BLADES

HEAT RESISTANT TOUGHCOAT™
For extended blade performance

14/18 TPI
For optimised cuts in metal applications

FEATURE
Allows for full blade use




PACKS

Cat. No.	Application	Length mm	TPI	Pack Qty.
DT2416-QZ	Fast cuts in metals, sheets metal, pipes and profiles	230	14 / 18	5
DT2417-QZ	Fast cuts in metals, sheets metal, pipes and profiles	152	14 / 18	5

SET

Cat. No.	Description	TPI	Contents
DT2446-QZ	8 piece break away recip blade set and storage case	14 / 18	DT2416-QZ 228mm x2 DT2417-QZ 152mm x6



RECIPROCATING BLADES - QUICK REFERENCE CHART

* bulk pack
 ■ Immersion tip
 ▼ For cordless
 HCS = High Carbon Steel
 Bi-M = HCS body with cobalt-alloyed M2 HSS-cutting



Length	100 mm		152 mm		203 mm		225 mm		228 mm		230 mm		240 mm		300 mm		305 mm		400 mm		457 mm	
	Bi-M	HCS	Bi-M	HCS	Bi-M	HCS	Bi-M	HCS	Bi-M	Bi-M	HCS	Bi-M	HCS	Bi-M	HCS	Bi-M	HCS	Bi-M	HCS	Bi-M	HCS	
Wood and plastic																						
Cordless tool																						
Clean, fast cuts		DT2362	DT2351					DT2363							DT2364							
Wood with nails			■ DT2359						■ DT2349 ■ DT2320							■ DT2350						
Varying material thickness				DT2402																		
Living wood														DT2352 DT2493*					DT2432			
Cordless tool																						
Clean, fast cuts			▼ DT2344																			
Metal																						
Cordless tool																						
Metal < 1.5 mm				DT2385																		
Metal < 3 mm				DT2384 DT2407L DT2417 DT99553		DT2354			DT2408L DT99552	DT2416										DT2409L		
Metal 3 to 8 mm				DT2361		DT2353 DT2323*																
Metal 1 to 100 mm				DT2404																		
Cordless tool																						
Metal < 3 mm				▼ DT2346																		
Universal																						
Cordless tool																						
Plastics, sandwich materials, tubing				DT2348		DT2387																DT2355
Metal, rubber, fibreglass, cast iron						DT2406 DT2490*																
Cordless tool																						
Wood with nails, aluminum, fibreglass				DT99554						DT99555												DT2345
Demolition work																						
Wood				■ DT2300L						■ DT2307L												■ DT2314L
Metal, metal profiles, metal piping																						
Metal, plastics, sandwich materials		DT2315L		DT2301L							DT2308L											DT2316L
Other specialist materials																						
Plasterboard				DT2356																		
Masonry, brick, ceramics, fibreglass				DT2332							DT2333											
Masonry, brick											DT2335											
Pallet work								DT2400*														
High-brick, brick, fibre cement															DT2420					DT2421		DT2422
INOX, reinforced plastics																						
Fibre insulation							DT2450									DT2451					DT2452	

XR EXTREME RUNTIME ALLIGATOR® SAW BLADES



FEATURES

- Designed for cordless tools to maximise battery life and runtime.
- Ideally suited for FlexVolt.
- High efficiency design achieves more cuts per charge.


FOR USE WITH

- XR FlexVolt, other corded and cordless reciprocating saws



SINGLE PACKS

Cat. No.	Application	Suitable for	Total length mm	Working length mm	Teeth	Pack Qty.
DT99590-QZ	Fast cutting of thermal building blocks. Course finish. Not for use in concrete, masonry, brick, breeze blocks or metal.	DCS 396 DWE 396	410	295	TCT	1
DT99591-QZ	Fast cutting of thermal brick blocks up to pressure strength class 12 and aerated concrete blocks.	DCS 397 DWE 397 DWE 398 DWE 399	555	430	TCT	1
DT99592-QZ	Fast cutting of hardwood, softwood, hardboard, plasterboard, and fibreboard. Medium finish. Not recommended for cutting chipboard.	DCS 396 DWE 396	410	295	HSS	1
DT99593-QZ	Fast cutting of hardwood, softwood, hardboard, plasterboard, fibreboard, and logs. Medium finish. Not recommended for cutting chipboard.	DCS 397 DWE 397 DWE 398 DWE 399	555	430	HSS	1



ALLIGATOR® SAW BLADES



FEATURES
 • 2-piece blades sheets in HSS quality or hard-metal-matched for optimum performance when used in DeWALT® Alligator® saws.



FOR USE WITH
 Alligator saws DW390 / 391 / 392 / 393



SINGLE PACKS

Cat. No.	Application	Suitable for	Total length mm	Working length mm	Teeth material	Pack Qty.
DT2960-QZ	Drywall, board	DW 390 DW 391	360	275	HSS	1
DT2961-QZ	Hardwood, softwood, plywood	DW 390 DW 391	360	275	HSS	1
DT2962-QZ	Plywood, chipboard, MDF	DW 390 DW 391	360	275	TCT	1
DT2963-QZ	Building block, Class 12 Poroton	DW 390 DW 391	360	275	TCT	1
DT2964-QZ	Building block, Class 12 Poroton	DW 392 DW 393 DW 394	528	425	TCT	1
DT2965-QZ	Building block, gas beton	DW 390 DW 391	528	425	TCT	1
DT2966-QZ	Building block, Class 20 Poroton	DW 390 DW 391	528	425	TCT	1



ALLIGATOR® SAW BLADES



FOR USE WITH
 DWE396 / 397 / 398 / 399



SINGLE PACKS

Cat. No.	Application	Suitable for	Total length mm	Working length mm	Teeth material	Pack Qty.
DT2970-QZ	Fine wood cutting	DWE 396	410	295	HSS	1
DT2971-QZ	Rough wood cutting	DWE 396	410	295	HSS	1
DT2972-QZ	Fine wood cutting	DWE 396	410	295	TCT	1
DT2973-QZ	Class 12 Poroton	DWE 396	410	295	TCT	1
DT2977-QZ	Class 20 Poroton	DWE 396	410	295	TCT	1
DT2974-QZ	Class 12 Poroton	DWE 397 DWE 398 DWE 399	555	430	TCT	1
DT2975-QZ	Gas beton white	DWE 397 DWE 398 DWE 399	555	430	TCT	1
DT2976-QZ	Class 20 Poroton	DWE 397 DWE 398 DWE 399	555	430	TCT	1
DT2978-QZ	Rough wood cutting	DWE 397 DWE 398 DWE 399	555	430	HSS	1
DT2979-QZ	Insulation material	DWE 397 DWE 398 DWE 399	555	430	HSS	1

BAND SAW BLADES



FEATURES
 • Saw blades made of high quality, tempered steel
 • Extremely sharpened and hardened teeth allow cleanest cuts
 • Specially hardened teeth.

FOR USE WITH
 DCS371



SINGLE PACKS

Cat. No.	Application	Suitable for	Tooth Design mm	Cant Angle	Tooth Kerf mm	Blade Thickness mm	Pack Qty.
DT8480-QZ	Wood-fretsaw blade	DW738 DW739	2095	3	0.6	4.2	1
DT8481-QZ	General purpose blade	DW738 DW739	2095	12	0.6	4.2	1
DT8482-QZ	Wood - thick cuts	DW738 DW739	2095	16	0.6	6.4	1
DT8483-QZ	Wood - contour / scroll	DW738 DW739	2095	6	0.6	3.2	1
DT8484-QZ	Non-ferrous metals - thin cuts	DW738 DW739	2095	6	0.6	1.8	1
DT8485-QZ	Non-ferrous metal - thick cuts	DW738 DW739	2095	12	0.6	3.2	1
DT8486-QZ	Wood, laminate and formica	DW738 DW739	2095	10	0.6	3.2	1

SINGLE PACKS

Cat. No.	Application	Suitable for	Tooth Design mm	Cant Angle	Tooth Kerf mm	Blade Thickness mm	Pack Qty.
DT8470-QZ	Wood - Fretsaw blade	DW876	2215	4	0.6	1.8	1
DT8471-QZ	Wood - contour / scroll	DW876	2215	6	0.4	4.2	1
DT8472-QZ	Wood - rip and cross-cut	DW876	2215	10	0.4	4.2	1
DT8473-QZ	Wood - fast rip cuts, medium composites	DW876	2215	16	0.6	6.4	1
DT8474-QZ	Wood - fast rip cuts in thick wood	DW876	2215	20	0.6	6.4	1
DT8475-QZ	Non-ferrous metal - thin steel section cuts	DW876	2215	6	0.6	1.4	1
DT8476-QZ	Non-ferrous metal - thick steel section cuts	DW876	2215	12	0.6	1.8	1

SETS

Cat. No.	Application	Suitable for	Tooth Design mm	Cant Angle	Tooth Kerf mm	Blade Thickness mm	Pack Qty.
DT8460-QZ	Metal 6.35-9.52mm aluminum, stainless steel, plastic	DCS371NT	835	12	0.5	1.8	4
DT8461-QZ	Metal 3.97-6.35mm aluminum, stainless steel, plastic	DCS371NT	835	12	0.5	1.4	4
DT8462-QZ	Metal up to 3.97mm aluminum, stainless steel, plastic	DCS371NT	835	12	0.5	1.05	4
DT8463-QZ	Metal 6.35-9.52mm aluminum, stainless steel, plastic	DCS371NT	835	12	0.5	1.8/1.4	4



RECOMMENDED MATERIALS



Wood Shaping



ROUTER BITS



FEATURES

• Double-edged for precise and burr-free edges.

APPLICATIONS

Basic and flank cutting.

For grooving, rebating, long hole milling and drilling.

The ground drilling drill allows drilling.

Can also be used for straight milling applications in laminate.

FOR USE WITH

Top milling machines



SINGLE PACKS

Cat. No.	Description	Shank mm (A)	Milling diameter mm (B)	Working length mm (C)	Total length mm	Pack Qty.
DT90001-QZ	Double edged (Z2), HM	8	5	12	50	1
DT90002-QZ	Double edged (Z2), HM	8	6	19	55	1
DT90003-QZ	Double edged (Z2), HM	8	8	20	55	1
DT90004-QZ	Double edged (Z2), HM	8	10	20	52	1
DT90005-QZ	Double edged (Z2), HM	8	12	20	52	1
DT90006-QZ	Double edged (Z2), HM	8	14	20	52	1
DT90007-QZ	Double edged (Z2), HM	8	15	20	52	1
DT90008-QZ	Double edged (Z2), HM	8	16	20	52	1
DT90009-QZ	Double edged (Z2), HM	8	18	20	52	1
DT90010-QZ	Double edged (Z2), HM	8	20	20	52	1
DT90011-QZ	Double edged (Z2), HM	8	22	20	52	1
DT90012-QZ	Double edged (Z2), HM	8	25	20	52	1
DT90013-QZ	Double-edged (Z2), HM	8	22.7	9.5	5	1
DT90014-QZ	Double-edged (Z2), HM	8	24.7	13.5	6	1
DT90015-QZ	Double-edged (Z2), HM	8	31.8	15.9	8	1

SETS

Cat. No.	Description
DT90016-QZ	12pc set inc. storage box with clear lid
DT90017-QZ	22pc set inc. storage box with clear lid

8MM ROUTER BIT SETS



SETS

Cat. No.*	Description and Contents	Ø mm
DT90016-QZ	12 Piece HM milling cutter set incl. storage box with clear cover:	
	Hollow flute cutter	12
	V-slot milling cutter	12.7
	Tine cutter	14.3
	Hollow flute cutter with ball bearing	21.5
	Profile milling cutter with ball bearing	27
	Chamfering mill with ball bearing	28.6
	Groove cutters	8
		12
	Slot milling cutter	16
	Flush end mill cutter with ball bearing	12.7
	Rounding cutters with ball bearing	24.7
		32.7
	DT90017-QZ	22 Piece HM milling cutter set incl. storage box with clear cover:
Groove cutter		6
Slot milling cutters		8
		10
Groove cutter		12
Slot milling cutters		16
		20
Tine cutter		14.3
Hollow flute cutters		8
		12
V-groove milling cutters		12.7
		12.7
Quarter-turn milling cutter		21
Profile milling cutter with ball bearing		22.22
Chamfering cutter with ball bearing		28.7
Round milling cutters with ball bearing		22.7
		28.6
Chamfering cutter with ball bearing		19.9
Flush end mill cutter with ball bearing		12.7
Profile milling cutter with ball bearing		27
Hollow flute cutters with ball bearing	19.5	
	25.5	
Folding cutter with ball bearing	31.8	

PLANER BLADES



FOR USE WITH

Corded and cordless planers.



SETS

Cat. No.	Description	Suitable for	Length mm	Width mm	Thickness mm	Pack Qty.
DT3901-QZ	80mm TCT reversible planer blades	DW676	80	5.9	1.2	1 pair
DT3905-QZ	82mm HSS reversible planer blades	DZ6500 D26501	82	5.5	1.1	1 pair
DT3906-QZ	82mm TCT reversible planer blades	DW678	82	5.5	1.1	1 pair



RECOMMENDED MATERIALS



Coated Abrasives



Abrasive mesh

Support material made of durable nylon braid.

Silicon carbide abrasive grain of the grating by a special composite process is applied to the nylon braid. This reduces the flexibility, but increases the lifetime up to 4x compared to DeWALT® standard abrasives.

Due to the large number of small openings in the grid lines, the suction power is significantly increased since the grinding dust is transported away over a larger surface. This results in a finer finish.

After intensive use, the grinding dust can be simply tapped or blown out.



Standard abrasives

High-quality aluminium oxide grains for a perfect surface finish.



Flap discs

For use with angle grinders.

EXTREME[®] ABRASIVE MESH



HOOK AND LOOP



EASY PLACEMENT

The open structure of the grid lines eliminates the need for precise positioning.

LONGER DURABILITY

Up to 4x longer life compared to DeWALT[®] standard abrasive papers by better removal of the sanding dust.

UP TO 25% BETTER SANDING RESULTS

The open weave structure enables a more effective removal of sanding dust. This results in a finer sanding pattern.

1x = 4x

4x LONG LIFE
vs. Standard DEWALT Sanding Sheets

FEATURES

The silicon carbide grain is applied to the nylon braid by a special composite process. This reduces the flexibility, but increases the service life up to 4x compared to DeWALT[®] standard abrasives.



Due to the large number of small openings in the grid lines, the suction capacity is significantly increased as the dust is transported over a significantly larger surface.

APPLICATIONS

For all basic, intermediate and final sanding applications in wood, metal, paints, varnishes, plaster and drywall.

WATER RESISTANT

After intensive use, dust can be easily washed off. After drying, the abrasive mesh is ready for use again



EXTREME[®] UNIVERSAL ABRASIVE MESH



RANDOM ORBIT



FEATURES

- Universal ROS (Random Orbit Sander) sheets.




FOR USE WITH

Works with all dust extraction hole configurations.



Universal ROS (Random Orbit Sanders) e.g. suitable for: DeWALT[®], Bosch[®], Festool[®], Makita[®], Metabo[®], Milwaukee[®].



Ø125mm - ROS PACKS

Cat. No.	Grain size	Pack Qty.
DTM8671-QZ	40	5
DTM8560-QZ	60	5
DTM3103-QZ	80	5
DTM3105-QZ	120	5
DTM3107-QZ	240	5
DTM8562-QZ	320	5
DTM8561-QZ	60	10
DTM3113-QZ	80	10
DTM3115-QZ	120	10
DTM3117-QZ	240	10
DTM8563-QZ	320	10

Ø125mm - ROS BULK PACKS

Cat. No.	Grain size	Pack Qty.
DTM8567-QZ	40	50
DTM8568-QZ	80	50
DTM8569-QZ	120	50
DTM8570-QZ	180	50
DTM8571-QZ	240	50

Ø150mm - ROS PACKS

Cat. No.	Grain size	Pack Qty.
DTM8556-QZ	60	5
DTM3123-QZ	80	5
DTM3125-QZ	120	5
DTM3127-QZ	240	5
DTM8558-QZ	320	5
DTM8557-QZ	60	10
DTM3133-QZ	80	10
DTM3135-QZ	120	10
DTM3137-QZ	240	10
DTM8559-QZ	320	10
DTM8572-QZ	40	50
DTM8573-QZ	80	50
DTM8574-QZ	120	50
DTM8575-QZ	180	50
DTM8576-QZ	240	50

Ø225mm - ROS PACKS

Cat. No.	Grain size	Pack Qty.
DTM8564-QZ	80	5
DTM8565-QZ	120	5
DTM8566-QZ	240	5

FOR USE WITH

Universal ROS (Random Orbit Sanders) e.g. suitable for: Flex, Festool.





EXTREME® ABRASIVE MESH

DETAIL SANDER



FOR USE WITH
Detail sander or
DeWALT® multi tool
DWE315 / DCS355.



93 X 93mm PACKS

Cat. No.	Grain size	Pack Qty.
DTM8667-QZ	40	5
DTM8668-QZ	60	5
DTM3092-QZ	80	5
DTM3093-QZ	120	5
DTM3095-QZ	240	5

DELTA SANDER



FOR USE WITH
Delta sander from Festool®



100 X 150mm PACKS

Cat. No.	Grain size	Pack Qty.
DTM8553-QZ	80	5
DTM8554-QZ	120	5
DTM8555-QZ	240	5

1/3 SHEET



FOR USE WITH
DeWALT®, Makita®



93 X 190 PACKS

Cat. No.	Grain size	Pack Qty.
DTM8655-QZ	40	5
DTM8656-QZ	60	5
DTM8621-QZ	80	5
DTM8622-QZ	120	5
DTM8624-QZ	240	5

EXTREME® ABRASIVE MESH

1/4 SHEET



FOR USE WITH
DeWALT®, Bosch®,
Festool®, Metabo®




115 X 115mm PACKS

Cat. No.	Grain size	Pack Qty.
DTM8663-QZ	40	5
DTM8664-QZ	60	5
DTM3022-QZ	80	5
DTM3023-QZ	120	5
DTM3025-QZ	240	5

1/2 SHEET



FOR USE WITH
DeWALT®, Bosch®,
Festool®, Metabo®




115 X 228mm PACKS

Cat. No.	Grain size	Pack Qty.
DTM8659-QZ	40	5
DTM8660-QZ	60	5
DTM851-QZ	80	5
DTM8552-QZ	120	5

MULTI-PURPOSE SANDING SHEETS


1/3 SHEETS



93 X 190mm PACKS

Cat. No.	Grain size	Pack Qty.
DT8650-QZ	40	10
DT8620-QZ	60	10
DT8621-QZ	80	10
DT8622-QZ	120	10
DT8623-QZ	180	10
DT8624-QZ	240	10


1/3 SHEETS



93 X 230mm PACKS

Cat. No.	Grain size	Pack Qty.
DT8590-QZ	60	10
DT8591-QZ	80	10
DT8592-QZ	120	10


1/2 SHEETS



115 X 228mm PACKS

Cat. No.	Grain size	Pack Qty.
DT8550-QZ	60	10
DT8551-QZ	80	10
DT8552-QZ	120	10

1/4 SHEETS




115 X 140mm PACKS

Cat. No.	Grain size	Pack Qty.
DT3011-QZ	40	25
DT3012-QZ	60	25
DT3014-QZ	100	25
DT3015-QZ	150	25
DT3017-QZ	220	25

SANDING SHEETS

1/4 SHEET



FEATURES

- Heat resistant resin adhesive bond, ideal for power sanding.
- Tough, durable paper backing ensures longer disc life and performance.
- Stearate coating reduces clogging, excellent for softwoods and painted surfaces
- Quick fit nylon loop backing allows fast and easy disc changeover.

APPLICATIONS

For all stripping sanding and finishing tasks on wood, metal and painted surfaces.



115 x 115mm PACKS

Cat. No.	Grain size	Pack Qty.
DT3020-QZ	40	10
DT3021-QZ	60	10
DT3022-QZ	80	10
DT3023-QZ	120	10
DT3024-QZ	180	10
DT3025-QZ	240	10
DT3026-QZ	320	10
DT3030-QZ	40	25
DT3031-QZ	60	25
DT3032-QZ	80	25
DT3033-QZ	120	25
DT3034-QZ	180	25
DT3035-QZ	240	25

SANDING SHEETS

DETAIL




FEATURES

- Industrial grade abrasive paper for all stripping, sanding and finishing tasks on wood, paint and fillers.
- High quality aluminium oxide grain gives superior finish.
- Resin bonding provides excellent grain adhesion and heat resistance for powered sanding.
- Tough, durable "E" weight backing ensures longer life and performance.

APPLICATIONS

For all sanding and finishing tasks on wood, painted surfaces and fillers.



DETAIL PACKS

Cat. No.	Grain size	Pack Qty.
DT3090-QZ	40	10
DT3091-QZ	60	10
DT3092-QZ	80	10
DT3093-QZ	120	10
DT3094-QZ	180	10
DT3095-QZ	240	10



WATER RESISTANT ABRASIVE PAPER 230 x 280mm

FULL SHEETS MULTI-PURPOSE



FEATURES

- Multi-purpose wet and dry sanding.
- High-quality, sharp aluminium oxide grains.
- High-strength and flexible, water-resistant latex paper for easier contouring and finishing.



APPLICATIONS

Fine sanding of primers and fillers.



FOR USE WITH

Hand sanding.



230 x 280mm PACKS

Cat. No.	Grain size	Pack Qty.
DT3244-QZ	180	10
DT3245-QZ	240	10
DT3246-QZ	320	10
DT3247-QZ	400	10
DT3248-QZ	1000	10
DT3249-QZ	1200	10

ABRASIVE FABRIC FOR METAL 230 x 280mm

FULL SHEETS



FEATURES

- Industrial aluminium oxide grains for fast and aggressive sanding and abrasion
- Resistant, flexible fabric Class J (J = cotton fabric, light weight).



APPLICATIONS

For sanding and removal work as well as for deburring and de-rusting of metal.



FOR USE WITH

Hand sanding.



230 x 280mm PACKS

Cat. No.	Grain size	Pack Qty.
DT3281-QZ	80	10
DT3282-QZ	120	10
DT3283-QZ	180	10
DT3284-QZ	240	10

MULTI-PURPOSE SANDING BELTS



FEATURES

- High-quality aluminium oxide grains for fast and aggressive material removal
- Heat-resistant and dust-resistant synthetic resin bond for powerful sanding.

APPLICATIONS

For all basic, intermediate and final sanding applications in wood, paints and lacquers as well as metal.

FOR USE WITH

Belt sanders.



45 x 715mm GRINDING BELT PACKS

Cat. No.	Grain size	Pack Qty.
DT3351-QZ	80	3
DT3352-QZ	100	3
DT3353-QZ	120	3
DT3354-QZ	150	3
DT3355-QZ	240	3

64 x 356mm MINI SANDING BELT PACKS

Cat. No.	Grain size	Pack Qty.
DT3661-QZ	60	3
DT3662-QZ	80	3
DT3663-QZ	100	3
DT3664-QZ	150	3
DT3299-QZ	220	3
DT3666-QZ	60	10
DT3667-QZ	80	10
DT3668-QZ	100	10
DT3669-QZ	150	10

75 x 457mm SANDING BELT PACKS

Cat. No.	Grain size	Pack Qty.
DT3640-QZ	40	3
DT3641-QZ	60	3
DT3642-QZ	80	3
DT3643-QZ	100	3
DT3644-QZ	EXTREME® 150	3

75 x 533mm SANDING BELT PACKS

Cat. No.	Grain size	Pack Qty.
DT3300-QZ	40	3
DT3376-QZ	60	3
DT3377-QZ	80	3
DT3628-QZ	100	3
DT3378-QZ	120	3
DT3301-QZ	40	10
DT3302-QZ	60	10
DT3303-QZ	80	10
DT3304-QZ	100	10
DT3629-QZ	120	10
DT3305-QZ	EXTREME® 150	10
DT3307-QZ	EXTREME® 220	10

100 x 560mm SANDING BELT PACKS

Cat. No.	Grain size	Pack Qty.
DT3312-QZ	40	3
DT3314-QZ	60	3
DT3315-QZ	80	3
DT3316-QZ	100	3
DT3318-QZ	EXTREME® 150	3

100 X 610mm SANDING BELT PACKS

Cat. No.	Grain size	Pack Qty.
DT3320-QZ	40	3
DT3321-QZ	60	3
DT3322-QZ	80	3
DT3323-QZ	100	3
DT3324-QZ	EXTREME® 150	3
DT3670-QZ	40	10
DT3671-QZ	60	10
DT3672-QZ	80	10
DT3673-QZ	100	10

SANDING SHEETS



FEATURES

- Multi-purpose
- High quality aluminium oxide grains for a perfect surface finish.
- Dust repellent resin bond for powerful sanding.
- High strength and flexible paper of class E (250g /m²) for increased durability and performance.



APPLICATIONS

For all basic, intermediate and final sanding applications in wood, paints and varnishes, as well as fillers.



FOR USE WITH

Vibratory sanders.



SINGLE PACKS

Cat. No.	Grain size	Size Length x Width	Pack Qty.
DT3580-QZ	60	5m x 115mm	1
DT3581-QZ	80	5m x 115mm	1
DT3582-QZ	120	5m x 115mm	1
DT3583-QZ	180	5m x 115mm	1
DT3584-QZ	220	5m x 115mm	1
DT3154-QZ	40	5m x 93mm	1
DT3590-QZ	60	5m x 93mm	1
DT3591-QZ	80	5m x 93mm	1
DT3592-QZ	120	5m x 93mm	1
DT3593-QZ	180	5m x 93mm	1
DT3594-QZ	220	5m x 93mm	1
DT3579-QZ	40	25m x 93mm	1
DT3595-QZ	60	25m x 93mm	1
DT3596-QZ	80	25m x 93mm	1
DT3597-QZ	120	25m x 93mm	1
DT3598-QZ	180	25m x 93mm	1
DT3599-QZ	220	25m x 93mm	1

RANDOM ORBIT SANDING SHEETS



FEATURES

- Heat-resistant synthetic resin base and top bond of the abrasive grain ensure the highest grinding performance and durability.
- Robust and flexible carrier.



APPLICATIONS

For all basic, intermediate and final sanding applications in wood, paints and lacquers as well as metal material.



Dust-repellent stearate coating permanently prevents the abrasive surface from clogging.

Nylon velor backing for perfect disc adhesion on the hook and loop grinding disc.



UNIVERSAL ABRASIVE PAPER 230 x 280mm

FULL SHEETS



FEATURES

- High-quality aluminium oxide grains for a perfect surface finish.
- High-strength and flexible paper of the class C / D (110 - 130 g / m²).
- Stearate coating effectively reduces dust and colour particle clogging.



APPLICATIONS

For basic, intermediate and finish sanding in wood, paints and varnishes.



FOR USE WITH

Hand sanding.




MULTIPURPOSE PACKS

Cat. No.	Grain size	Pack Qty.
DT3230-QZ	40	10
DT3231-QZ	60	10
DT3232-QZ	80	10
DT3233-QZ	120	10
DT3234-QZ	180	10
DT3235-QZ	240	10
DT3236-QZ	320	10
DT3238-QZ	60	50
DT3239-QZ	80	50
DT3240-QZ	120	50
DT3241-QZ	180	50
DT3242-QZ	240	50

SUITABLE FOR

DeWALT®, AEG®, Bosch®, Atlas Copco®, Festool®, Elu®, Fein®, Hitachi®, Kress®, Makita®, Metabo®, Skil®




8-HOLE, Ø125mm PACKS

Cat. No.	Grain size	Pack Qty.
DT3101-QZ	40	10
DT3102-QZ	60	10
DT3103-QZ	80	10
DT3105-QZ	120	10
DT3106-QZ	180	10
DT3107-QZ	240	10
DT3108-QZ	320	10
DT3111-QZ	40	25
DT3112-QZ	60	25
DT3113-QZ	80	25
DT3115-QZ	120	25
DT3116-QZ	180	25
DT3117-QZ	240	25
DT3118-QZ	320	25

SUITABLE FOR

DeWALT®, Bosch®, Hitachi®, Metabo®, Peugeot®



6-HOLE, Ø150mm PACKS

Cat. No.	Grain size	Pack Qty.
DT3121-QZ	40	10
DT3122-QZ	60	10
DT3123-QZ	80	10
DT3125-QZ	120	10
DT3126-QZ	180	10
DT3127-QZ	240	10
DT3128-QZ	320	10
DT3131-QZ	40	25
DT3132-QZ	60	25
DT3133-QZ	80	25
DT3135-QZ	120	25
DT3136-QZ	180	25
DT3137-QZ	240	25
DT3138-QZ	320	25

SANDING SHEETS

ROS DRY WALL SANDER




FEATURES

- Heat resistant resin adhesive bond, ideal for power sanding.
- Tough, durable paper backing ensures longer disc life and performance.
- Stearate coating reduces clogging, excellent for softwoods and painted surfaces (grits 80 or greater).
- Quick fit nylon loop backing allows fast and easy disc changeover.



APPLICATIONS

For all stripping sanding and finishing tasks on wood, metal and painted surfaces.



Ø225mm PACKS

Cat. No.	Grain size	Pack Qty.
DT3164-QZ	60	10
DT3169-QZ	80	10
DT3179-QZ	100	10
DT3170-QZ	120	10



EXTREME[®] ORBITAL SANDING SHEETS



APPLICATIONS

For grinding and removal work as well as for deburring and de-rusting.

FOR USE WITH

Corded and cordless angle grinders.



125mm PACKS

Cat. No.	Grain size	Pack Qty.
DT3211-QZ	40	25
DT3212-QZ	60	25
DT3213-QZ	80	25



GRINDING AND POLISHING BACKING PLATES

FEATURES

- Thermoplastic backing pad supplied with flange locking nut.

APPLICATIONS

For use with angle grinder fibre discs for grinding and polishing backing pads.

FOR USE WITH

Corded and cordless angle grinders and polishers.



BACKING PAD - SINGLE PACKS

Cat. No.	Max. speed	Diameter mm	Bore	Pack Qty.
DT3610-QZ	13000 U/min	115	M14 (22.2)	1
DT3611-QZ	15000 U/min	125	M14 (22.2)	1
DT3612-QZ		178	M14 (22.2)	1

POLISHING BONNET



FEATURES

- Wool polishing bonnet.

APPLICATIONS

For high-gloss polishing of various materials such as painted surfaces, metal, stone, plastic, etc.

FOR USE WITH

Corded and cordless angle grinders and polishers.



SINGLE PACKS

Cat. No.	Description	Max. speed	Diameter mm	Pack Qty.
DT3621-QZ	Polishing bonnet	13000 U/min	125	1
DT3622-QZ	Polishing bonnet	15000 U/min	178	1
DT3568-QZ	Velcro wool bonnet		180	1

RANDOM ORBIT SANDING PLATTENS




FEATURES

- Hook and loop ROS sanding platten.

FOR USE WITH

DeWALT[®] Random Orbit Sanders.



SINGLE PACKS

Cat. No.	Description	Grain size	Pack Qty.
DT3600-QZ	For R/O Sander D26453 8-hole	125	1
DT3601-QZ	For R/O Sander DW443 6-hole	150	1

CORK HAND SANDING BLOCK



SINGLE PACK

Cat. No.	Description	Pack Qty.
DT3199-QZ	40 x 60 x 100mm	1



Industrial ceramic grain for improved performance and life

Type 29 design for grinding angles of 15-25 degrees

APPLICATIONS

For rust removal, grinding and cleaning of metal.

FOR USE WITH

XR FlexVolt, other corded and cordless angle grinders.



SINGLE PACKS

Cat. No.	Description	Diameter mm	Grit	Type	Material	Pack Qty.
DT99583-QZ	XR 125mm Flap Disc 40G	125	40	Type 29	INOX	1
DT99584-QZ	XR 125mm Flap Disc 60G	125	60	Type 29	INOX	1
DT99585-QZ	XR 125mm Flap Disc 80G	125	80	Type 29	INOX	1



EXTREME® FLAP DISCS



FEATURES

- Resistant, durable zirconium oxide grain
- Very robust and resistant, with very high removal rate
- Zirconium oxide grain allows a 3x faster material removal than conventional resin-bonded fibre discs
- Type 27 design for grinding angles of 0-15 degrees

APPLICATIONS

For rust removal, grinding and cleaning of metal.

FOR USE WITH

Corded and cordless angle grinders.



SINGLE PACKS

Cat. No.	Description	Diameter mm	Grit	Type	Material	Pack Qty.
DT30601-QZ	115mm x 22.2mm	115	40	Type 27, Flat		1
DT30611-QZ	115mm x 22.2mm	115	60	Type 27, Flat		1
DT30621-QZ	115mm x 22.2mm	115	80	Type 27, Flat		1
DT30622-QZ	125mm x 22.2mm	125	80	Type 27, Flat		1
DT30602-QZ	125mm x 22.2mm	125	40	Type 27, Flat		1
DT30612-QZ	125mm x 22.2mm	125	60	Type 27, Flat		1



STANDARD FLAP DISCS



FEATURES

- Resistant, durable zirconium oxide grain
- Very robust and resistant, with very high removal rate
- Type 27 design for grinding angles of 0-15 degrees
- Type 29 design for grinding angles of 15-25 degrees

APPLICATIONS

For rust removal, grinding and cleaning of metal.

FOR USE WITH

Corded and cordless angle grinders.



PACKS

Cat. No.	Diameter mm	Grit	Type	Pack Qty.
DT3255-QZ	115	36	Type 29, Angled	10
DT3256-QZ	115	60	Type 29, Angled	10
DT3257-QZ	115	80	Type 29, Angled	10
DT3258-QZ	115	120	Type 29, Angled	10
DT3265-QZ	125	36	Type 29, Angled	10
DT3266-QZ	125	60	Type 29, Angled	10
DT3267-QZ	125	80	Type 29, Angled	10
DT3268-QZ	125	120	Type 29, Angled	10
DT3292-QZ	115	36	Type 27, Flat	10
DT3293-QZ	115	60	Type 27, Flat	10
DT3294-QZ	115	80	Type 27, Flat	10
DT3295-QZ	115	120	Type 27, Flat	10
DT3308-QZ	125	36	Type 27, Flat	10
DT3309-QZ	125	60	Type 27, Flat	10
DT3310-QZ	125	80	Type 27, Flat	10



Bonded Abrasives

RECOMMENDED MATERIALS



CUTTING & GRINDING DISCS

Disc type

Application

- Metal/non-ferrous
- Brick/Concrete
- Aluminum
- Stainless steel/thin sheet

DISC COLOUR CODING

- 80 m/s
- 100 m/s
- 50 m/s

Max. speed (rpm)*

OSA no.

Safety symbols

Cat. No.

Disc diameter

Disc thickness

Bore diameter

Disc material

European norm

OSA-Logo

EAN

DT43260-XJ

EXTRME CUTTING

ALU

MAX RPM 13,300

80m/s

EN12413



AC46TBF

5 035048 084212 >

ABRASIVES IDENTIFICATION

DeWALT® uses an industry-recognised colour coding and marking system that helps the user to find the correct grinding disc for a particular application.

Other features such as, the speed, size and thickness of the disc, as well as the bore diameter must also be considered when selecting.



TYPES OF ABRASIVE GRAINS

ALUMINUM OXIDE

Tough durable grain used for cutting, grinding and finishing of metal in bonded abrasives, and metal, wood and coatings in coated abrasives

TREATED ALUMINUM OXIDE

Aluminum oxide grain with a coating that increases bond strength for harder longer lasting bonded abrasives

ZIRCONIA

Tough durable grain with fine crystal structure used for rugged stock removal of metal in bonded abrasives, and metal and wood in coated abrasives

CERAMIC

Tough durable grain with very fine crystal structure to create many more cutting edges in each grain. Used for the highest stock removal of metal in bonded and coated abrasives

SILICON CARBIDE

Very hard and brittle grain used on concrete and very soft or very hard metals in bonded abrasives, and for very fine finishing of metal and coatings in coated abrasives

DIAMOND

Very hard and durable grain for use in cutting and grinding concrete and metal

XR EXTREME RUNTIME CERAMIC BONDED DISCS OSA

INOX

XR EXTREME RUNTIME

DT99582-QZ

Ø125 x 1.1 x22.23mm

A60TBF

CERAMIC

AS1788.1-1987

EN12413

MAX RPM 12,250

80m/s

XR FLEX VOLT

Optimized for OptiSmart tool (Optimal pour l'OptiSmart) voir

MADE IN GERMANY

5 035048 542439 >

Industrial ceramic grain for improved performance and Life. Designed for cordless tools to maximise battery life and runtime. OSA accredited. Increased efficiency for maximum cordless run time. High density grain concentration for longer life. Sharper grain for aggressive and fast stock removal. Upto 4x life (vs High Performance bonded abrasive).



APPLICATIONS

For general metal grinding and cutting work on the stainless steel, ferrous and non-ferrous metals, including weld and surface preparation.

FOR USE WITH

XR FlexVolt, other corded and cordless angle grinders.

SINGLE PACK

Cat No.	Description	Diameter mm	Thickness mm	Bore mm	Type	Application	Pack Qty.
DT99582-QZ	Cutting Disc	125	1.1	22.23	1		1
DT99581-QZ	Cutting / Grinding Disc	125	3	22.23	27		1
DT99580-QZ	Grinding Disc	125	6	22.23	27		1



CHOP SAW DISC

APPLICATION
Cutting metal sections.



SINGLE PACK

Cat. No.	Description	Diameter mm	Thickness mm	Bore mm	Pack Qty
DT3450-QZ	Chop saw disc	355	3.0	22.2	1

GRINDING AND HONING WHEELS

FOR USE WITH
DeWALT® bench grinders.



PACKS

Cat. No.	Description	Diameter mm	Thickness mm	Bore mm	Pack Qty
DT3380-QZ	Silicon carbide	400	125	25	20
DT3385-QZ	White aluminium oxide	80	125	25	20

LOCKING GRINDER NUT

LOCKING GRINDER NUT

Cat. No.	Description
DT3559-QZ	M14 Locking Grinder Nut



WIRE BRUSHES



FEATURES

- Highly specified wire grades for optimum material removal
- High wire content for extra brush durability.



APPLICATIONS

Aggressive twist knot wire wheel and cup brushes for heavy duty cleaning work.

Crimped wire wheel and cup brushes for medium duty cleaning.

Wire wheel and cup brushes for multi purpose cleaning applications in hard to reach areas.

FOR USE WITH

Corded and cordless angle grinders.



TWIST KNOT WIRE WHEELS



For the toughest applications:
To remove stubborn paint, heavy rust, cleaning of welds, etc.



SINGLE PACKS

Cat. No.	Wire length mm	Diameter mm	Bore mm	Pack Qty.
DT3466-QZ	22	115	M14 (22.2)	1
DT3502-QZ	22	115	M14 (22.2)	1

CRIMPED WIRE CUP BRUSHES



For medium applications:
To remove paint, rust, deposits, surface remediation, deburring, etc.



SINGLE PACKS

Cat. No.	Wire length mm	Diameter mm	Bore mm	Pack Qty.
DT3480-QZ	19	65	M14 (22.2)	1
DT3488-QZ	23	75	M14 (22.2)	1
DT3489-QZ	26	100	M14 (22.2)	1

TWIST KNOT WIRE CUP BRUSHES



For the toughest cleaning work.




SINGLE PACKS

Cat. No.	Wire length mm	Diameter mm	Bore mm	Pack Qty.
DT3500-QZ	18	65	M14 (22.2)	1
DT3492-QZ	22	75	M14 (22.2)	1
DT3501-QZ	24	100	M14 (22.2)	1



Diamond Cutting, Grinding and Drilling Accessories

RECOMMENDED MATERIALS



<p>EXTREME Metal</p>	<p>EXTREME Diamond Edge</p>	<p>Diamond cups</p>
<p>For fast cutting of metals with extended blade life.</p>	<p>For metal cutting.</p>	<p>For finishing and preparation of concrete surfaces.</p>
<p>Professional cutting discs</p>	<p>High performance</p>	<p>Diamond core</p>
<p>For specific concrete, masonry and tile cutting applications.</p>	<p>For general cutting of masonry, concrete and tiles.</p>	<p>For wet and dry drilling of concrete and masonry walls and floors.</p>

EXTREME METAL CUTTING DISCS NEW

EXTREME DURABILITY
Up to 1000+ cuts per blade. 30X longer wheel life compared to bonded cut-off wheels*

BREAKTHROUGH DIAMOND TECHNOLOGY
Robust diamond edge segments prevents wear - the cutting depth of the blade is maintained providing better control and precision

SAFETY
Strong, solid steel body greatly reduces the risk of breakage

LESS DUST RESIDUE
Less wear compared to bonded abrasives ensures less dust residue and odour

1000+ CUTS
30X LONGER WHEEL LIFE
14,551 RPM MAX 80m/s
N000900

COMPLIES WITH AUSTRALIAN STANDARD AS 1788.1-1997. FLANGES MUST BE FITTED AS ILLUSTRATED BELOW.

DT40250
ø105 x 1.3 x 16mm
EN13236

Warning: Cutting wheels must be mounted correctly. Metal guards must be used on all machines. Danger: Do not exceed maximum safe speed. Flanges must be Min. 1/2 diameter of wheel.

11779


POINTE DE DIAMANT

BORDE DE DIAMANTE




APPLICATIONS

For a range of metals including steel, stainless steel, cast iron, rebar, sheet metal, aluminium and non-ferrous metals.



FOR USE WITH

Corded and cordless angle grinders and chop saws.



1000+ CUTS
30X LONGER WHEEL LIFE
(Diamond vs. Bonded Abrasive)*

*Average performance of Extreme Metal versus 115 x 1mm (Aluminium Oxide) Bonded Abrasive Cutting Disc in 25mm Carbon Steel Tube

SINGLE PACKS

Cat. No.	Ø mm	Bore mm	Segment thickness mm	Pack Qty.
DT40250-QZ	105	16	1.3mm	1
DT40251-QZ	115	22.23	1.3mm	1
DT40252-QZ	125	22.23	1.3mm	1
DT40253-QZ	150	22.23	1.3mm	1
DT40254-QZ	180	22.23	1.5mm	1
DT40255-QZ	230	22.23	1.5mm	1
DT40256-QZ	300	25.4	3.3mm	1
DT40257-QZ	355	25.4	3.3mm	1



EXTREME DIAMOND EDGE CHOP SAW BLADE FOR METAL



APPLICATIONS

Can be used in place of conventionally bonded cutting blades.

Can be used on all conventional machines that work with bonded cutting blades.

Ideal for cutting metal pipe/profile bundles.



FEATURES

- Innovative diamond technology with a 100 times longer service life than conventional cutting discs.
- Very robust, laser-welded diamond cutting blades with a balanced ratio of cutting speed and durability.
- 100 times longer durability than conventionally bonded cutting discs.
- Optimal working at 4,000 rpm.

FOR USE WITH

Metal cutting abrasive disc chop saws.



SINGLE PACK

Cat. No.	Diameter mm	Bore mm	Segment height mm	Segment thickness mm	Pack Qty.
DT3752-QZ	355	25.4	3	1.6	1



DIAMOND JOINTING DISCS



FEATURES

- Fast removal of mortar and masonry due to the twin wheel construction.
- Laser welded to disc body for tougher applications.



APPLICATIONS

For mortar raking and wall chasing.

FOR USE WITH

Corded and cordless 125mm angle grinders.

SINGLE PACK

Cat. No.	Diameter mm	Bore mm	Segment height mm	Segment thickness mm	Pack Qty.
DT3758-QZ	125	22.2	10	6.3	1
DT3757-QZ	125	22.2	10	6.3	1





LASER-WELDED DIAMOND CUTTING DISCS

PROFESSIONAL 1 UNIVERSAL BUILDING MATERIALS AND CONCRETE



FEATURES

- The best choice of diamond blade for fast, aggressive cuts in most standard construction materials.
- Segments laser welded to the core for use in tougher applications.



APPLICATIONS

For use in standard construction materials including concrete, brick, tiles and paving slabs.



FOR USE WITH

Corded and cordless angle grinders.
Diameter 115 - 230mm only for dry cutting.



SINGLE PACKS

Cat. No.	Diameter mm	Bore mm	Segment height mm	Segment thickness mm	Pack Qty.
DT3740-XJ	115	22.2	7.5	2	1
DT3741-XJ	125	22.2	7.5	2	1
DT3743-XJ	230	22.2	8.5	2.4	1



LASER-WELDED DIAMOND CUTTING DISCS

PROFESSIONAL 3 - HARD CONCRETE AND GRANITE



FEATURES

- Manufactured using 'Advanced Bond Technology' which increases blade productivity and operating life.
- A layer of pre-alloyed metal encloses the diamond creating.



APPLICATIONS

These blades achieve optimum speed of cut in granite, reinforced concrete and most construction materials.



FOR USE WITH

Corded and cordless angle grinders.



VERY HARD MATERIALS - SINGLE PACKS

Cat. No.	Diameter mm	Bore mm	Segment height mm	Segment thickness mm	Pack Qty.
DT3761-XJ	125	22.2	7.5	2	1
DT3763-XJ	230	22.2	8.5	2.8	1

PROFESSIONAL 2 - ABRASIVE MATERIALS AND CONCRETE



FEATURES

- High performance diamond blade providing a balanced combination of cut speed and durability in abrasive materials.
- Segments laser welded to the core for use in tougher applications.



APPLICATIONS

For use in abrasive materials including sandstone, concrete, concrete roof tiles, brick and breeze blocks.



FOR USE WITH

Corded and cordless angle grinders.
Diameter 230mm only for dry cutting.



SINGLE PACKS

Cat. No.	Diameter mm	Bore mm	Segment height mm	Segment thickness mm	Pack Qty.
DT3773-XJ	230	22.2	7.5	2.4	1

SINTERED DIAMOND CUTTING DISCS

PROFESSIONAL 4 - TILE & CERAMICS



FEATURES

- Diamond blade containing a high concentration of top quality diamonds with excellent cutting performance in extremely hard materials.
- Continuous rim sintered blade for fine finish and minimal chipping in tiles and ceramics.



APPLICATIONS

For porcelain tiles, floor and wall tiles, slate, concrete tiles, bricks, terracotta etc.



Not recommended for use on wet tile saws.



FOR USE WITH

Corded and cordless angle grinders.



SINGLE PACKS

Cat. No.	Diameter mm	Bore mm	Segment height mm	Segment thickness mm	Pack Qty.
DT3735-XJ	115	22.2	7	1.6	1
DT3736-XJ	125	22.2	7	1.6	1
DT3738-XJ	230	22.2	7	2.1	1



HIGH PERFORMANCE DIAMOND CUTTING DISCS

HIGH PERFORMANCE 2 - TURBO DISC UNIVERSAL CONCRETE



FEATURES

- "Turbo" cutting edge for fast clean cuts.

APPLICATIONS

For clean cuts in all masonry, concrete and tile materials.

FOR USE WITH

Corded and cordless angle grinders.



TURBO - SINGLE PACKS

Cat. No.*	Diameter mm	Bore mm	Segment height mm	Segment thickness mm	Pack Qty.
DT3702-QZ	115	22.2	7	2.1	1
DT3712-QZ	125	22.2	7	2.2	1
DT3722-QZ	180	22.2	7	2.4	1
DT3732-QZ	230	22.2	7	2.4	1



HIGH PERFORMANCE DIAMOND CUTTING DISCS

HIGH PERFORMANCE 1 - SEGMENTED DISC UNIVERSAL CONCRETE



FEATURES


- Fast cutting, segmented disc

APPLICATIONS

General construction material such as building blocks, paving blocks and concrete.

FOR USE WITH

Corded and cordless angle grinders.



SINGLE PACKS

Cat. No.	Diameter mm	Bore mm	Segment height mm	Segment thickness mm	Pack Qty.
DT3701-QZ	115	22.2	7	2.1	1
DT3711-QZ	125	22.2	7	2.2	1
DT3721-QZ	180	22.2	7	2.4	1
DT3731-QZ	230	22.2	7	2.4	1

HIGH PERFORMANCE 4 - CONTINUOUS RIM DIAMOND CUTTING DISC



APPLICATIONS

Clean cuts in tiles and ceramics materials.

FOR USE WITH

Corded and cordless angle grinders.



TURBO - SINGLE PACKS

Cat. No.*	Diameter mm	Bore mm	Segment height mm	Segment thickness mm	Pack Qty.
DT3703-QZ	115	22.2	5	1.6	1
DT3713-QZ	125	22.2	5	1.6	1
DT40206-QZ	180	22.2	5	?	1
DT40207-QZ	230	22.2	5	?	1



HIGH PERFORMANCE 1 - SEGMENTED WET OR DRY CUTTING DISCS



FEATURES

- Fast cutting segment diamond disc.

APPLICATIONS

For cutting concrete slabs and curb stones.

FOR USE WITH

Petrol disc cutters.



SINGLE PACKS

Cat. No.	Diameter mm	Bore mm	Segment height mm	Segment thickness mm	Pack Qty.
DT40212-QZ	300	25.4 / 20	10	?	1
DT40213-QZ	350	25.4 / 20	10	?	1

DIAMOND TILE CUTTING DISC



FEATURES

- Continuous rim for chip free cuts in tiles and ceramic tiles.

APPLICATIONS

For wet and dry cuts in hard materials such as ceramic tiles, stoneware, granite and marble.

FOR USE WITH

Portable tile saw DWC410.



SINGLE PACK

Cat. No.	Diameter mm	Bore mm	Segment height mm	Segment thickness mm	Pack Qty.
DT3715-QZ	110	20	8	1.6	1
DT3714-QZ	110	20	5	1.6	1

DIAMOND TILE CUTTING DISCS - STATIONARY SAWS

PROFESSIONAL 4 - STATIONARY



FEATURES

- Continuous rim for chip free cuts in tiles and ceramic tiles.

APPLICATIONS

For wet cuts in hard materials such as ceramic tiles, stoneware, granite and marble.

FOR USE WITH

Stationary tile saws



TURBO - SINGLE PACK

Cat. No.*	Diameter mm	Bore mm	Segment height mm	Segment thickness mm	Pack Qty.
DT3734-XJ	250	25.4	5	1.6	1
DT3733-XJ	250	25.4	8	1.6	1



EXTREME[®] DIAMOND GRINDING CUPS



FEATURES

- Robust diamond segments: turbo cup for fastest results, double cup for quick surface grinding and single cup for general surface grinding.

APPLICATIONS

For smoothing of concrete and masonry.

FOR USE WITH

Corded and cordless angle grinders and associate dust extraction guard.

SINGLE PACK

Cat. No.	Diameter mm	Shank	Segment height mm	Cup	Pack Qty.
DT3796-QZ	125	M14	6	Double	1
DT3797-QZ	125	M14	6	Turbo	1
DT3795-QZ	125	M14	5	Single	1



DIAMOND CUTTING BLADES - QUICK REFERENCE CHART



PROFESSIONAL			
Universal Construction materials Concrete	Abrasive materials Abrasive materials Concrete	Extreme hard materials Granite Concrete	Tiles Hard ceramics
1	2	3	4

HIGH PERFORMANCE		
Universal Construction material Concrete	Turbo Construction material Concrete	Tiling Hard ceramics
1	2	4

VERY ABRASIVE AND NOT COMPACT

Asphalt				
Fresh concrete				
Light bricks (Poroton®, Unipor®, Porotherm®, Argex®, Syporex®)	●	●		
Firebricks	●			
Slag stone	●	●		

MEDIUM ABRASIVE AND COMPACT

Terrazzo, granite	●	●		●
Cement fiber boards	●	●		●
Lightweight concrete	●	●		●
Clay brick (brick, tile)	●	●		●
Plasterboard	●	●		●
Natural stone, soft	●	●		●
Handform brick	●	●	●	●
Concrete roof tile	●	●	●	●
Sand-lime brick	●	●	●	●

ABRASIVE AND VERY COMPACT

Concrete with soft aggregates (industrial flooring)	●	●	●	
Medium hard sandstone	●	●	●	
Abrasive marble (crystalline)	●	●	●	
Hard-ceramics (clinker, bricks)	●	●	●	
Clay pipe, stoneware pipe	●	●		

MEDIUM HARD AND COMPACT

Natural slate	●	●	●	
Concrete (board and edging stones, blocks)	●	●	●	
Lightweight concrete (reinforced)	●	●	●	
Concrete with medium hard aggregates (industrial flooringwe)	●	●	●	
Treated concrete with medium-hard aggregates	●	●	●	
Hard sandstone	●	●	●	

HARD AND COMPACT

Hard marble	●		●	
Reinforced concrete (window sills)	●		●	
Treated concrete with hard aggregates (pebbles)	●		●	
Clinker, bricks brick	●		●	
Quartzite			●	
Hardbrand ceramics (clinker brick, brick), medium hard concrete			●	
Soft granite (black)			●	

VERY HARD

Light, reinforced concrete (with pebbles)			●	
Colorful granite			●	
Clinker			●	

OTHER

Soft tiles, terracotta				●
Hard tiles				●
Stoneware, porcelain				●
Mortar Joints (Facade Restoration)				●

KEY

● Especially suitable ● Suitable

EXTREME® WET DIAMOND CORE DRILLS

EXTERNAL THREAD FITMENT 1/2" BSP (MALE) - HARD MATERIALS



FEATURES

- Optimized diamond segment design for special applications in hard materials.
- Laser welded segments prevent segment breakouts during wet drilling.



APPLICATIONS

Standard R 1/2 "external thread adapter suitable for DeWALT® and other professional brands (used in connection with an adapter for machines with a different thread).



FOR USE WITH

Wet diamond drilling machines



SINGLE PACKS

Cat. No.	Diameter mm	Length mm	Segments	Pack Qty.
DT9737-QZ	30	350	1	1
DT9738-QZ	32	350	1	1

INTERNAL THREAD FITMENT 1 1/4" UNC (FEMALE) UNIVERSAL



FEATURES:

- Optimized diamond segment design allows the combination of high drilling speeds and long tool path in a variety of materials.
- Laser welded segments prevent segment breakouts during wet drilling.
- For universal and hard materials.



APPLICATIONS

Universal concrete materials



FOR USE WITH

Wet diamond drilling machines.



SINGLE PACKS

Cat. No.	Diameter mm	Length mm	No. of segments	Pack Qty.
DT9760-QZ	52	400	5	1
DT9761-QZ	60	400	6	1
DT9762-QZ	65	400	7	1
DT9763-QZ	72	400	7	1
DT9765-QZ	82	400	8	1
DT9766-QZ	91	400	9	1
DT9767-QZ	102	400	9	1
DT9769-QZ	112	400	10	1
DT9770-QZ	122	400	11	1
DT9771-QZ	127	400	11	1
DT9773-QZ	152	400	13	1
DT9774-QZ	162	400	13	1
DT9777-QZ	200	400	16	1

SINGLE PACKS

Cat. No.	Diameter mm	Length mm	Segments	Pack Qty.
DT9778-QZ	212	400	16	1
DT9780-QZ	250	400	17	1



WET DIAMOND CORE BITS

EXTERNAL THREAD FITMENT 1/2" BSP (MALE) - UNIVERSAL



FEATURES:

- Optimized diamond segment design allows the combination of high drilling speeds and long durability in a variety of materials.
- Laser welded segments prevent segment breakouts during wet drilling.
- For universal and hard materials.



APPLICATIONS

For use in a variety of concrete materials



FOR USE WITH

Wet diamond drilling machines.



SINGLE PACKS

Cat. No.	Diameter mm	Length mm	Segments	Pack Qty.
DT9710-QZ	25	350	1	1

EXTERNAL THREAD FITMENT 1/2" BSP (MALE) - UNIVERSAL



FEATURES:

- Optimized diamond segment design allows the combination of high drilling speeds and long tool paths in a variety of materials.
- Laser welded segments prevent segment breakouts during dry drilling.



APPLICATIONS:

For the dry drilling of clean holes with large diameter in concrete, masonry and stone.



FOR USE WITH

Diamond dry drilling machines.



SINGLE PACKS

Cat. No.*	Diameter mm	Length mm	Segments	Pack Qty.
DT3885-QZ	38	150	3	1
DT3886-QZ	48	150	4	1
DT3887-QZ	52	150	3	1
DT3888-QZ	60	150	3	1
DT3889-QZ	65	150	3	1
DT3892-QZ	82	150	4	1
DT3894-QZ	107	150	4	1
DT3896-QZ	127	150	5	1
DT3898-QZ	152	150	6	1

DOSENKER DIAMOND CORE BIT

APPLICATIONS

Users length of 62mm, equipment M16, for example, electrical installations wall mountings or boxes, etc. M16 shank (internal thread).

FOR USE WITH

Dry diamond drilling machines.

PACK

Cat. No.	Diameter mm	Length mm	Segments	Pack Qty.
DT3866-QZ	82	62	M16 IG	4

DIAMOND CORE BIT ACCESSORIES

ADAPTOR



SINGLE PACKS

Cat. No.	Adapter from	Adapter to	Wet/Dry	Pack Qty.
DT3815-QZ	SDS-plus®	G 1/2" AG	Dry	1

EXTENSION PIECE



SINGLE PACKS

Cat. No.	Adapter from	Adapter to	Length mm	Wet/Dry	Pack Qty.
DT3829-QZ	1 1/4" UNC IG	1 1/4" UNC AG	150	Wet	1
DT3839-QZ	1 1/4" UNC IG	1 1/4" UNC AG	300	Wet	1
DT3844-QZ	G 1/2" IG	G 1/2" AG	150	Dry	1

PILOT DRILL BIT



SINGLE PACK

Cat. No.	Length mm	Wet/Dry	Pack Qty.
DT3848-QZ	1	Dry	1

RECOMMENDED MATERIALS



Metal



Concrete



Wood




Reclaimed Wood
with Nails



Plasterboard



Plastic



Multi-Tool Accessories





MULTI-TOOL

SAW PACKS

Cat. No.	Description	Application	Pack Qty.
DT20701-QZ	BiM saw blade 43 x 30mm	Wood, wood with nails, plastics and plasterboard	1
DT20702-QZ	BiM-Titan Saw Blade 55 x 44mm	Wood, wood with nails, plastics and plasterboard	1
DT20703-QZ	BiM saw blade 67x 30mm	Hardwood. Suitable for plastics and plasterboard	1
DT20704-QZ	BiM saw blade 43 x 30mm	Fast cuts in wood, plastics and plasterboard. High cutting speed	1
DT20705-QZ	BiM saw blade 43 x 65mm	Fast cuts in wood, plastics and plasterboard. High cutting speed	1
DT20706-QZ	BiM detail saw blade 43 x 10mm	Cut-outs and recesses in wood, plastic and plasterboard	1
DT20707-QZ	Titanium metal saw blade 43x 30mm	Metal, wood, wood with nails, plastics and plasterboard	1
DT20708-QZ	BiM segment saw blade 100mm	Wood, wood with nails, plastics and plasterboard	1
DT20709-QZ	Titanium segment saw blade 100mm	Wood, wood with nails, plastics and plasterboard	1
DT20710-QZ	BiM segment saw blade 100mm, cranked	Flush cuts in wood, wood with nails, plastics and plasterboard	1
DT20711-QZ	Titanium segment saw blade 100mm, cranked	Wood, wood with nails, plastics and plasterboard	1
DT20740-QZ	Japanese saw blade 32mm HCS cut surfaces	Hardwood	1
DT20741-QZ	Japanese saw blade 64mm - HCS surfaces	Hardwood	1
DT20742-QZ	35mm (1-3/8") Carbide Blade	Longer lasting for better results in wood, cutting nails, light gauge metals, grout, plaster etc.	2
DT20743-QZ	35mm (1-3/8") Carbide Blade	Longer lasting for better results in wood, cutting nails, light gauge metals, grout, plaster etc.	1
DT20747-QZ	64mm (2-1/2") Bi Metal Wood w/Nails TiN	Wood, wood with nails, drywall, PVC. The titanium blade has longer life in wood & nails than the non-titanium version.	1
DT20748-QZ	64mm (2-1/2") Bi Metal Wood w/Nails	Wood, wood with nails, drywall, PVC	1



MULTI-TOOL



CUT/FILL/SCRAPE - SINGLE PACKS

Cat. No.	Description	Application	Pack Qty.
DT20712-QZ	Multi-material cutting blade 100mm	Cutting roof shingles, plastic, foam, rubber, cardboard, leather, carpet floor etc.	1
DT20714-QZ	Solid filler 52mm	Removing adhesive residues, carpeting, tile adhesive, mortar, concrete residues	1
DT20716-QZ	Flexible Scraper Blade 35mm	To remove silicone joints, soft carpet adhesive residues, paint residues	1
DT20749-QZ	Caulk Removing (Wide)	Caulk removal	1
DT20750-QZ	Rectangular Scraping (Flush)	Caulk removal in expansion joints	1
DT20751-QZ	Carbide Flush Cut Finger	Coarse sanding of fillers, tile adhesive, concrete, stone and wood.	1



TILE AND JOINTS PROCESSING - SINGLE PACKS

Cat. No.	Description	Application	Pack Qty.
DT20717-QZ	Hard metal Segment saw blade 95mm, 3mm cutting width	Milling fine tile joints and slits in plaster or similar materials.	1
DT20718-QZ	Carbide segment saw blade 95mm, 5mm cutting width	Cutting tile joints and cracks in plaster or similar materials. Carbide edged for extra toughness and durability in harder materials. Faster joint separating.	1
DT20719-QZ	Carbide rasp	Coarse grinding of tile adhesives, concrete, and wood. Optimized carbide grain size for effective material removal.	1
DT20739-QZ	Diamond saw blade 7 5x 60 mm, cutting width 2.4 mm	Tile joints and cracks in plaster or similar materials. Diamond edged for additional blade life and durability.	1
DT20745-QZ	Diamond Half Moon	Tile grout, cutting grooves in plaster, lightweight concrete, and similar construction materials	1
DT20746-QZ	Diamond Flush Cut	Tile grout, cutting grooves in plaster, lightweight concrete, and similar construction materials	1



SANDING PACKS

Cat. No.	Description	Application	Pack Qty.
DT20700-QZ	Sanding plate with suction	Sanding	1
DT3090-QZ	Triangular abrasive paper 93 x 93mm, K40	Sanding	10
DT3091-QZ	Triangular abrasive paper 93 x 93mm, K60	Sanding	10
DT3092-QZ	Triangular abrasive paper 93 x 93mm, K80	Sanding	10
DT3093-QZ	Triangular abrasive paper 93 x 93mm, K120	Sanding	10
DT3094-QZ	Triangular abrasive paper 93 x 93mm, K180	Sanding	10
DT3095-QZ	Triangular abrasive paper 93 x 93mm, K240	Sanding	10
DTM3092-QZ	EXTREME® triangle abrasive mesh 93 x 93mm, K80	Sanding	5
DTM3093-QZ	EXTREME® triangle abrasive mesh 93 x 93mm K120	Sanding	5
DTM3095-QZ	EXTREME® triangle abrasive mesh 93 x 93mm K240	Sanding	5



MULTI-TOOL ACCESSORIES



5 PIECE PACKS

Cat. No.	Description	Application	Pack Qty.
DT20723-QZ	DT20701 x5 Wood with Nails Blade 30 x 43mm	For use in wood, wood with nails, plastics and plasterboard	5
DT20724-QZ	DT20703 x5 Hardwood Blade 30 x 67mm	For use in hardwood. Suitable for plastics and plasterboard	5
DT20725-QZ	DT20704 x5 Fastcut Wood Blade 30 x 43mm	For fast cuts in wood, plastics and plasterboard. High cutting speed	5
DT20726-QZ	DT20706 x5 Wood Detail Blade 10 x 43mm	For cut-outs and recesses in wood, plastic and plasterboard	5
DT20727-QZ	DT20707-QZ x5 Titanium Metal Blade 30 x 43mm	For use in metal, wood, wood with nails, plastics and plasterboard	5
DT20728-QZ	DT20708-QZ x5 Semicircle Blade 100mm	For use in wood, wood with nails, plastics and plasterboard	5
DT20729-QZ	DT20710-QZ x5 Flush Cut Blade 100mm	Suitable for flush cuts in wood, wood with nails, plastics and plasterboard	5

SETS

Cat. No.	Description	Application	Pack Qty.
DT20713-QZ	3 Piece Multi-Tool Accessory Set DT20701 x1 / DT20706 x1 / DT20704 x1	Mixed applications	3
DT20715-QZ	5 Piece Multi-Tool Accessory Set DT20701 x2 / DT20704 x1 / DT20714 x1 / DT20711 x1	Mixed applications	5
DT20731-QZ	8 Piece Multi-Tool Accessory & Sanding Set DT20700 x1 / DT20701 x1 / DT20704 x1 / DT20705 x1 / DT20710 x1 Detail Sanding Paper x3 (60G, 80G, 120G)	Mixed applications	8

OSCILLATING BLADES - QUICK REFERENCE GUIDE



Cat No.	Wood	Wood with Nails	Drywall	PVC	Metal	Asphalt Roofing Shingles	Carpet	Cardboard	Vinyl Flooring	Foam Insulation	Tile	Adhesives Lacquers Sealants	Brick
DT20700	•		•	•									
DT20701	•	•	•	•									
DT20702	•	•	•	•									
DT20703	•		•	•									
DT20704	•		•	•									
DT20705	•		•	•									
DT20706	•		•	•									
DT20707					•								
DT20708	•	•	•	•									
DT20709	•	•	•	•									
DT20710	•	•	•	•									
DT20711	•	•	•	•									
DT20712						•	•	•	•	•			
DT20713	•	•	•	•									
DT20714												•	
DT20715	•	•	•	•								•	
DT20716												•	
DT20717											•		
DT20718											•		
DT20719												•	
DT20723	•	•	•	•									
DT20724	•		•	•									
DT20725	•		•	•									
DT20726	•		•	•									
DT20727					•								
DT20728	•	•	•	•									
DT20729	•	•	•	•									
DT20731	•	•	•	•								•	
DT20739											•		
DT20740	•		•	•									
DT20741	•		•	•									
DT20742	•	•	•	•	•							•	
DT20743	•	•	•	•	•							•	
DT20745			•								•		•
DT20746			•								•		
DT20747	•	•	•	•									
DT20748	•	•	•	•									
DT20749												•	
DT20750												•	
DT20751	•											•	•

NEW

MODULAR STORAGE & SETS SYSTEM

DESIGNED FOR **TSTAK™**



IMPROVED BIT HOLDER DESIGN FOR EASY ACCESS

STORAGE COMPATIBILITY FOR SITE, WORKSHOP AND VAN

INTERLOCKING SYSTEM WITH MODULAR EASY-FIT CASES AND CADDY

COMPACT AND VERSATILE



Sets



Screwdriving Sets



Drill Bit Sets



Hole Saw Sets



Blade Sets



TSTAK Drawer Compatible Sets



Router and Multi-tool Sets

SITE, VAN + WORKSHOP STORAGE

SCREWDRIVING SETS



SCREWDRIVER AND DRILL BIT SET

Cat. No.	Description	Application	Contents	Pack Quantity
DT9281-QZ	63pc Drill Drive Set with EXTREME [®] Masonry & EXTREME [®] 2 Metal drill bits	Screwdriving Masonry Drilling Metal Drilling	EXTREME [®] Masonry: 4, 5, 6 x2, 8 x2mm EXTREME [®] 2 Metal: 1.5, 2, 2.5, 3, 3.5, 4, 4.5, 5, 5.5, 6, 6.5, 7mm 25mm: PH1, PH2 x3, PH3, PZ1, PZ2 x23, PZ3, T15, T20 x2, T25 x3, T30, T40 50mm: PZ2, PH2, SL5.5, SL6.5 Magnetic bit tip holder and drive guide	63
DT9282-QZ	57pc Drill Drive Set with Brad Point & EXTREME [®] Flatwood drill bits	Screwdriving Wood Drilling	Brad Point: 3, 4, 5, 6, 8, 10, 12mm Flatwood: 12, 14, 16, 20, 22, 25mm 25mm: PH1, PH2 x2, PH3, PZ1, PZ2 x3, PZ3, T15, T20 x22, T25 x3, T30, T40 50mm: PZ2, PH2, SL5.5, SL6.5 Magnetic bit tip holder and drive guide	57
DT9283-QZ	69pc Drill Drive Set with EXTREME [®] SDS-plus [®] , EXTREME [®] 2 Metal, and EXTREME [®] Masonry drill bits	Screwdriving Masonry Drilling Metal Drilling	EXTREME [®] SDS-plus [®] : 6mm x 110, 6mm x 160mm x2, 8mm x 160mm x2, 10mm x 160mm x2 EXTREME [®] 2 Metal: 1.5, 2, 2.5, 3, 3.5, 4, 4.5, 5, 5.5, 6, 6.5, 7mm EXTREME [®] Masonry: 4, 5, 6 x2, 8 x2mm 25mm: PH1, PH2 x2, PH3, PZ1, PZ2 x3, PZ3, T15, T20 x22, T25 x3, T30, T40 50mm: PZ2, PH2, SL5.5, SL6.5 Magnetic bit tip holder and drive guide	69
DT9286-QZ	72pc Drill Drive Set with Masonry bits and HSS-G Metal drill bits	Screwdriving Masonry Drilling Metal Drilling	Masonry drill bits: 4, 5, 6 X2, 8 X2mm HSS-G Metal drill bits: 1, 1.5, 2, 2.5, 3, 3.2, 3.3, 3.5, 4, 4.2, 4.5, 4.8, 5, 5.5, 6, 6.5, 7, 7.5, 8, 10, 12mm 25mm: PH1, PH2 x2, PH3, PZ1, PZ2 x3, PZ3, T15, T20 x22, T25 x3, T30, T40 50mm: PZ2, PH2, SL5.5, SL6.5 Magnetic bit tip holder and drive guide	72

MASONRY CHISELLING SETS



SDS-max[®] CHISEL SET / SDS-plus[®] CHISEL SET

Cat. No.	Description	Type	Contents	Length (mm)	Pack Quantity
DT9000-QZ	2pc SDS-max [®] Flat & Pointed Chisel Set	SDS-max [®]	Point Chisel Flat Chisel	400	2
DT60330-QZ	3pc SDS-plus [®] Chisel Set	SDS-plus [®]	Point Chisel Flat Chisel 20mm x 250mm Flat Chisel 40mm x 250mm	250	7

MASONRY DRILLING SETS



XLR SDS-plus[®] - FULL HEAD CARBIDE

Cat. No.	Description	Type	Contents	Length (mm)	Pack Quantity
DT8976-QZ	7pc XLR SDS-plus [®] Drilling Set	XLR SDS-plus [®] FULL HEAD CARBIDE	XLR SDS-plus [®] FHC masonry drill bits: 5mm x 110mm, 6mm x 110mm, 6mm x 160mm, 8mm x 110mm, 8mm x 160mm, 10mm x 160mm, 12mm x 160mm	110 160	10
DT8977B-QZ	10pc XLR SDS-plus [®] Full Head Carbide Set	XLR SDS-plus [®] FULL HEAD CARBIDE	SDS-plus [®] Full Head Carbide masonry drill bits: 5mm x 110mm, 6mm x 110mm x2, 6mm x 160mm x2, 6.5mm x 160mm, 8mm x 160mm x2, 10mm x 160mm, 12mm x 160mm	110 160	10



EXTREME[®] 2 SDS-plus[®]

Cat. No.	Description	Type	Contents	Length (mm)	Pack Quantity
DT7935B-QZ	10pc SDS-plus [®] EXTREME [®] 2 Set	SDS-plus [®] EXTREME [®] 2	SDS-plus [®] EXTREME [®] DEWALT 2 masonry drill bits: 5mm x 110mm, 6mm x 110mm x2, 6mm x 160mm x2, 7mm x 160mm, 8mm x 160mm, 9mm x 160mm, 10mm x 160mm, 12mm x 160mm	110 160	4
DT9700-QZ	4pc SDS-plus [®] EXTREME [®] 2 Drilling Set	SDS-plus [®] EXTREME [®] 2		110 160	7
DT9701-QZ	7pc SDS-plus [®] EXTREME [®] 2 Drilling Set	SDS-plus [®] EXTREME [®] 2	SDS-plus [®] EXTREME [®] 2 masonry drill bits: 5mm x 110mm, 6mm x 110mm, 6mm x 160mm, 8mm x 110mm, 8mm x 160mm, 10mm x 160mm, 12mm x 160mm	110 160	4
DT9702-QZ	4pc SDS-plus [®] EXTREME [®] 2 Drilling Set	SDS-plus [®] EXTREME [®] 2	SDS-plus [®] EXTREME [®] 2 masonry drill bits: 5.5mm x 160mm, 7mm x 160mm, 8mm x 160mm, 10mm x 160mm	160	5
DT6956-QZ	5pc Drilling Set	SDS-plus [®] EXTREME [®]	Masonry drill bits: 4mm x 75mm, 5mm x 85mm, 6mm x 100mm, 8mm x 120mm, 10mm x 120mm	75 85 100 120	-
DT7940-QZ	10pc SDS-plus [®] EXTREME [®] Drilling Set	SDS-plus [®] EXTREME [®]	SDS-plus [®] EXTREME [®] masonry drill bits mm: 5mm x 160mm, 5.5mm x 160mm x3, 7mm x 160mm x3, 8mm x 160mm, 10mm x 160mm, 12mm x 160mm	160	8

SDS-plus[®] DRILLING SETS

Cat. No.	Description	Type	Contents	Length (mm)	Pack Quantity
DT60300-QZ	8pc SDS-plus [®] Drilling Set	SDS-plus [®]	SDS-plus [®] drill bits: 6mm x2, 7mm x2, 8mm x2, 10mm x2	160	5
DT60301-QZ	5pc SDS-plus [®] Drilling Set	SDS-plus [®]	SDS-plus [®] drill bits: 5mm x 110mm, 6mm x 110mm, 6mm x 160mm, 8mm x 160mm, 10mm x 160mm	110 160	6
DT60302-QZ	6pc SDS-plus [®] Drilling Set	SDS-plus [®]	SDS-plus [®] drill bits: 6mm x 160mm x2, 8mm x 160mm x2, 10mm x 160mm x2	160	3



MASONRY DRILLING SETS



XLR SDS-plus® - FULL HEAD CARBIDE

Cat. No.	Description	Type	Contents	Length (mm)	Pack Quantity
DT9398-QZ	5pc SDS-plus® Drilling Set (12 Set Counter Top Display)	SDS-plus®	SDS-plus® masonry drill bits: 5.5mm x 110mm x3, 7mm x 110mm x2	110	5
DT9399-QZ	5pc SDS-plus® Drilling Set (12 Set Counter Top Display)	SDS-plus®	SDS-plus® masonry drill bits: 5mm, 6mm x2, 8mm x2.	110	5
DT9670-QZ	15pc SDS-plus® Drill & Chisel Set in ALU case	SDS-plus®	11 x SDS-plus® masonry drill bits: 4mm x 110mm, 5mm x 110mm, 5.5mm x 110mm, 6mm x 110mm, 6mm x 160mm, 7mm x 110mm, 7mm x 160mm x2, 10mm x 160mm, 12 x 160mm, 14mm x 210mm 4 x SDS-plus® masonry chisels: Point Chisel 250mm Flat Chisel 20mm x 250mm Flat Chisel 40mm x 250mm	110 160 210 250	15
DT9679-QZ	15pc SDS-plus® Drill & Chisel Set in ALU case	SDS-plus®	11 x SDS-plus® masonry drill bits: 5mm x110mm, 5.5mm x 110mm, 6mm x 110mm, 6mm x 160mm, 7mm x 110mm, 8mm x 110mm, 8mm x 160mm, 10mm x 110mm, 10mm x 160mm, 12 x 160mm, 14mm x 210mm 4 x SDS-plus® masonry chisels: Point Chisel 250mm Flat Chisel 20mm x 250mm Flat Chisel 40mm x 250mm	110 160 210 250	15

HEX SHANK - MULTI MATERIAL / STRAIGHT SHANK - MASONRY

Cat. No.	Description	Type	Contents	Length (mm)	Pack Quantity
DT60099-QZ	5pc Multi-Material Drilling Set	Hex Shank	Multi-Material drill bits: 4, 5, 5.5, 6, 8mm	152	5
DT6952-QZ	5pc Drilling Set	Straight Shank	Masonry drill bits: 4mm x 75mm, 5mm x 85mm, 6mm x 100mm, 8mm x 120mm, 10mm x 120mm	75 85 100 120	5
DT9288-QZ	8pc Drilling Set	Straight Shank	Masonry drill bits: 3mm x 60mm, 4mm x 75mm, 5mm x 85mm, 6mm x 100mm, 7mm x 100mm, 8mm x 120mm, 9mm x 120mm, 10mm x 120mm	60 75 85 100 120	8



METAL DRILLING SETS



COBALT

Cat. No.	Description	Type	Contents	Pack Quantity
DT4956-QZ	6pc Cobalt Set	Cobalt	Cobalt metal drill bits: 2, 3, 4, 5, 6, 8mm	6
DT4957-QZ	29pc Cobalt Drilling Set	Cobalt	Cobalt metal drill bits: 1, 1.5, 2, 2.5, 3, 3.2, 3.3, 3.5, 4, 4.2, 4.5, 4.8, 5, 5.5, 6, 6.5, 7, 7.5, 8, 8.5, 9, 9.5, 10, 10.5, 11, 11.5, 12, 12.5, 13mm	29
DT5935-QZ	10pc Cobalt Drilling Set	Cobalt	Cobalt metal drill bits: 1, 2, 3, 4, 5mm x 86mm, 6mm x 93mm, 7mm x 109mm, 8mm x 117mm, 9mm x 125mm, 10mm x 133mm	10
DT5936-QZ	19pc Cobalt Drilling Set	Cobalt	Cobalt metal drill bits: 1, 1.5, 2, 2.5, 3, 3.5, 4, 4.5, 5mm x 86mm, 5.5mm x 93mm, 6mm x 93mm, 6.5mm x 101mm, 7mm x 109mm, 7.5mm x 109mm, 8mm x 117mm, 8.5mm x 117mm, 9mm x 125mm, 9.5mm x 125mm, 10mm x 133mm	19
DT4968-QZ	13pc Industrial Cobalt Set	Cobalt	Industrial Cobalt metal drill bits: 1.5, 2, 2.5, 3, 3.2, 3.5, 4, 4.5, 5, 5.5, 6, 6.5, 7mm	13

TITANIUM

Cat. No.	Description	Type	Contents	Pack Quantity
DT71916-QZ	29pc Titanium Drill Set in Tough Case (Imperial drill bit sizes)	Titanium	1/16" (1.6mm), 5/64" (2.0mm), 3/32" (2.4mm), 7/64" (2.8mm), 1/8" (3.2mm), 9/64" (3.6mm), 5/32" (4.0mm), 11/64" (4.4mm), 3/16" (4.8mm), 13/64" (5.2mm), 7/32" (5.6mm), 15/64" (6.0mm), 1/4" (6.4mm), 17/64" (6.7mm), 9/32" (7.1mm), 19/64" (7.5mm), 5/16" (7.9mm), 21/64" (8.3mm), 11/32" (8.7mm), 23/64" (9.1mm), 3/8" (9.5mm), 25/64" (9.9mm), 13/32" (10.3mm), 27/64" (10.7mm), 7/16" (11.1mm), 29/64" (11.5mm), 15/32" (11.9mm), 31/64" (12.3mm), 1/2" (12.7mm)	29
DT7914-QZ	14pc Titanium Drilling Set (Imperial Sizes)	Titanium	Titanium Metal drill bits: 1/16" (1.6mm) x2, 5/64" (2mm), 3/32" (2.4mm), 7/64" (2.8mm), 1/8" (3.2mm) x2, 9/64" (3.6mm), 5/32" (4mm), 3/16" (4.8mm), 1/4" (6.4mm), 5/16" (8mm), 3/8" (9.5mm), 1/2" (12.7)	14

EXTREME® 2

Cat. No.	Description	Type	Contents	Pack Quantity
DT7926-XJ	29pc EXTREME® 2 Drilling Set	EXTREME® 2	EXTREME® 2 Metal drill bits: 1, 1.5, 2, 2.5, 3, 3.2, 3.3, 3.5, 4, 4.2, 4.5, 4.8, 5, 5.5, 6, 6.5, 7, 7.5, 8, 8.5, 9, 9.5, 10, 10.5, 11, 11.5, 12, 12.5, 13mm	29



HSS-G

Cat. No.	Description	Type	Contents	Pack Quantity
DT5920-QZ	19pc HSS-G Drilling Set	HSS-G	HSS-G Metal drill bits: 1mm x2, 1.5mm x3, 2mm x3, 2.5 x2, 3, 3.5, 4, 4.5, 5, 5.5, 6, 6.5, 8mm	19
DT5921-QZ	10pc HSS-G Drilling Set	HSS-G	HSS-G Metal drill bits: 1, 2, 3, 4, 5, 6, 7, 8, 9, 10mm	10
DT5922-QZ	13pc HSS-G Drilling Set	HSS-G	HSS-G Metal drill bits: 1.5, 2, 2.5, 3, 3.2, 3.5, 4, 4.5, 5 x2, 5.5, 6, 6.5mm	13
DT5923-QZ	19pc HSS-G Drilling Set	HSS-G	HSS-G Metal drill bits: 1mm x 34mm, 1.5mm x 40mm, 2mm x 49mm, 2.5mm x 57mm, 3mm x 61mm, 3.5mm x 70mm, 4mm x 75mm, 4.5mm x 80mm, 5mm x 86mm, 5.5mm x 93mm, 6mm x 93mm, 6.5mm x 101mm, 7mm x 109mm, 7.5mm x 109mm, 8mm x 117mm, 8.5mm x 117mm, 9mm x 125mm, 9.5mm x 125mm, 10mm x 133mm	19
DT5929-QZ	29pc HSS-G Drilling Set	HSS-G	HSS-G Metal drill bits: 1, 1.5, 2, 2.5, 3, 3.2, 3.3, 3.5, 4, 4.2, 4.5, 4.8, 5, 5.5, 6, 6.5, 7, 7.5, 8, 8.5, 9, 9.5, 10, 10.5, 11, 11.5, 12, 12.5, 13mm	29

HSS-R

Cat. No.	Description	Type	Contents	Pack Quantity
DT5911-QZ	10pc HSS-R Drilling Set	HSS-R	HSS-R Metal drill bits: 1, 2, 3, 4, 5, 6, 7, 8, 9, 10mm.	10
DT5912-QZ	13pc HSS-R Drilling Set	HSS-R	HSS-R Metal drill bits: 1.5, 2, 2.5, 3, 3.2, 3.5, 4, 4.5, 5x2, 5.5, 6, 6.5mm	13
DT5913-QZ	19pc HSS-R Drilling Set	HSS-R	HSS-R Metal drill bits: 1, 1.5, 2, 2.5, 3, 3.5, 4, 4.5, 5, 5.5, 6, 6.5, 7, 7.5, 8, 8.5, 9, 9.5, 10mm	19
DT5930-QZ	29pc HSS-R Drilling Set	HSS-R	HSS-R Metal drill bits: 1, 1.5, 2, 2.5, 3, 3.2, 3.3, 3.5, 4, 4.2, 4.5, 4.8, 5, 5.5, 6, 6.5, 7, 7.5, 8, 8.5, 9, 9.5, 10, 10.5, 11, 11.5, 12, 12.5, 13mm	29
DT71701-QZ	21pc Black Oxide Metal Drill Set	HSS-R	HSS-R metal drill bits: 1, 1.5, 2, 2.5, 3, 3.2, 3.3, 3.5, 4, 4.2, 4.5, 4.8, 5, 5.5, 6, 6.5, 7, 7.5, 8, 10, 12mm	21



WOOD DRILL BIT SETS



EXTREME® IMPACT WOOD-MILLING DRILL

Cat. No.	Description	Length (mm)	Contents	Pack Quantity
DT7943B-QZ	8pc Flat Wood Set	152mm	Hex shank flat wood drill bits: 12, 16, 18, 20, 22, 25, 28, 32mm	8

HIGH PERFORMANCE

Cat. No.	Description	Length (mm)	Contents	Pack Quantity
DT4842-QZ	8pc Flat Wood Set	152mm	Hex shank flat wood drill bits: 12, 16, 18, 20, 22, 25, 28, 32mm (DT4812-QZ, DT4816-QZ, DT4818-QZ, DT4820-QZ, DT4822-QZ, DT4825-QZ, DT4828-QZ, DT4832-QZ)	8
DT4535-QZ	5pc Brad Point Set		Brad Point drill bits: 4, 5, 6, 8, 10mm	5



HOLE SAW SETS



EXTREME® 2X LIFE

Cat. No.	Description	Contents	Pack Quantity
DT8269L-QZ	11pc Plumbers Set	Diameters: 19, 22, 29, 38, 44, 51, 57mm Small Quick Change Mandrel Large Quick Change Mandrel Pilot drill bits x2	11
DT8270L-QZ	11pc General Purpose Set	Diameters: 22, 29, 35, 44, 51, 64, 68mm Small Quick Change Mandrel Large Quick Change Mandrel Pilot drill bits x2	11
DT8273L-QZ	11pc Electrician's Set	Diameters: 16, 20, 25, 32, 35, 51, 64mm Small Quick Change Mandrel Large Quick Change Mandrel Pilot drill bits x2	11

EXTREME® HM CARBIDE TEETH

Cat. No.	Description	Contents	Pack Quantity
DT8360-QZ	3pc Carbide Set	Diameters: 22, 29, 35mm (inc. replacement pilot drill bit DT8362-QZ)	3



HIGH PERFORMANCE

Cat. No.	Description	Contents	Pack Quantity
DT83001-QZ	13pc General Purpose Set	Diameters: 16, 19, 25, 32, 38, 44, 48, 51, 64mm Small Quick Change Mandrel Large Quick Change Mandrel Pilot drill bits x2	13
DT83002-QZ	11pc Electrician's Set	Diameters: 22, 29, 35, 38, 44, 51, 64mm Small Quick Change Mandrel Large Quick Change Mandrel Pilot drill bits x2	11
DT83003-QZ	11pc Electrician's Set	Diameters: 16, 20, 25, 32, 40, 51, 64mm Small Quick Change Mandrel Large Quick Change Mandrel Pilot drill bits x2	11
DT83004-QZ	11pc Electrician's Set	Diameters: 20, 25, 32, 35, 44, 51, 64mm Small Quick Change Mandrel Large Quick Change Mandrel Pilot drill bits x2	11



SCREWDRIVER BIT SETS



EXTREME® FLEXTORQ 25MM BITS - SMALL BULK STORAGE SETS

Cat. No.	Description	Bit Length (mm)	Contents	Pack Quantity
DT70555T-QZ	PH2	25mm	PH2 x25	25
DT70556T-QZ	PZ2	25mm	PZ2 x25	25
DT70557T-QZ	T20	25mm	T20 x25	25
DT70558T-QZ	T25	25mm	T25 x25	25
DT70618T-QZ	PZ2	25mm	PZ2 x15 Compact Magnetic Drive Guide	16
DT70621T-QZ	PZ2	25mm	PZ2 x25 Compact Magnetic Drive Guide	25
DT70522T-QZ	PZ2, T15, T20, T25	25mm	PZ2 x6, T15 x3, T20 x3, T25 x3 Compact Magnetic Drive Guide	16
DT70564T-QZ	PZ2	25mm	PZ2 x25 Compact Magnetic Drive Guide	26
DT70577T-QZ	PH2, PZ2, T10, T15, T20, T25	25mm	PH2 x3, PZ2 x3, T10 x2, T15, T20 x3, T25 x3 Compact Magnetic Drive Guide	16
DT70586T-QZ	PH2	25mm	PH2 x25	25

HIGH PERFORMANCE BITS - SMALL BULK STORAGE SETS

Cat. No.	Description	Bit Length (mm)	Contents	Pack Quantity
DP42-QZ	T20	25mm	T20 x25	25
DP43-QZ	T25	25mm	T25 x25	25
DP44-QZ	T30	25mm	T30 x25	25
DP73-QZ	PZ2	50mm	PZ2 x15	15
DT71521-QZ	PZ2	25mm	PZ2 x25	25
DT71522-QZ	PH2	25mm	PH2 x25	25
DT71706-QZ	PZ2	25mm	PZ2 x25 Bit Holder	25
DT71910-QZ	PH2	25mm	PH2 x25 Compact Magnetic Drive Guide	26
DT71911-QZ	SQ2	25mm	SQ2 x25 Compact Magnetic Drive Guide	26
DT71560-QZ	PZ2	25mm	PZ2 x25 Compact Magnetic Drive Guide	26
DT71511-QZ	PH2, PZ2, PZ3, T20, T25	25mm	PH2 x2, PZ2 x6, PZ3 x3, T20 x2, T25 x2 Compact Magnetic Drive Guide	16
DT71573-QZ	PH2, PZ2, PZ3, T20, T25	25mm	PH2 x2, PZ2 x2, PZ3, T20 x6, T25 x4 Compact Magnetic Drive Guide	16

25MM BITS FOR DRYWALL APPLICATIONS - SMALL BULK STORAGE SETS

Cat. No.	Description	Bit Length (mm)	Contents	Pack Quantity
DT7300-QZ	PR2	25mm	PR2 x25	25

SCREWDRIVER BIT SETS (CONTINUED)



EXTREME® IMPACT TORSION - 25MM BITS - SLIM POCKET CASE

Cat. No.	Description	Bit Length (mm)	Contents	Pack Quantity
DT70512T-QZ	14pc Set	25mm	25mm: PH1, PH2, PH3, PZ1, PZ2x3, PZ3, SL6, T20, T25, T30, Magnetic drive guides x2 (compact & longer version)	
DT70574T-QZ	14pc Set	25mm	25mm: PH1, PH2, T10, T15, T20x2, T25x2, T30, PZ1, PZ2, Magnetic drive guides x2 (compact & longer version)	



HIGH PERFORMANCE - 25MM BITS - SLIM POCKET CASE

Cat. No.	Description	Bit Length (mm)	Contents	Pack Quantity
DT7915-QZ	11pc Set	25mm	PZ1, PZ2, PZ3, PH1, PH2, PH3, SL4.5, SL5.5, SL6.5, SL8, Magnetic bit tip holder	11
DT7916-QZ	11pc Set	25mm	PZ1, PZ2, PZ3, PH1, PH2, PH3, T10, T15, T20, T25, Magnetic bit tip holder	11
DT7917-QZ	11pc Set - Torx	25mm	T7, T8, T9, T10, T15, T20, T25, T27, T30, T40, Magnetic bit tip holder	11
DT71570-QZ	14pc Set	25mm	25mm: PH1, PH2 x2, PZ2, T10, T15 x2, T20 x2, T25 x2, T30, Magnetic drive guides x2 (compact & longer version)	14
DT71502-QZ	14pc Set	25mm	25mm: PH1, PH2, PH3, PZ2 x3, PZ3, SL6, T15, T20, T25, T30, Magnetic drive guides x2 (compact & longer version)	14
DT71908-QZ	14pc Set	25mm	25mm: PH2 x4, SQ2 x4, T15, T20, T25, SL6, Magnetic drive guides x2 (compact & longer version)	14
DT71905-QZ	14pc Set	25mm	25mm: PH2 x4, SQ2 x4, T15, T20, T25, SL6, Magnetic drive guides x2 (compact & longer version)	14

SCREWDRIVER BIT and SOCKET SETS



EXTREME® IMPACT TORSION 25MM

Cat. No.	Description	Bit Length (mm)	Contents	Pack Quantity
DT70523T-QZ	32pc Set	25mm	PH1, PH2 x3, PH3, PZ1 x2, PZ2 x5, PZ3 x3, T10 x2, T15 x2, T20 x2, T25 x2, T27, T30, T40, SL6 x2, SL8, PR2 x2, Magnetic bit tip holder	32
DT70523TM-QZ	32pc Set	25mm	PH1, PH2 x3, PH3, PZ1 x2, PZ2 x5, PZ3 x3, T10 x2, T15 x2, T20 x2, T25 x2, T27, T30, T40, SL6 x2, SL8, PR2 x2, Magnetic bit tip holder	32
DT70560T-QZ	32pc Set	25mm	PH1, PH2 x5, PH3 x2, PZ1, PZ2 x10, PZ3 x3, T15, T20, T25 x2, T27, T30 x3, Adapter, Magnetic bit tip holder	32



SCREWDRIVER BIT and SOCKET SETS



HIGH PERFORMANCE 25mm

Cat. No.	Description	Bit Length (mm)	Contents	Pack Quantity
DT7969-QZ	32pc Set	25mm	PH1, PH2 x2, PH3, PZ1, PZ2 x2, PZ3, SL3, SL4, SL5, SL6.5, H3, H4, H5, H6, T10, T15, T20, T25, T27, T30, T40, T10H, T15H, T20H, T25H, T27H, T30H, T40H, Hex to 1/4" adapter, Magnetic bit tip holder	32
DT7969M-QZ	32pc Set	25mm	PH1, PH2 x2, PH3, PZ1, PZ2 x2, PZ3, SL3, SL4, SL5, SL6.5, H3, H4, H5, H6, T10, T15, T20, T25, T27, T30, T40, T10H, T15H, T20H, T25H, T27H, T30H, T40H, Hex to 1/4" adapter, Magnetic bit tip holder	32
DT71562-QZ	32pc Set	25mm	PZ1 x2, PZ2 x6, PZ3 x3, PH1, PH2 x6, PH3 x2, SL3, SL4, SL5, SL6, T15, T20, T25, T27, T30, T40, Hex to 1/4" adapter, Magnetic bit tip holder	32
DT7944-QZ	31pc Set	25mm	PZ1 x2, PZ2 x3, PZ3, PH1 x2, PH2 x2, PH3, SL4.5, SL5.5, SL6.5, T10 x2, T15 x2, T20 x2, T25 x2, T30 x2, T40 x2, Hex3, Hex4 x2, Hex5, Quick change magnetic bit tip holder	31
DT7944M-QZ	31pc Set	25mm	PZ1 x2, PZ2 x3, PZ3, PH1 x2, PH2 x2, PH3, SL4.5, SL5.5, SL6.5, T10 x2, T15 x2, T20 x2, T25 x2, T30 x2, T40 x2, Hex3, Hex4 x2, Hex5, Quick change magnetic bit tip holder	31



HIGH PERFORMANCE 25mm

Cat. No.	Description	Bit Length (mm)	Contents	Pack Quantity
DT71516-QZ	24pc Set	25mm	Sockets: 6, 7, 8, 10, 11, 13mm Ratchet 25mm: PZ1, PZ2, PZ3, PH1, PH2, PH3, T10, T15, T20, T25, T30, T40, Hex 4, Hex 5, Hex 6, adapter, Magnetic bit tip holder	24
DT71516M-QZ	24pc Set	25mm	Sockets: 6, 7, 8, 10, 11, 13mm Ratchet 25mm: PZ1, PZ2, PZ3, PH1, PH2, PH3, T10, T15, T20, T25, T30, T40, Hex 4, Hex 5, Hex 6, adapter, Magnetic bit tip holder	24



MIXED DRILL DRIVE SETS



HIGH PERFORMANCE

Cat. No.	Description	Bit Length (mm)	Contents	Pack Quantity
DT71565-QZ	36pc Drill Drive Set Double Sided Case	25mm 50mm	25mm: PZ0, PZ1, PZ2, PZ3, PH1, PH2, PH3, SL4, SL6. 50mm: PH0 x2, PH1 x2, PH2, PH3, PZ1 x2, PZ2 x2, PZ3, T10, T15, T20, SL4, SL6 x2, SL7.2 Masonry Drill Bit: 6mm HSS TIN drill bits: 2, 2.5, 3, 3.5, 4, 4.5, 5mm Bit tip holder	36
DT71567-QZ	16pc Drill Drive Set	25mm	Masonry drill bits: 5, 6, 8mm Titanium metal drill bits: 2, 3, 4, 5, 6mm 25mm screw driving bits: PZ1 x2, PZ2 x3, PZ3 x2 Bit tip holder	16

BIT TIP HOLDER and SCREWDRIVING BIT SETS



EXTREME® IMPACT TORSION

Cat. No.	Description	Bit Length (mm)	Contents	Pack Quantity
DT70518T-QZ	10pc with Pivoting Bit Tip Holder	25mm	25mm: PH2 x2, PZ2 x2, PZ3 x2, T15, T30, SL6 Pivoting bit tip holder	10
DT70578T-QZ	10pc with Pivoting Bit Tip Holder	25mm	25mm: PH2 x2, PZ2, T10, T15, T20 x2, T25, T30 Pivoting bit tip holder	10
DT70563T-QZ	4pc Set with 10X Magnetic Bit Holder	25mm	10X Magnetic Bit Tip Holder with removable sleeve 25mm: PZ2, PH2, T20.	4

HIGH PERFORMANCE

Cat. No.	Description	Bit Length (mm)	Contents	Pack Quantity
DT71514-QZ	6pc Set with Compact Rapid Load	25mm	25mm: PZ2, PZ3, T25 50mm: PZ2, T20 Compact rapid load bit holder	6



FLIP 'N' DRIVE QUICK CHANGE SYSTEM



QUICK-CHANGE SET

Cat. No.	Description	Bit Length (mm)	Contents	Pack Quantity
DT7612-XJ	10pc Countersink Flip & Drive Set	25mm	Countersink No 6, 8, 10, 12 countersink and pilot bits 25mm: PZ2 x2, PH2 x2 Allen Key	10

ATTACHMENT ACCESSORIES



EXTREME90° RIGHT ANGLE ATTACHMENT

Cat. No.	Description	Bit Length (mm)	Contents	Pack Quantity
DT71517T-QZ	10pc Right Angle Attachment Set	25mm	Impact Ready Right Angle Attachment 25mm: PZ2 x3, PH2 x2, T10, T15, T20, T25	10
DT70619T-QZ	10pc Right Angle Attachment Set	25mm	Impact Ready Right Angle Attachment 25mm: PZ2 x3, PH2 x2, T10, T15, T20, T25	10



IMPACT RIGHT ANGLE FLEXI SCREWDRIVING SHAFT

Cat. No.	Description	Bit Length (mm)	Contents	Pack Quantity
DT70621-QZ	Impact Right Angle Flexi Shaft	304mm	Impact Right Angle Flexi Shaft PH2 25mm	1

IMPACT SHEET SHEAR ATTACHMENT



FEATURES

- Extremely powerful: easily cuts up to 1.3mm in metal
- Faster in straight and curved sections vs. conventional hand-held sheet metal shears
- 500m cutting capacity in sheet metal, 360° rotating head

APPLICATIONS

For use in sheet metal (steel, stainless steel, titanium, zinc) panel sections, precision cuts, notches, sheet metal coverings and spiral pipes.

SINGLE PACK

Cat. No.	Description
DT70620-QZ	18ga Cutting Shear Attachment for Impact Drivers



MAGBOXES



EXTREME® IMPACT TORSION

Cat. No.	Description	Bit Length (mm)	Contents	Pack Quantity
DT7919T-QZ	15pc Set in Magnetic Box	25mm 50mm	25mm: PH1, PH2, PH3, PZ1, PZ2x2, PZ3, T20, T25 50mm: PH2, PH3 Socket Drivers mm: 7, 8, 10 Magnetic bit tip holder	15
DT7965T-QZ	20pc Set in Magnetic Box	25mm 50mm	25mm: PH1, PH2, PH3, PZ1, PZ2x2, PZ3, T20, T25 50mm: PH3 EXTREME® Impact Hex Shank Metal Drill Bits: 3mm, 4mm Socket Drivers mm: 7, 8, 10 Magnetic Bit Tip Holder	20
DT7967T-QZ	15pc Set in Magnetic Box - Torx	25mm 50mm	25mm: T10, T15, T20 x3, T25 x3, T30 50mm: T20, T25. Socket Drivers mm: 7, 8, 10. Magnetic bit tip holder	15



HIGH PERFORMANCE

Cat. No.	Description	Bit Length (mm)	Contents	Pack Quantity
DT7918-QZ	15pc Set in Magnetic Box	25mm 50mm	25mm: PH1, PH2, PH3, PZ1, PZ2 x2, PZ3, T20, T25. 50mm: PH2, PZ1. Socket Drivers: 7, 8, 10mm. Magnetic bit tip holder	15

EXTREME® FLEXTORQ SMALL TOUGHCASE™



Cat. No.	Description	Contents
DT70730T-QZ	25pc FLEXTORQ Screw Driving Set	Compact magnetic drive guide with torsion zone, Cleanable socket driver 8mm
	PH2 PZ2 PZ3 SL6 T20 T25 T30	
25mm		7 1 1 2 2 2
50mm	2	2 1
85mm	1	1

Cat. No.	Description	Contents
DT70731T-QZ	37pc FLEXTORQ Screw Driving Set	Compact magnetic drive guide with torsion zone, Aluminium magnetic sleeve
	PH1 PH2 PH3 PZ1 PZ2 PZ3 SL4-6 T20 T25 T25 Security	
25mm	1	3 1 2 8 3 1 1 1 1
50mm		2 1 5 1 1 1
85mm	1	1

Cat. No.	Description	Contents
DT70732T-QZ	37pc FLEXTORQ Screw Driving Set Tx	Compact magnetic drive guide with torsion zone, Aluminium magnetic sleeve
	PH1 PH2 PZ1 PZ2 T10 T15 T20 T25 T27 T30 T20 Security T25 Security	
25mm	1	1 1 2 3 5 4 1 1 1 1
50mm		1 1 2 3 3
85mm		1 1

Cat. No.	Description	Contents
DT70733T-QZ	38pc FLEXTORQ Set+Safety Glasses	Bit tip holder, 1/4" hex to 1/4" square adapter, 1/4" hex to 3/8" square adapter, Cleanable socket driver 8mm, Tinted safety glasses
	PH2 PH3 PZ2 PZ3 T10 T15 T20 T25 T30 T40	
25mm	1	1 1 1 3 4 8 6 2 1
50mm	1	1 1 1 1
85mm		1

Cat. No.	Description	Contents
DT70734T-QZ	29pc FLEXTORQ Screw Driving Set	Aluminium magnetic sleeve
	PH2 PZ2 PZ3 T10 T15 T20 T25 T27 T30 T20 Security T25 Security	
25mm		1 1 1 1 1 1 1
50mm	1	1 2 3 7 5 1
85mm		

Cat. No.	Description	Contents
DT70735T-QZ	25pc FLEXTORQ Drill Drive Set	Socket Drivers: 8mm, 10mm, Magnetic bit tip holder
	PH1 PH2 PH3 PZ2 T10 T15 T20 T25 T30	
25mm	1	1 1 1 1 1 5 3 1
50mm		1 1
Metal Drill Bits		3mm 4mm 5mm 6mm 8mm
Hex shank		1 1 1 1 1

Cat. No.	Description	Contents
DT70736TM-QZ	32pc FLEXTORQ Set+Mug	Cleanable socket driver 8mm, Compact rapid load bit holder
	PH2 PZ1 PZ2 PZ3 SL6 T15 T20 T25 T30	
25mm	1	2 8 2 1 1 2 3 2
50mm	1	2 1
85mm	1	2 1

Cat. No.	Description	Contents
DT70737T-QZ	31pc FLEXTORQ Screw Driving Set	31pc FLEXTORQ Screw Driving Set
	PH1 PH2 PH3 PZ1 PZ2 PZ3 T20 T25	
25mm	1	3 1 1 6 1 1 1
50mm	1	3 1 6 2 1 1

Cat. No.	Description	Contents
DT70738T-QZ	31pc FLEXTORQ Screw Driving Set	Magnetic bit tip holder with torsion zone
	PH2 PZ2 T10 T15 T20 T25 T30 T20 Security T25 Security	
25mm	1	1 1 4 3 1 5 2
50mm	1	1 2 6 4

Continued overleaf

EXTREME® FLEXTORQ SMALL TOUGHCASE™



Cat. No.	Description	Contents
DT70739T-QZ	31pc FLEXTORQ Screw Driving Set	Magnetic bit tip holder with torsion zone
	PH1 PH2 PH3 PZ1 PZ2 PZ3 T20 T25 T30	
25mm		2 1 1 7 1 1 1 1
50mm	1	3 1 7 1 1 1 1

Cat. No.	Description	Contents
DT70740T-QZ	38pc FLEXTORQ Set+Safety Glasses	Compact magnetic drive guide with torsion zone, 1/4" hex to 1/4" square adapter, 1/4" hex to 3/8" square adapter, Cleanable socket driver 8mm, Tinted safety glasses
	PH2 PH3 PZ1 PZ2 PZ3 SL6 SL6-8 T10 T15 T20 T25 T30	
25mm	3	2 1 11 3 1 1 1 1 1 1 2
50mm	1	3 1
85mm		1

Cat. No.	Description	Contents
DT70741T-QZ	32pc FLEXTORQ Drill Drive Set	Magnetic bit tip holder with torsion zone, Cleanable socket driver 8mm
	PH2 PH3 PZ1 PZ2 PZ3 SL6 T15 T20 T25 T30	
25mm	1	1 1 8 3 1 1 2 2 2
50mm		2 1
85mm	1	1
Metal Drill Bits		5mm 6mm 8mm
Hex shank		1 1 1

Cat. No.	Description	Contents
DT70742T-QZ	33pc FLEXTORQ Screw Driving Set	Socket Drivers: 8mm, 10mm, Compact magnetic drive guide with torsion zone
	PH1 PH2 PH3 PZ1 PZ2 PZ3 T10 T15 T20 T25 T30	
25mm	1	5 1 2 8 2 2 1 3 2 1
50mm		1 1

Cat. No.	Description	Contents
DT70743T-QZ	32pc FLEXTORQ Screw Driving Set	Cleanable socket driver 8mm, Magnetic bit tip holder with torsion zone
	PH2 PZ1 PZ2 PZ3 SL6 T15 T20 T25 T30	
25mm	2	1 7 2 1 2 2 3 2
50mm	1	1 1 1 1 1 1 1
85mm	1	1 1

Cat. No.	Description	Contents
DT70744T-QZ	25pc FLEXTORQ Screw Driving Set	Compact magnetic drive guide with torsion zone, Cleanable socket driver 8mm
	PH2 PZ2 PZ3 T10 T15 T20 T25 T30	
25mm	2	2 1 1 1 2 5 2
50mm	1	1 1 2 1 1
85mm		1 1

Cat. No.	Description	Contents
DT70745T-QZ	31pc FLEXTORQ Screw Driving Set Tx	Magnetic bit tip holder with torsion zone
	PH2 PZ2 T10 T15 T20 T25 T30 T20 Security T25 Security	
25mm	1	1 1 2 4 2 1 1 1
50mm	1	1 2 3 5 4

Cat. No.	Description	Contents
DT70746T-QZ	34pc FLEXTORQ Screw Driving Set	Aluminium magnetic sleeve
	PH1 PH2 PH3 PZ1 PZ2 PZ3 T20 T25	
25mm	1	2 1 5 2 1 1
50mm	1	2 1 10 2 2 1

Cat. No.	Description	Contents
DT70747T-QZ	32pc FLEXTORQ Screw Driving Set	Magnetic bit tip holder with torsion zone, Cleanable socket driver 10mm
	PH2 PZ1 PZ2 PZ3 T10 T15 T20 T25 T30	
25mm	1	1 2 1 2 8 5 2
50mm	1	1 1 1 2 2 1 1
85mm		1

Continued overleaf

EXTREME® FLEXTORQ SMALL TOUGHCASE™



Cat. No.	Description	Contents									
DT70748T-QZ	24pc FLEXTORQ Drill Drive Set										
	PH1	PH2	PH3	PZ1	PZ2	PZ3	T20	T25	T30		
25mm	1	2	1	1	4	1	2	1	1		
Metal Drill Bits	3mm	3.2mm	3.5mm	4mm	5mm	5.5mm	6mm	7mm	8mm	10mm	
Hex shank	1	1	1	1	1	1	1	1	1	1	1

Cat. No.	Description	Contents									
DT70749T-QZ	25pc FLEXTORQ Drill Drive Set	Compact magnetic drive guide with torsion zone									
	PH1	PH2	PH3	PZ1	PZ2	PZ3	T20				
25mm	1	5	1	1	6	1					
50mm		1			2		1				
Metal Drill Bits	3mm	4mm	5mm	6mm	8mm						
Hex shank	1	1	1	1	1						

HIGH PERFORMANCE - MIXED SCREWDRIVING SETS



SMALL TOUGHCASE™ SETS

Cat. No.	Description	Contents										
DT70700-QZ	40pc Screw Driving Set+Gloves	Socket Drivers: 8mm, 10mm, Compact magnetic drive guide										
	PH1	PH2	PH3	PZ2	PZ3	T10	T15	T20	T25	T30		
25mm	1	2	2	6	4	1	2		2	1		
50mm	1	2	3	3	1	1	1	3	2	2		
85mm	1		1									

Cat. No.	Description	Contents										
DT70702-QZ	40pc Screw Driving Set	Socket Drivers: 8mm, 10mm, Compact magnetic drive guide										
	PH1	PH2	PH3	PZ2	PZ3	T10	T15	T20	T25	T30		
25mm	1	2	2	6	3	1	2		2	2		
50mm	1	2	4	4	1	1	1	2	2	2		
85mm	1		1									

Cat. No.	Description	Contents															
DT70703-QZ	47pc Screw Driving Set+Safety Glasses	Bit tip holder, Tinted Safety Glasses															
	PH1	PH2	PH3	PZ1	PZ2	PZ3	T20	T25	T30	SL6	T10 Security	T15 Security	T20 Security	T25 Security	T30 Security	T40 Security	
25mm	1	5	2	3	14	5	1	2	2	1	1	1	1	1	1	1	
50mm	1			1	1		1										

Cat. No.	Description	Contents														
DT70704-QZ	47pc Screw Driving Set+Safety Glasses Tx	1/4" hex to 1/4" square adapter, 1/4" hex to 3/8" square adapter, Bit tip holder, Tinted Safety Glasses														
	PH1	PH2	PZ1	PZ2	T10	T15	T20	T25	T30	T40	T10 Security	T15 Security	T20 Security	T25 Security	T30 Security	
25mm	1	1	1	1	4	4	6	8	3	3	1	1	2	2	2	
50mm				1			1	1	1							

Cat. No.	Description	Contents											
DT70705-QZ	40pc Screw Driving Set Tx	Socket Drivers: 8mm, 10mm, Compact magnetic drive guide											
	PH1	PH2	PH3	PZ1	PZ2	PZ3	T10	T15	T20	T25	T30	SL6	
25mm	1	2	1	2	2	2	2	2	3	3	2	1	
50mm	1	2		1	2		1	1	3	3	2		



HIGH PERFORMANCE - MIXED SCREWDRIVING SETS



SMALL TOUGHCASE™ SETS

Cat. No.	Description	Contents						
DT70706M-QZ	25pc Drill Drive Set+Mug	Socket Driver 10mm, Compact magnetic drive guide, Thermal mug						
	PH2	PZ2	PZ3	T10	T15	T20	T25	T30
25mm	2	5	2	1	1	1	2	1
50mm	1	1	1				1	
Metal Drill Bits	3mm	4mm	5mm	6mm				
Hex shank	1	1	1	1				

Cat. No.	Description	Contents						
DT70707-QZ	25pc Drill Drive Set+Mug	Socket Driver 10mm, Compact magnetic drive guide, Thermal mug						
	PH2	PZ2	PZ3	T10	T15	T20	T25	T30
25mm	2	5	2	1	1	1	2	1
50mm	1	1	1				1	
Metal Drill Bits	3mm	4mm	5mm	6mm				
Hex shank	1	1	1	1				

Cat. No.	Description	Contents						
DT70708-QZ	25pc Drill Drive Set	Compact rapid load bit holder, Compact magnetic drive guide						
	PH2	PZ2	PZ3	T10	T15	T20	T25	T30
25mm	2	5	2	1	1	1	2	1
50mm	1	1					1	1
Metal Drill Bits	3mm	4mm	5mm	6mm				
Hex shank	1	1	1	1				

Cat. No.	Description	Contents													
DT70709-QZ	33pc Screw Driving Set	Compact magnetic drive guide, Magnetic bit holder													
	PH1	PH2	PH3	PZ1	PZ2	PZ3	T10	T15	T20	T25	T30	T40	SL5.5	SL8	
25mm	1	4	1	1	6	3	1	1	1	4	2	1	1	1	
50mm		1			1				1						

Cat. No.	Description	Contents												
DT70710-QZ	13pc Extreme 2 Metal Drilling Set	Bit tip holder, Tinted Safety Glasses												
Metal Drill Bits	1.5mm	2mm	2.5mm	3mm	3.2mm	3.5mm	4mm	4.5mm	5mm	5.5mm	6mm	6.5mm	7mm	
Extreme 2 Metal	1	1	1	1	1	1	1	1	1	1	1	1	1	

Cat. No.	Description	Contents						
DT70711-QZ	19pc Extreme 2 Metal Drill Drive Set	Compact magnetic drive guide, Magnetic bit holder						
	PH2	PZ2	PZ3					
25mm	3	4		1				
50mm	1	2						
Metal Drill Bits	2mm	3mm	4mm	5mm	6mm	8mm		
Extreme 2 Metal	1	1	1	1	1	1		

Cat. No.	Description	Contents						
DT70712-QZ	19pc Extreme Masonry Drill Drive Set	Compact magnetic drive guide, Magnetic bit holder						
	PH2	PZ2	T25					
25mm	3	4	1					
50mm	1	1	1					
Masonry drill bits	4mm	5mm	5.5mm	6mm	7mm	8mm		
Extreme Masonry	1	1	1	1	1	1		

Cat. No.	Description	Contents						
DT70713-QZ	67pc Drill Drive Set (ANZ)	Compact magnetic drive guide, Pocket case, 2 x small bulk storage cases						
	PH2	SQ2	SL6	H5	T15	T20	T25	
25mm	24	22	2	2	2	2	2	
50mm	2	1					1	
Metal drill bits	4.5mm	5mm	5.5mm	6mm	6.5mm	7mm		
HSS-G Metal	1	1	1	1	1	1		

HIGH PERFORMANCE - MIXED SCREWDRIVING SETS



SMALL TOUGHCASE™ SETS

Cat. No.	Description	Contents
DT70714-QZ	40pc Screw Driving Set (ANZ)	Socket Driver 3/8", Socket Driver 5/16", Compact magnetic drive guide
	PH1 PH2 PH3 SQ2 SL6 SL8 H4 H5 T10 T15 T20 T25	
25mm	1 6 1 3 1 1 2 2 1 1 1 1	
50mm	5 4 1 1 1 1 1 1 1 1 1 1	
85mm	1 1 1 1 1 1 1 1 1 1 1 1	

Cat. No.	Description	Contents
DT70715-QZ	40pc Screw Driving Set (ANZ)	Socket Driver 3/8", Socket Driver 5/16", Compact magnetic drive guide
	PH2 SQ2 SL6 H5 T15 T20 T25	
25mm	6 6 1 3 1 2 2	
50mm	6 6 1 1 1 1 1	
85mm	1 1 1 1 1 1 1	

Cat. No.	Description	Contents
DT50050-QZ	10pc Impact Titanium Drill Bit Set	Bit tip holder, Tinted Safety Glasses
Metal drill bits	3mm 3.2mm 3.5mm 4mm 4.5mm 5mm 6mm 8mm 10mm 12mm	
Impact Titanium	1 1 1 1 1 1 1 1 1 1 1	



NEW



TSTAK CADDY

Securely stores small bulk storage sets and small Toughcases™. Works as a carry case and compatible with the TSTAK® storage system for easy in-van and workshop storage.

DT70716-QZ

MEDIUM MIXED SETS

HIGH PERFORMANCE MEDIUM TOUGHCASE™

Cat. No.	Description	Bit Length (mm)	Contents	Pack Quantity
DT71501-QZ	56pc Drill Drive Set inc. PZ2 x25 pocket storage case	Screwdriving Metal Drilling Wood Drilling Socket / Nut Driving	HSS-G metal drill bits: 3, 4, 5, 6, 8, 10, 12mm Flat wood: 14, 20mm 25mm: PH1 x2, PH2 x2, SL6, SL8, PZ2 x25, PZ3 x2, T10 x3, T20 x3, T25 x2, T30 x2 Adapters: 1/4 to 1/4 square, 1/4 to 3/8 square Socket Drivers: 8, 10mm	56

DT7938B-QZ	36pc EXTREME® 2 METAL Drilling Set	Screwdriving Metal Drilling	EXTREME® 2 Metal drill bits: 1, 1.5, 2, 2.5, 3, 3.2, 3.3, 3.5, 4, 4.2, 4.5, 4.8, 5, 5.5, 6, 6.5, 7, 7.5, 8, 10, 12mm 25mm: PZ1, PZ2 x2, PZ3, PH1, PH2, PH3, T20, T25 50mm: PH2, PZ2 70mm: T20, T25 Magnetic bit holder Compact magnetic drive guide	67
-------------------	------------------------------------	--------------------------------	--	----

DT7939-QZ	39pc SDS-plus® Drill Drive Set	Screwdriving Masonry Drilling Socket Driving	SDS-plus® EXTREME® drill bits mm: 5mm x 160mm, 5.5mm x 160mm, 6mm x 160mm, 7mm x 160mm, 8mm x 160mm 25mm: PZ1 x2, PZ2 x2, PZ3, PH1, PH2 x2, PH3, T10, T15, T20, T25, T30, T40, SL4.5, SL5.5, SL6.5 50mm: PZ1 x2, PZ2 x2, PZ3, PH1 x2, PH2 x2, PH3 70mm: T20, T25, T30 Socket Drivers: 7mm, 8mm Magnetic bit holder	39
------------------	--------------------------------	--	---	----



LARGE MIXED SETS

LARGE MIXED SETS

Cat. No.	Description	Bit Length (mm)	Contents	Pack Quantity
DT71563-QZ	100pc Drill Drive set	Screwdriving Masonry Drilling Metal Drilling Wood Drilling Socket / Nut Driving	Brad point drill bits: 3 x2, 3.5, 4, 4.5, 5 x2, 5.5, 6, 6.5, 7, 7.5, 8mm Metal drill bits: 1.5, 2, 2.5, 3x2, 3.5, 4, 4.5, 5, 5.5, 6, 6.5mm Masonry drill bits: 6, 7, 8mm 25mm: PH1x2, PH2x2, PH3x2, PZ1, PZ2x28, PZ3 x2, SL4, SL5, SL7.2, T15, T20, T25, T30, T40, H4, H5, H6, H7 50mm: PH1, PH2x2, PH3, PZ1, PZ2x2, PZ3, SL5, SL6, SL7.2 Socket Drivers 5, 6, 8, 10, 11, 12, 13mm Hole Saws 32, 44mm Hole Saw Mandrel and Pilot Drill Bit Magnetic bit tip holder Countersink	100

DT71566-QZ	100pc Drill Drive set	Screwdriving Masonry Drilling Metal Drilling Wood Drilling Socket / Nut Driving	Brad point drill bits: 3, 4, 5, 6, 8mm Metal drill bits: 1.5, 2, 2.5, 3 x2, 3.5, 4, 4.5, 5, 5.5, 6, 6.5mm Masonry drill bits: 5, 5.5, 6, 7, 8, 10, 12mm 25mm: PH1 x2, PH2 x2, PH3 x2, PZ1, PZ2 x33, PZ3, SL4, SL5, SL7.2, T15, T20, T25, T30, T40, H4, H5, H6, H7 50mm screw driver bits PH1, PH2x2, PH3, PZ1, PZ2x6, PZ3, SL5, SL6, SL7.2 Socket Drivers 6, 8, 10mm Hole Saws: 32, 44mm Hole Saw Mandrel and Pilot Drill Bit Magnetic bit tip holder Countersink	100
-------------------	-----------------------	---	--	-----

DT7981-QZ	98pc Drill Drive Set - Roll Mat	Screwdriving Masonry Drilling Metal Drilling Wood Drilling Socket / Nut Driving	Brad point drill bits: 3, 3.2, 3.5, 4, 4.5, 4.8, 5, 5.5, 6, 6.5, 7, 7.5, 8mm Masonry drill bits: 3, 5.5, 6, 7, 8, 10mm HSS Tin drill bits: 1.5, 2, 2.5, 3, 3.2, 3.5, 4, 4.5, 4.8, 5, 5.5, 6, 6.5mm 25mm: Ph0 x2, Ph1 x2, Ph2 x3, Ph3 x2, Pz0 x2, Pz1 x3, Pz2 x4, Pz3 x2, SL4, SL5 x2, SL6, SL7.2, SQ1, SQ2, SQ3, Hex 3, Hex4 x2, Hex5 x2, Hex6, T10, T15, T20, T25, T27, T30 50mm: Ph0, Ph1, Ph2, Ph3, Pz1, Pz2 x2, Pz3, T10, T15, T20, SL4, SL6, SL7.2 Socket Drivers: 5, 6, 7, 8, 9, 10, 11, 12, 13mm Magnetic bit tip holder Countersink	98
------------------	---------------------------------	---	--	----



EXTREME® LARGE MIXED SETS

EXTREME® IMPACT TORSION - FIT TSTAK IV DRAWER

Cat. No.	Description	Bit Length (mm)	Contents	Pack Quantity
DT70620T-QZ	100pc Drill Drive set Compatible with TSTAK IV drawer	Screwdriving Masonry Drilling Metal Drilling Wood Drilling Socket / Nut Driving	Masonry drill bits: 4, 5, 6 x2, 7, 8 x2mm Metal drill bits: 1.5, 2, 2.5, 3, 3.5, 4, 4.5, 5, 5.5, 6, 6.5, 7mm 25mm: PZ1, PZ2 x30, PZ3, PH1 x2, PH2 x27, PH3, T15, T20 x2, T25, T30, SL4/6 x2, SL6/8 x2 Socket Drivers: 6, 8, 10mm Cleanable Socket Driver: 8mm Hole Saws: 32, 38, 44, 54mm Hole Saw Mandrel and Pilot Drill Bit Pivoting Bit Tip Holder	100

HIGH PERFORMANCE - FIT TSTAK IV DRAWER

Cat. No.	Description	Bit Length (mm)	Contents	Pack Quantity
DT71583-QZ	102pc Drill Drive Set Compatible with TSTAK IV drawer	Screwdriving Masonry Drilling Metal Drilling Wood Drilling Socket / Nut Driving	Masonry drill bits: 5.5 x2, 6 x2, 7 x2, 8 x2, 10 x2mm HSS black metal drill bits: 1.5, 2, 2.5, 3, 3.5, 4, 4.5, 5, 5.5, 6, 6.5, 7mm 25mm: PZ1 x2, PZ2 x23, PZ3 x2, PH1 x2, PH2 x23, PH3, SL4, SL5, SL6, SL7.2, T10 x2, T15 x2, T20 x2, T25 x2, T27 x2, T30 x2 Socket Drivers: 5, 6, 7, 8, 10mm Hole Saws: 32, 38, 44, 54mm Hole Saw Mandrel and Pilot Drill Bit Magnetic bit tip holder	102
DT71569-QZ	100pc Drill Drive set Compatible with TSTAK IV drawer	Screwdriving Masonry Drilling Metal Drilling Wood Drilling Socket / Nut Driving	Masonry drill bits: 4, 5, 5.5, 6 x2, 8 x2, 10mm. HSS black metal drill bits: 1.5, 2, 2.5, 3, 3.5, 4, 4.5, 5, 5.5, 6, 6.5, 7mm. 25mm: PZ1 x2, PZ2 x29, PZ3 x2, PH1 x2, PH2 x2, PH3, SL4, SL5, SL6, SL7.2, T10 x2, T15 x2, T20 x2, T25 x2, T27 x2, T30 x2. 50mm: PZ2 x15 Socket Drivers: 5, 6, 7, 8, 10mm Hole Saws: 32, 38, 44, 54mm Hole Saw Mandrel and Pilot Drill Bit Magnetic bit tip holder	100




JIGSAW BLADE SETS



JIGSAW BLADES

Cat. No.	Description	Application	Contents	Pack Quantity
DT2290-QZ	10pc Wood Cutting Set	Wood Cutting	DT2050, DT2165 x2, DT2168, DT2166 x2, DT2075 x2, DT2177 x2 (Bosch equivalent T101B, T119B0, T101A0, T111C, T144D, T144DP)	10
DT2292-QZ	10pc Metal Cutting Set	Metal Cutting	DT2054, DT2160 x3, DT2161 x2, DT2163 x2, DT2172 x2 (Bosch equivalent T118A, T118G, T118E0F, T118B, T127D)	10
DT2294-QZ	10pc Wood / Metal Cutting Set	Wood / Metal Cutting	DT2050 x2, DT2160 x2, DT2163 x2, DT2165 x2, DT2177 x2 (Bosch equivalent T101B, T119B0, T127D, T111C, T118A)	10
DT2296-QZ	10pc Wood Cutting Set	Wood Cutting	DT2205 x2, DT2209 x2, DT2213 x2, DT2216, DT2217, DT2218, DT2220	10
DT2298-QZ	14pc Wood Cutting Set	Wood Cutting	DT2205 x3, DT2209 x3, DT2213 x3, DT2216 x2, DT2217, DT2218, DT2220	14

RECIPROCATING SAW BLADE SETS



EXTREME® RUNTIME OPTIMISED FOR FLEXVOLT TOOLS

Cat. No.	Description	Application	Contents	Pack Quantity
DT99551-QZ	8pc XR Flexvolt Set + storage case	Mixed applications Wood Metal	DT99552-QZ (203mm) DT99553-QZ x3 (152mm) DT99554-QZ x3 (152mm) DT99555-QZ (230mm)	8
DT99550-QZ	13pc XR Flexvolt Set + storage case	Mixed applications Wood Metal	DT99552-QZ x2 (203mm) DT99553-QZ x4 (152mm) DT99554-QZ x5 (152mm) DT99555-QZ x2 (230mm)	13

EXTREME® 2X LIFE TOOLS

Cat. No.	Description	Application	Contents	Pack Quantity
DT2440L-QZ	6pc Set + storage case	Mixed applications Wood Metal	DT2300L-QZ (152mm) DT2307L-QZ (228mm) DT2315L-QZ (100mm) DT2301L-QZ (152mm) DT2308L-QZ (228mm) DT2407L-QZ (152mm)	6
DT2443L-QZ	8pc Set + storage case	Mixed applications Wood Metal	DT2300L-QZ x3 (152mm) DT2308L-QZ (228mm) DT2407L-QZ x3 (152mm) DT2408L-QZ (203mm)	8
DT2441L-QZ	12pc Set + storage case	Mixed applications Wood Metal	DT2300L-QZ x2 (152mm) DT2307L-QZ x2 (228mm) DT2315L-QZ x2 (100mm) DT2301L-QZ x2 (152mm) DT2308L-QZ x2 (228mm) DT2407L-QZ (152mm) DT2408L-QZ (203mm)	12

BREAK-AWAY RECIP BLADES

Cat. No.	Description	Application	Contents	Pack Quantity
DT2446-QZ	8pc Break-Away Recip Blade Set + storage case	Metal Cutting	DT2416-QZ x2 (228mm) DT2417-QZ x6 (152mm)	8

HIGH PERFORMANCE

Cat. No.	Description	Application	Contents	Pack Quantity
DT2442-QZ	8pc Set + storage case	Mixed applications	DT2301-QZ x2 (152mm) DT2303-QZ x2 (152mm) DT2349-QZ x2 (228mm) DT2353-QZ x2 (203mm)	8
DT2444-QZ	6pc Set + storage case	Mixed applications	DT2345-QZ x2 (152mm) DT2349-QZ x2 (228mm) DT2353-QZ x2 (203mm)	6
DT2445-QZ	12pc Set + storage case	Mixed applications	DT2345-QZ x1 (152mm) DT2349-QZ x3 (228mm) DT2359-QZ x2 (152mm) DT2353-QZ x3 (203mm) DT2361-QZ x3 (152mm)	12

SOCKET SETS



EXTREME® IMPACT

Cat. No.	Description	Contents	Pack Quantity
DT7506-QZ	17pc Socket Set	MM: 6, 8, 10, 11, 12, 13, 14, 16, 17, 18, 19, 20, 21, 22, 24, 27 & 1/4" to 1/2" adapter)	17
DT7507-QZ	9pc Socket Set	MM: 10, 13, 15, 17, 19, 22, 24, 27 & 1/4" to 1/2" adapter)	9
DT7512-QZ	1/4" to 1/2" Impact Driver Adapter	1/4" to 1/2" Impact Driver Adapter	1

ROUTER SETS



WOOD ROUTER SETS WITH 8mm SHAFT

Cat. No.	Description	Application	Contents	Pack Quantity
DT90016-QZ	12pc Router Bit Set	8mm	Round, V-Groove, Dovetail, Cove, Roman Ogee, Chamfer, Straight x3, Trim, Round Over x2	12
DT90017-QZ	22pc Router Bit Set	8mm	Straight x6, Trim, Roman Ogee, Chamfer, Round Over x2, V-Groove x2, Round x2, Dovetail, Cove x2, Guided Trimmer, Guided Rebater, Ogee Panel, Traditional Torus	22

OSCILLATING BLADE SETS



OSCILLATING BLADE SETS

Cat. No.	Description	Application	Contents	Pack Quantity
DT20713-QZ	3pc Set	Wood + Nails Wood - Fast Cut Wood - Detail	DT20701-QZ, DT20704-QZ, DT20706-QZ	3
DT20715-QZ	5pc Set	Wood + Nails Wood - Fast Cut Sealants / Adhesives	DT20701-QZ x2 DT20704-QZ DT20711-QZ DT20714-QZ	5
DT20731-QZ	8pc Set with sanding paper	Wood Wood + Nails	DT20700-QZ, DT20701, DT20704, DT20705, DT20710 Detail Sanding Paper x 3 (60G, 80G, 120G)	8

DT43918-QZ	126	DT60233-QZ	10	DT70522T-QZ	157	DT70710-QZ	165
DT43919-QZ	126	DT60234-QZ	10	DT70523TM-QZ	158	DT70711-QZ	33
DT43921-QZ	126	DT60235-QZ	10	DT70523T-QZ	59	DT70711-QZ	165
DT43922-QZ	126	DT60300-QZ	153	DT70523T-QZ	158	DT70712-QZ	24
DT43931-QZ	126	DT60301-QZ	16	DT70531T-QZ	57	DT70712-QZ	165
DT43932-QZ	126	DT60301-QZ	153	DT70532T-QZ	57	DT70713-QZ	165
DT43933-QZ	126	DT60302-QZ	16	DT70533T-QZ	57	DT70714-QZ	166
DT43934-QZ	126	DT60302-QZ	153	DT70534T-QZ	57	DT70715-QZ	166
DT43935-QZ	126	DT60330-QZ	22	DT70535T-QZ	58	DT70716-QZ	166
DT43936-QZ	126	DT60330-QZ	152	DT70536T-QZ	58	DT70730T-QZ	162
DT43937-QZ	126	DT60340-QZ	15	DT70537T-QZ	58	DT70731T-QZ	162
DT43938-QZ	126	DT60341-QZ	15	DT70538T-QZ	58	DT70732T-QZ	162
DT43939-QZ	126	DT60342-QZ	15	DT70547T-QZ	58	DT70733T-QZ	162
DT43940-QZ	126	DT60343-QZ	15	DT70555T-QZ	58	DT70734T-QZ	59
DT43941-QZ	126	DT60809-QZ	8	DT70555T-QZ	157	DT70734T-QZ	162
DT43942-QZ	126	DT60810-QZ	8	DT70556T-QZ	58	DT70735T-QZ	162
DT43943-QZ	126	DT60811-QZ	8	DT70556T-QZ	157	DT70736TM-QZ	162
DT43946-QZ	126	DT60812-QZ	8	DT70557T-QZ	58	DT70737T-QZ	162
DT43947-QZ	126	DT60813-QZ	8	DT70557T-QZ	157	DT70738T-QZ	162
DT43948-QZ	126	DT60814-QZ	8	DT70558T-QZ	58	DT70739T-QZ	163
DT43949-QZ	126	DT60815-QZ	8	DT70558T-QZ	157	DT70740T-QZ	163
DT43951-QZ	126	DT60816-QZ	8	DT70560T-QZ	158	DT70741T-QZ	163
DT43952-QZ	126	DT60817-QZ	8	DT70563T-QZ	59	DT70742T-QZ	163
DT50000-QZ	36	DT60818-QZ	8	DT70563T-QZ	160	DT70743T-QZ	163
DT50001-QZ	36	DT60819-QZ	8	DT70564T-QZ	157	DT70744T-QZ	163
DT50002-QZ	36	DT60820-QZ	8	DT70566T-QZ	58	DT70745T-QZ	59
DT50003-QZ	36	DT60821-QZ	8	DT70567T-QZ	58	DT70745T-QZ	163
DT50004-QZ	36	DT60822-QZ	8	DT70568T-QZ	58	DT70746T-QZ	163
DT50005-QZ	36	DT60823-QZ	8	DT70569T-QZ	58	DT70747T-QZ	163
DT50006-QZ	36	DT60824-QZ	8	DT70574T-QZ	158	DT70748T-QZ	164
DT50007-QZ	36	DT60825-QZ	8	DT70577T-QZ	157	DT70749T-QZ	164
DT50008-QZ	36	DT60826-QZ	8	DT70578T-QZ	59	DT71501-QZ	166
DT50009-QZ	36	DT60827-QZ	8	DT70578T-QZ	160	DT71502-QZ	158
DT50010-QZ	36	DT60828-QZ	8	DT70586T-QZ	157	DT71511-QZ	157
DT50011-QZ	36	DT60829-QZ	8	DT70618T-QZ	157	DT71514-QZ	160
DT50012-QZ	36	DT60830-QZ	8	DT70619T-QZ	161	DT71515-QZ	63
DT50013-QZ	36	DT60831-QZ	8	DT70620-QZ	161	DT71516M-QZ	159
DT50014-QZ	36	DT60832-QZ	8	DT70620T-QZ	167	DT71516-QZ	62
DT50015-QZ	36	DT60833-QZ	8	DT70621-QZ	161	DT71516-QZ	159
DT50016-QZ	36	DT60834-QZ	8	DT70621T-QZ	157	DT71517T-QZ	59
DT50017-QZ	36	DT60835-QZ	8	DT70700-QZ	164	DT71517T-QZ	161
DT50018-QZ	36	DT60836-QZ	8	DT70702-QZ	63	DT71521-QZ	157
DT50050-QZ	36	DT60837-QZ	8	DT70702-QZ	164	DT71522-QZ	157
DT50050-QZ	166	DT60838-QZ	8	DT70703-QZ	164	DT71560-QZ	157
DT60000-QZ	27	DT60839-QZ	8	DT70704-QZ	63	DT71562-QZ	159
DT60001-QZ	27	DT60840-QZ	8	DT70704-QZ	164	DT71563-QZ	167
DT60003-QZ	27	DT60842-QZ	8	DT70705-QZ	164	DT71565-QZ	159
DT60004-QZ	27	DT60844-QZ	8	DT70706M-QZ	165	DT71566-QZ	167
DT60099-QZ	27	DT60845-QZ	8	DT70707-QZ	165	DT71567-QZ	159
DT60099-QZ	154	DT60846-QZ	8	DT70708-QZ	165	DT71569-QZ	167
DT60230-QZ	10	DT60847-QZ	8	DT70709-QZ	62	DT71570-QZ	62
DT60231-QZ	10	DT70512T-QZ	158	DT70709-QZ	165	DT71570-QZ	158
DT60232-QZ	10	DT70518T-QZ	160	DT70710-QZ	33	DT71572-QZ	63

DT71573-QZ	157	DT83083-QZ	51	DT99570-QZ	75	DTM8561-QZ	109
DT71583-QZ	167	DT83086-QZ	51	DT99571-QZ	75	DTM8562-QZ	109
DT71701-QZ	155	DT83089-QZ	51	DT99572-QZ	75	DTM8563-QZ	109
DT71706-QZ	157	DT83092-QZ	51	DT99573-QZ	75	DTM8564-QZ	109
DT71905-QZ	158	DT83095-QZ	51	DT99574-QZ	75	DTM8565-QZ	109
DT71908-QZ	158	DT83098-QZ	51	DT99575-QZ	75	DTM8566-QZ	109
DT71910-QZ	157	DT83102-QZ	51	DT99576-QZ	75	DTM8567-QZ	109
DT71911-QZ	157	DT83105-QZ	51	DT99577-QZ	75	DTM8568-QZ	109
DT71916-QZ	155	DT83108-QZ	51	DT99578-QZ	75	DTM8569-QZ	109
DT83001-QZ	51	DT83114-QZ	51	DT99579-QZ	75	DTM8570-QZ	109
DT83001-QZ	156	DT83121-QZ	51	DT99580-QZ	125	DTM8571-QZ	109
DT83002-QZ	51	DT83127-QZ	51	DT99581-QZ	125	DTM8572-QZ	109
DT83002-QZ	156	DT83140-QZ	51	DT99582-QZ	125	DTM8573-QZ	109
DT83003-QZ	51	DT83152-QZ	51	DT99583-QZ	120	DTM8574-QZ	109
DT83003-QZ	156	DT90001-QZ	104	DT99584-QZ	120	DTM8575-QZ	109
DT83004-QZ	51	DT90002-QZ	104	DT99585-QZ	120	DTM8576-QZ	109
DT83004-QZ	156	DT90003-QZ	104	DT99590-QZ	99	DTM8621-QZ	110
DT83014-QZ	51	DT90004-QZ	104	DT99591-QZ	99	DTM8622-QZ	110
DT83016-QZ	51	DT90005-QZ	104	DT99592-QZ	99	DTM8624-QZ	110
DT83017-QZ	51	DT90006-QZ	104	DT99593-QZ	99	DTM8655-QZ	110
DT83019-QZ	51	DT90007-QZ	104	DT99595-QZ	75	DTM8656-QZ	110
DT83020-QZ	51	DT90008-QZ	104	DT99596-QZ	75	DTM8659-QZ	111
DT83021-QZ	51	DT90009-QZ	104	DTM3022-QZ	111	DTM8660-QZ	111
DT83022-QZ	51	DT90010-QZ	104	DTM3023-QZ	111	DTM8663-QZ	111
DT83024-QZ	51	DT90011-QZ	104	DTM3025-QZ	111	DTM8664-QZ	111
DT83025-QZ	51	DT90012-QZ	104	DTM3092-QZ	110	DTM8667-QZ	110
DT83027-QZ	51	DT90013-QZ	104	DTM3092-QZ	147	DTM8668-QZ	110
DT83029-QZ	51	DT90014-QZ	104	DTM3093-QZ	110	DTM8671-QZ	109
DT83030-QZ	51	DT90015-QZ	104	DTM3093-QZ	147		
DT83032-QZ	51	DT90016-QZ	104	DTM3095-QZ	110		
DT83033-QZ	51	DT90016-QZ	104	DTM3095-QZ	147		
DT83035-QZ	51	DT90016-QZ	169	DTM3103-QZ	109		
DT83037-QZ	51	DT90017-QZ	104	DTM3105-QZ	109		
DT83038-QZ	51	DT90017-QZ	104	DTM3107-QZ	109		
DT83040-QZ	51	DT90017-QZ	169	DTM3113-QZ	109		
DT83041-QZ	51	DT99550-QZ	93	DTM3115-QZ	109		
DT83043-QZ	51	DT99550-QZ	168	DTM3117-QZ	109		
DT83044-QZ	51	DT99551-QZ	93	DTM3123-QZ	109		
DT83046-QZ	51	DT99551-QZ	168	DTM3125-QZ	109		
DT83048-QZ	51	DT99552-QZ	93	DTM3127-QZ	109		
DT83051-QZ	51	DT99553-QZ	93	DTM3133-QZ	109		
DT83052-QZ	51	DT99554-QZ	93	DTM3135-QZ	109		
DT83054-QZ	51	DT99555-QZ	93	DTM3137-QZ	109		
DT83057-QZ	51	DT99560-QZ	75	DTM8551-QZ	111		
DT83060-QZ	51	DT99561-QZ	75	DTM8552-QZ	111		
DT83064-QZ	51	DT99562-QZ	75	DTM8553-QZ	110		
DT83065-QZ	51	DT99563-QZ	75	DTM8554-QZ	110		
DT83067-QZ	51	DT99564-QZ	75	DTM8555-QZ	110		
DT83068-QZ	51	DT99565-QZ	75	DTM8556-QZ	109		
DT83070-QZ	51	DT99566-QZ	75	DTM8557-QZ	109		
DT83073-QZ	51	DT99567-QZ	75	DTM8558-QZ	109		
DT83076-QZ	51	DT99568-QZ	75	DTM8559-QZ	109		
DT83079-QZ	51	DT99569-QZ	75	DTM8560-QZ	109		



Products sold as per dealer's valid price list. Please refer to price list for stock availability.

DeWALT is a member of EPTA

Dual voltage - all DeWALT power tools are supplied in both 230 Volts and 115 Volts options unless otherwise stated. Please contact your local dealer for availability.

DeWALT reserves the right to revise product specifications at any time without notice.

All measurements are in millimetres (mm) unless otherwise stated.

WARNING: all warranties are country/region specific. Tools purchased e.g. in the USA and imported into Europe, which are not CE approved, will not be supported/serviced in Europe by DeWALT as a result.

Only CE approved European tools are covered by a European warranty.

GUARANTEED TOUGH, ROBUSTESSE GARANTIE, DeWALT EXTREME, DeWALT, EXTREME DeWALT, DeWALT EXTREME IMPACT, DeWALT GUARANTEED TOUGH, SERIES 20, SERIES 30, SERIES 40, SERIES 60, AVC, XRP, XPC, XLR, TOUGHSYSTEM, XR, XPS, ALLIGATOR and the yellow and black colour scheme for portable electric power tools are registered trademarks of The Black and Decker Corporation and Stanley Black & Decker Inc. The yellow and black colour scheme is used on DeWALT power tools and accessories as a trademark.

GORE Wet/Dry Filter is a trademark of W.L Gore & Associates Inc.



Registered Trade Marks of Robert Bosch GmbH. Torx® is a Registered Trade Mark of Acument Intellectual Properties, LLC.

DeWALT Norway
Gullhaugveien 11
0484 Oslo
E-mail: kundeservice.no@sbdinc.com

DeWALT Denmark
Roskildevej 22
2620 Albertslund
E-mail: kundeservice.dk@sbdinc.com

DeWALT Finland
Elimäenkatu 28 4 krs
00520 HELSINKI
Sähköposti: asiakaspalvelu.fi@sbdinc.com

DeWALT Sweden
Box 94,
431 22 Mölndal
E-mail: kundserservice.se@sbdinc.com

www.DEWALT.com

The yellow and black colour scheme is used on DeWALT Power Tools and Accessories as a trademark. DeWALT reserves the right to change any deal at any time without notice. Deals available while stocks last.