



PC-Board layout
view component side
thickness 1,6 mm



Connector retention and insertion forces on PC-Board: 25 N / 80 N

09 65 263 3811	M3	PL1
09 65 263 6811	M3	PL2
09 65 263 7811	M3	PL3
09 65 263 5811	M3	S4
09 65 263 3812	4-40 UNC	PL1
09 65 263 6812	4-40 UNC	PL2
09 65 263 7812	4-40 UNC	PL3
09 65 263 5812	4-40 UNC	S4
Part number	Nut thread	Performance level



All Dimensions in mm
Original Size DIN A4

Scale

1:1

Free size tol.

Ref.

Sub.



All rights reserved
Department EC PD - FR

Created by
SONN

Inspected by
BAGDIKIAN

Standardisation
HOFFMANN

Date
2015-04-29

State
Final Release

Title
D-Sub 15-Pole Male Angled

Doc-Key / ECM-Nr.
100620634/UGD/000/A
500000088435

Type
TB

Number
0965263X81X

Rev.
A

Page
1/1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[09652636812](#) [09652637812](#) [09652637811](#) [09652636811](#)