

Features

- Magnetically shielded
- Flat wirewound
- Low DCR
- High saturation current
- Extra solder pad for increased mechanical stability
- AEC-Q200 qualified
- RoHS compliant* and halogen free**

Applications


- Automotive - power conversion
- DC/DC converters
- Switch-mode power supplies
- High current Point-of-Load

PQ2617BHA Series - Shielded Power Inductors


Electrical Specifications @ 25 °C

Bourns Part Number	Inductance @ 100 kHz / 0.1 V		SRF (MHz) Typ.	DCR (mΩ) Typ.	DCR (mΩ) Max.	I _{rms} (A) Typ.	Isat1 (A) Typ.	Isat2 (A) Typ.
	L (μH)	Tol. (%)						
PQ2617BHA-3R3K	3.3	± 10	40	2.16	2.50	28	92.5	93.6
PQ2617BHA-4R7K	4.7	± 10	30	2.16	2.50	28	61.2	62.4
PQ2617BHA-6R8K	6.8	± 10	25	2.16	2.50	28	45.0	45.9
PQ2617BHA-100K	10	± 10	20	2.16	2.50	28	31.2	32.1
PQ2617BHA-150K	15	± 10	16	2.16	2.50	28	21.2	21.9
PQ2617BHA-220K	22	± 10	15	2.16	2.50	28	14.0	15.0
PQ2617BHA-330K	33	± 10	10	2.16	2.50	28	8.7	9.6


How to Order



Typical Part Marking



Recommended Layout



General Specifications

Dielectric Withstand Voltage - Terminal to Core 300 VDC 5 mA max.

Operating Temperature -40 °C to +155 °C (Temperature rise included)

Storage Temperature (Component) -40 °C to +155 °C

Rated Current Inductance drops 20 % at Isat1
Inductance drops 30 % at Isat2

Temperature Rise 40 °C at rated I_{rms}

Moisture Sensitivity Level 1

ESD Classification (HBM) N/A

Materials


Core Ferrite

Wire Enameled copper


Terminal Finish Sn

Packaging 25 pcs/tray

Product Dimensions



Soldering Profile



09/17

* RoHS Directive 2002/95/EC Jan. 27, 2003 including annex and RoHS Recast 2011/65/EU June 8, 2011.


** Bourns considers a product to be "halogen free" if (a) the Bromine (Br) content is 900 ppm or less; (b) the Chlorine (Cl) content is 900 ppm or less; and (c) the total Bromine (Br) and Chlorine (Cl) content is 1500 ppm or less.

Specifications are subject to change without notice.

The device characteristics and parameters in this data sheet can and do vary in different applications and actual device performance may vary over time.

Users should verify actual device performance in their specific applications.

Electrical Schematic



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Bourns:

[PQ2617BHA-150K](#) [PQ2617BHA-3R3K](#) [PQ2617BHA-220K](#) [PQ2617BHA-6R8K](#) [PQ2617BHA-330K](#) [PQ2617BHA-100K](#) [PQ2617BHA-4R7K](#)