

WI-M-10-XX-@

(Extra Heavy-Duty 10 AWG, Silicone Jacket Test Lead Wire)



- Mueller's WI-M-10-@ is 10 AWG, 1050/0.08 stranded, tinned copper wire with highly flexible 0.197" (5mm) diameter silicone jacket.
- Ratings:

Current	45 Amps @ 150°C
Voltage	600V
Dielectric Strength	2 KV/Min
Spark Test	6 KV
Bend Radius	3D
Rated Temperature	-40°C to 200°C
Temperature Rating	FT2
UL Safety Standard	UL 758
- Length: The "XX" in the model number indicated length in feet.
Standard lengths: 10', 25', 30', 50', and 100'
- Color: The "@" in the model number represents color.
Available colors: -0 Black, -2 Red

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Mueller Electric:

[WI-M-10-10-0](#) [WI-M-10-25-6](#) [WI-M-10-10-4](#) [WI-M-10-25-2](#) [WI-M-10-10-6](#) [WI-M-10-10-5](#) [WI-M-10-25-9](#) [WI-M-10-25-0](#) [WI-M-10-25-4](#) [WI-M-10-25-5](#) [WI-M-10-10-9](#) [WI-M-10-10-2](#)