



Product designation
Product type designation
Function

Float switches for
grey water
LVFSP1
Emptying or filling
function

Counterweights

Counterweight

External
(provided with the
float switch)

Activation angle

45°

Relay outputs

Number of relays

N° 1

Contact arrangement

1 changeover
contact C/O-
SPDT

Rated operational voltage AC (IEC)

VAC 250

Contact ratings

AC1 10A
250VAC AC15
8A 250VAC

Connections

Maximum cable length

m / ft 10

Ambient conditions

Temperature

Operating temperature

max °C +50

Storage temperature

max °C +80

Maximum operating pressure

bar 3

Maximum installation depth

m 30

Housing

Cable material

PVC A05 VV-
F3X1

Float casing material

Polypropylene


IEC degree of protection

IP68

Weight

g 1410

Dimensions



Certifications and compliance

Compliance

IEC/EN 60730-1
 IEC/EN 60730-2-15

Certificates

TÜV-SUD