

	Description	UT658DUAL
Input & Output ports (Type A)		√
Input & Output ports (Type C)		√
Data/charging protocol		2.0/(3.0/4.0)
Voltage range	4~24VDC, resolution: 0.01V	√
Current range (Type-A)	0.05~3ADC, resolution: 0.01A	√
Current range (Type-C)	0.05~5ADC, resolution: 0.01A	√
Capacity	0~99999mAh, resolution: 1mAh	√
Energy	0~1000Wh	√
Circuit equivalent resistance measurement	1~480Ω	√
USB data cable voltage (D+, D-)	0~3.3V	√
Data storage	10 sets	√
Maximum recording time	99h, 59min, 59sec; resolution: 1s	√
Fast charge protocol (Type-A)	QC 3.0 fast charge protocol	√
Fast charge protocol (Type-C)	QC 4.0 fast charge protocol	√
General Characteristics		
Product color	White	
Product net weight	65.8g	
Product size	93mm x 55mm x 13mm	
Standard individual packing	Gift box, English manual	
Standard quantity per carton	60pcs	
Standard carton measurement	280mm x 220mm x 225mm	