


Rugged Chassis For DIY Electronic Projects, Features “BNC Input/Output”

2.6" BNC Housing



Tolerances Unless Otherwise Noted	
0-0.197 (0-0.5)	\pm 0.004 (\pm 0.10)
0.197-0.315 (0.5-8.0)	\pm 0.008 (\pm 0.20)
0.315-1.181 (8.0-30.0)	\pm 0.016 (\pm 0.40)
1.181-4.724 (30.0-120.0)	\pm 0.020 (\pm 0.50)

A Tooling Dimple, 2 Locations, Diameter 0.055 in (1.40 mm), Depth 0.055 in (1.40 mm)
Provides a cavity for dimpling the sleeve with a center punch. The mechanical contact also provides an electrical contact and shields the internal circuitry in the body.

No.	Description	Qty	Material	Plating
1	Body	1	Brass	Nickel
2	Center Pin	2	Brass	Gold

BNC-KIT-2.6MF Rev. C

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Crystek:](#)

[BNC-KIT-2.6MF](#)