



MATERIALS:

Body and Fittings: Brass, Tarnish Resistant Plating

Center Contact: Gold Plated Beryllium Copper

Dielectric: PTFE

Finish: Body and Fittings: Tarnish Resistant

Center Contact: Gold Plated

RATING:

Nominal Impedance: 50 Ohms

Operating Temperature: -65°C to $+165^{\circ}\text{C}$

ORDERING INFORMATION: Model 2451

All dimensions are in inches. Tolerances (except noted): $.xx = \pm .02''$ (.51 mm), $.xxx = \pm .005''$ (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pomona:

2451 2451#