

#### 3.0A SBR SUPER BARRIER RECTIFIER SMA

#### Product Summary (@ T<sub>A</sub> = +25°C)

V <sub>RRM</sub> (V)	I <sub>O</sub> (A)	V <sub>F(MAX)</sub> (mV)	I <sub>R(MAX)</sub> (μA)
40	3	500	400

#### **Features and Benefits**

- Low Leakage Current
- Patented Super Barrier Rectifier Technology
- Soft, Fast Switching Capability
- +150°C Operating Junction Temperature
- Lead-Free Finish; RoHS Compliant (Notes 1 & 2)
- Halogen and Antimony Free. "Green" Device (Note 3)
- Qualified to AEC-Q101 Standards for High Reliability
- PPAP Capable (Note 4)

## **Applications**

- SMPS
- AC-DC
- DC-DC Converter
- Freewheeling Diodes

#### **Mechanical Data**

- Case: SMA
- Case Material: Molded Plastic, "Green" Molding Compound.
   UL Flammability Classification Rating 94V-0
- Moisture Sensitivity: Level 1 per J-STD-020
- Terminals: Lead Free Plating (Matte Tin Finish.) Solderable per MIL-STD-202, Method 208
- Polarity Indicator: Cathode Band
- Weight: 0.064 grams (Approximate)



Top View



Bottom View

#### **Ordering Information** (Note 5)

Part Number	Compliance	Case	Packaging
SBR3A40SA-13	Commercial	SMA	5,000/Tape & Reel
SBR3A40SAQ-13	Automotive	SMA	5,000/Tape & Reel

Notes:

- 1. EU Directive 2002/95/EC (RoHS) & 2011/65/EU (RoHS 2) compliant. All applicable RoHS exemptions applied.
- See http://www.diodes.com/quality/lead\_free.html for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and Lead-free.
- 3. Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.
- 4. Automotive products are AEC-Q101 qualified and are PPAP capable. Automotive, AEC-Q101 and standard products are electrically and thermally the same, except where specified. For more information, please refer to http://www.diodes.com/quality/product\_compliance\_definitions/.
- 5. For packaging details, go to our website at http://www.diodes.com/products/packages.html.

## **Marking Information**



SV 4 = Product Type Marking Code

| Manufacturers' Code Marking

| YWW = Date Code Marking
| Y = Last Digit of Year (ex: 7 for 2007)

| WW = Week Code 01 to 52

| XX = Foundry and Assembly Site

Note: 6. Device has a cathode band (as shown above) and may also have a cathode notch.

March 2016 © Diodes Incorporated



### **Maximum Ratings** (@T<sub>A</sub> = +25°C, unless otherwise specified.)

Single phase, half wave, 60Hz, resistive or inductive load For capacitance load, derate current by 20%.

Characteristic	Symbol	Value	Unit
Peak Repetitive Reverse Voltage	$V_{RRM}$		
Working Peak Reverse Voltage	$V_{RWM}$	40	V
DC Blocking Voltage	$V_{RM}$		
Maximum Voltage Rate of Change (Rated V <sub>R</sub> )	dv/dt	10,000	V/µs
RMS Reverse Voltage	V <sub>R(RMS)</sub>	28	V
Average Rectified Output Current	lo	3	Α
Non-Repetitive Peak Forward Surge Current 8.3ms Single Half Sine-Wave Superimposed on Rated Load	I <sub>FSM</sub>	45	А

### **Thermal Characteristics**

Characteristic	Symbol	Value	Unit
Maximum Thermal Resistance Thermal Resistance Junction to Soldering (Note 7) Thermal Resistance Junction to Ambient (Note 8) Thermal Resistance Junction to Case (Note 8)	$egin{array}{c} R_{ heta JS} \ R_{ heta JA} \ R_{ heta JC} \end{array}$	5 124 14.3	°C/W
Power Dissipation (Note 8) @T <sub>A</sub> = +25°C	$P_D$	1.2	W
Operating and Storage Temperature Range	T <sub>J</sub> , T <sub>STG</sub>	-65 to +150	°C


# **Electrical Characteristics** (@T<sub>A</sub> = +25°C, unless otherwise specified.)

Characteristic	Symbol	Min	Тур	Max	Unit	Test Condition
Reverse Breakdown Voltage (Note 9)	V <sub>(BR)R</sub>	40	_	_	V	$I_R = 0.4 \text{mA}$
Forward Voltage Drop	V <sub>F</sub>	- - -	0.30 0.33 0.43 -	0.35 0.38 0.50 0.48	V	$I_F = 0.5A$ , $T_J = +25^{\circ}C$ $I_F = 1.0A$ , $T_J = +25^{\circ}C$ $I_F = 3.0A$ , $T_J = +25^{\circ}C$ $I_F = 3.0A$ , $T_J = +125^{\circ}C$
Leakage Current (Note 9)	I <sub>R</sub>	_	45 80 9	250 400 40	μΑ μΑ mA	$V_R = 5V$ , $T_J = +25$ °C $V_R = 40V$ , $T_J = +25$ °C $V_R = 40V$ , $T_J = +125$ °C

Notes:

- 7. Theoretical R<sub>0JS</sub> calculated from the top center of the die straight down to the PCB cathode tab solder junction.
- 8. FR-4 PCB, 2 oz. Copper, minimum recommended pad layout per http://www.diodes.com/package-outlines.html.
- 9. Short duration pulse test used to minimize self-heating effect.
- 10. FR-4 PCB, 2 oz. Copper, single side 16 x MRP, 1" x 1" PC Board.








## **Package Outline Dimensions**


Please see http://www.diodes.com/package-outlines.html for the latest version.



SMA				
Dim	Min	Max		
Α	2.29	2.92		
В	4.00	4.60		
C	1.27	1.63		
D	0.15	0.31		
Е	4.80	5.59		
G	0.05	0.20		
H	0.76	1.52		
J	1.96	2.40		
All Dimensions in mm				

## **Suggested Pad Layout**

Please see http://www.diodes.com/package-outlines.html for the latest version.



Dimensions	Value (in mm)
С	4.00
G	1.50
Х	2.50
X1	6.50
Y	1.70



#### **IMPORTANT NOTICE**

DIODES INCORPORATED MAKES NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).

Diodes Incorporated and its subsidiaries reserve the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. Diodes Incorporated does not assume any liability arising out of the application or use of this document or any product described herein; neither does Diodes Incorporated convey any license under its patent or trademark rights, nor the rights of others. Any Customer or user of this document or products described herein in such applications shall assume all risks of such use and will agree to hold Diodes Incorporated and all the companies whose products are represented on Diodes Incorporated website, harmless against all damages.

Diodes Incorporated does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel. Should Customers purchase or use Diodes Incorporated products for any unintended or unauthorized application, Customers shall indemnify and hold Diodes Incorporated and its representatives harmless against all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized application.

Products described herein may be covered by one or more United States, international or foreign patents pending. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks.

This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes Incorporated.

#### LIFE SUPPORT

Diodes Incorporated products are specifically not authorized for use as critical components in life support devices or systems without the express written approval of the Chief Executive Officer of Diodes Incorporated. As used herein:

- A. Life support devices or systems are devices or systems which:
  - 1. are intended to implant into the body, or
  - 2. support or sustain life and whose failure to perform when properly used in accordance with instructions for use provided in the labeling can be reasonably expected to result in significant injury to the user.
- B. A critical component is any component in a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or to affect its safety or effectiveness.

Customers represent that they have all necessary expertise in the safety and regulatory ramifications of their life support devices or systems, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of Diodes Incorporated products in such safety-critical, life support devices or systems, notwithstanding any devices- or systems-related information or support that may be provided by Diodes Incorporated. Further, Customers must fully indemnify Diodes Incorporated and its representatives against any damages arising out of the use of Diodes Incorporated products in such safety-critical, life support devices or systems.

Copyright © 2016, Diodes Incorporated

www.diodes.com

# **Mouser Electronics**

**Authorized Distributor** 

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Diodes Incorporated: SBR3A40SA-13