


Deep groove ball bearings, single row, shield on both sides

Principal dimensions			Basic load ratings		Fatigue load limit P_u	Speed ratings		Mass	Designation
d	D	B	dynamic	static		Reference speed	Limiting speed		
mm			kN		kN	r/min		kg	-
30	72	19	29,6	16	0,67	20000	11000	0,35	6306-2Z *



Calculation factors

k_r 0,03
 f_0 13