

TERMINAL BLOCK Connector

PCB Series

KLS2-103-5.00 Series Pitch=5.00mm/10.00mm

Electrical :



Rated voltage: 300V
Rated current: 16A
Contact resistance: 20mΩ
Insulation resistance: 5000MΩ/1000V
Withstanding Voltage: AC1500V/1Min
Wire range: 22-12AWG 2.5mm²

Material

Screws: M2.5 steel Zinc plated
Pin header: Brass, Tin plated
Housing: PA66, UL94V-0

Mechanical

Temp. Range: -40°C~+105°C
MAX Soldering: 250°C for 5 Sec.
Torque: 0.4Nm (3.6lb.in)
Strip length: 6-7mm



ORDER INFORMATION

Product NO.: KLS2-103-5.00-XXP X X X

Pos. NO.

Series No.

Pitch: 5.00=5.00mm
10.00=10.00mm

Number of Pole

Customer Request

Screw: C=Cross Screw
S=Slot Screw

Color: 1=Gray
4=Green
7=Transparent

2=Blue
5=Orange
8=Yellow

3=Black
6=Red
9=White