# **TERMINAL BLOCK Connector**

## **PCB** Series

### KLS2-129-5.00/5.08 Series Pitch=5.00mm/5.08mm

#### **Electrical:**


Rated voltage: 300VRated current: 10AContact resistance:  $20m\Omega$ Insulation resistance:  $5000M\Omega/1000V$ Withstanding Voltage: AC1500V/1Min Wire range: 24-12AWG 2.5mm<sup>2</sup>

#### Material

Screws: M2.5 steel Zinc plated Contact: Brass Pin header: Brass, Tin plated Housing: PA66, UL94V-0

#### **Mechanical**

Temp. Range: -40°C~+105°C MAX Soldering: +250°C for 5 Sec. Torque: 0.4Nm (3.6lb.in) Strip length: 6-7mm



All specification & dimensions are subject to change, please call your nearest KLS sales represesntative for update information

