

5

4



3

2


1

SPECIFICATION



Performance level	PL2
Capacitance	1000pf±20%
Working Voltage	100v
Current Rating	7.5A
Insulation Resistance	>1GΩ



Solder buckets for AWG 20



FREQUENCY (MHz)	ATTENUATION dB
5	1dB
10	3dB
50	12dB
100	20dB
500	34dB
1000	30dB

				Dat.	Name	 All Dim. in mm Orig. Size DIN A 4	D-Sub, male, Straight 25 Poles, turned solder buckets, with dimples and holes	Mo?Mstab/ Scale 1.5:1
			Detail.	8-JUL-02	CV			
			Insp.	12/01/12	JB			
			Stand.					
36283	12/01/12	SD				 Sub.	TB 09643217230	Blatt/ Page 1 / 1
33423	06/02/06	JMDR						
31058	8-JUL-02	CV						
Mod.	Dat.	Name						
HARTING EURL F-95972 Paris								

D

C

B

A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[09643217230](#)