

**KISC M3X20.5/10 EK4****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Screwable cross-connections are easy to mount and de mount. Thanks to the big contact surface, even high currents can be transmitted with maximum contact reliability.

**General ordering data**

Version	Clamping yoke, Mounting screw, Steel
Order No.	<a href="#">0303000000</a>
Type	KISC M3X20.5/10 EK4
GTIN (EAN)	4008 190 163686
Qty.	100 pc(s).

Creation date January 7, 2022 12:09:16 PM CET

Catalogue status 17.12.2021 / We reserve the right to make technical changes.

## KISC M3X20.5/10 EK4

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

### Dimensions and weights

Height	20 mm	Height (inches)	0.787 inch
Diameter	3 mm	Net weight	1.16 g

### Material data

Material	Steel	Surface finish	Miscellaneous
Colour	silver		

### System specifications

Version	for busbars
---------	-------------

### Additional technical data

Explosion-tested version	No	Installation advice	Direct mounting
Type of fixing	when screwed in	Type of mounting	when screwed in

### Dimensions

Diameter	3 mm	Metric size of the thread, external	0 M3.0
----------	------	-------------------------------------	--------

### General

Installation advice	Direct mounting	Surface finish	Miscellaneous
---------------------	-----------------	----------------	---------------

### Classifications

ETIM 6.0	EC002848	ETIM 7.0	EC002848
ETIM 8.0	EC002848	ECLASS 9.0	27-14-11-92
ECLASS 9.1	27-14-11-92	ECLASS 10.0	27-14-11-92
ECLASS 11.0	27-14-11-92		

### Approvals

ROHS	Conform
------	---------

### Downloads

Engineering Data	<a href="#">CAD data – STEP</a>
Engineering Data	<a href="#">EPLAN, WSCAD</a>
User Documentation	<a href="#">StorageConditionsTerminalBlocks</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>