

[AC Switch disconnectors](#) - [Load Break Switching \(LBS\)](#) - [Power Protection, Transfer & Distribution](#)

SIRCO M3 3X60A

22013006

Load break switch standards UL and CSA SIRCO M 3P 60A

Médias (Ref)

Accessories Prime Picture	PP_PACKSHOT\sircm\sircm_229_front.eps
Reference prime picture quality level	1

Load break switch

Rated current	60
Number of poles	3
Frame size	M3
Control operator	Direct : M01 / External : S00, S0, S01
Rated voltage	690 VAC - 400 VDC

Technical Characteristics

Type	Rotary
------	--------

Logistics

GTIN/EAN	3596031973743
Customs number	85365080
Price unit	PC
Weight of the packing unit	0.63
Length of the packing unit	0.17
Width of the packing unit	0.1
Depth of the packing unit	0.09

Commerce

Discount Policy Label	SIRCO M1 to M3
Country of origin	CN
Weight	0.63
Length of the product unit	0.189
Width of the product unit	0.078
Depth of the product unit	0.075

Norms

Conformity to standards	IEC UL
Norms	CE

SYSTEME

ReferenceLabel	22013006-SIRCO M3 3X60A
----------------	-------------------------

Classification

Technical Product Type	Other
------------------------	-------

UNSPSC	39122233
--------	----------

UNSPSC Title	Disconnect switch
--------------	-------------------

ETIM Class	EC000216
------------	----------

IGCC	5290
------	------

IGCC Category	Disconnect switch
---------------	-------------------

Product Management

Product kind	Main
--------------	------