



USB TYPE-C CONNECTORS

TE Connectivity's (TE) USB Type-C connectors are designed to an industry standard that provides a sleek, slim design small enough for handheld devices and robust enough for industrial applications. The USB Type-C connector features a reversible mating interface; the receptacle is designed to accept a plug in any direction, enabling easy, reliable mating. This connector supports a variety of different protocols, and with the use of adaptors, it is backwards compatible to HDMI, VGA, DisplayPort, and other types of connections from the single USB Type-C port. We provide a distinctive electromagnetic interference (EMI) design on the back of the receptacle shell to help eliminate unwanted EMI leakage, as well as enhanced retention features and splash proof options for better performance in rugged environments.

USB Type-C Connectors

Benefits

- Distinctive design on the back of the receptacle shell for industry leading EMI performance
- Enhanced board retention features for added durability
- Splash proof options available. IPX4 rated to protect against water splashed from all directions.
- Available in one of the smallest dual row surface mount (SMT) footprints, saving valuable board real-estate.
- Provide one interconnect solution for data, power, and A/V
- Designed with a flippable and reversible mating interface
- Supports USB 2.0, USB 3.1 Gen 1 and USB 3.1 Gen 2
- Deliver power up to 100W at 20V
- Backward compatible to other USB connectors using converter cables or adaptors

Applications

- Factory automation
- Industrial machinery
- Data centers
- Medical devices
- A/V digital switches
- Power packs and chargers
- Automotive infotainment
- Business equipment
- Lighting
- Tablets
- PCs and laptops
- Wearables
- Smart phones

Part Number Information

Description	TE Part Number
USB Type-C Receptacle Mid-Mount 0.485 Hybrid	2129691-1
USB Type-C Receptacle Offset 0.65mm Dual Row SMT, Splash Proof	2295018-2
USB Type-C Receptacle Offset 0.65mm Dual Row SMT	1-2295018-2

te.com/products/USBTypeC

TE Connectivity, TE, TE Connectivity (logo) and Every Connection Counts are trademarks. All other logos, products and/or company names referred to herein might be trademarks of their respective owners.

The information given herein, including drawings, illustrations and schematics which are intended for illustration purposes only, is believed to be reliable. However, TE Connectivity makes no warranties as to its accuracy or completeness and disclaims any liability in connection with its use. TE Connectivity's obligations shall only be as set forth in TE Connectivity's Standard Terms and Conditions of Sale for this product and in no case will TE Connectivity be liable for any incidental, indirect or consequential damages arising out of the sale, resale, use or misuse of the product. Users of TE Connectivity products should make their own evaluation to determine the suitability of each such product for the specific application.

©2016 TE Connectivity Ltd. family of companies. All Rights Reserved.

1-1773868-8 05/16 DND



Mid-Mount Hybrid Receptacle



NEW Splash Proof Dual Row SMT Receptacle

Materials

- Contact: Copper alloy
- Housing: Thermo plastic, UL 94 V-0
- Shell: stainless steel

Ratings

- Voltage rating: 30V max.
- Current rating:
 - VBUS pins: 5A max, GND pins: 6.25A
 - VCONN pins: 1.25A max.
 - Signal pins contact: 0.25A min.
- Temperature rating: -30°C to 85°C

Specifications

- Product specs: 108-99061, 108-115109-2