



Shell size	A ^{+0.76} ₀	B ^{+0.25} ₀	C \pm 0.12	F \pm 0.12	G ^{+0.25} ₀	L ^{+0.22} ₀	Part Number
E	30.43	16.21	24.99	10.96	6.05	0.80	86553148TLF
A	38.76	24.54	33.32	10.96	6.05	0.80	86553149TLF
B	52.65	38.25	47.04	10.96	6.05	0.80	86553150TLF
C	68.94	54.71	63.50	10.96	6.05	0.80	86553151TLF

NOTES

- RoHS INFO : The product meets the european directives and others countries regulations as described on the GS-47-0004
- The product isn't intended to be exposed to a manufacturing solder process
- Plating : Sn pure bright over copper
- Packaging spec : see GS-14-920

spec ref	-	dr	A Parrenin	2013/04/04	projection	mm	size	A3	scale	2:1	
tolerance std	ISO 406 ISO 1101	eng	A Parrenin	2013/05/16			ecn no	ELX-B-14776-1			
TOLERANCES UNLESS OTHERWISE SPECIFIED		chr	Laurent Mulin	2013/05/16			product family	D-Sub	rel level	Released	
surface	<input checked="" type="checkbox"/> linear <input type="checkbox"/> angular	appr	Gert Dreesbeke	2013/05/16			dwg no	C01-8655-1657		rev	D
ISO 1302	0.X ±0.3 0.XX ±0.10 0.XXX ±0.05 0° ±2°	www.fci.com	cat. no.	-	Product - Customer Drw		sheet 1 of 1				