



PART NUMBER	CABLE O.D. RANGE
S15KS20	Ø 0.205 - 0.225 [5.21 - 5.72]
S15KS23	Ø 0.235 - 0.255 [5.97 - 6.48]
S15KS26	Ø 0.265 - 0.285 [6.73 - 7.24]

CUSTOMER DRAWING

NOTES:

1. RATED 15 AMP, 24 VOLT DC AT 105° C (CURRENT CARRY ONLY) WHEN USING 14 AWG STRANDED CONDUCTOR CABLE.
2. USE CABLE LUBE WHEN ASSEMBLING CABLE.
3. IP68 RATED WHEN MATED TO ST15S JACK.
4. HANDLE SHIPPED UNASSEMBLED.
5. THIS PRODUCT IS ROHS COMPLIANT.

REV	ECO NUMBER	DATE	BY	APVD
A	28515	7/18/22	TJK	TJK
REVISIONS				

UNLESS OTHERWISE SPECIFIED

1. ALL DIMENSIONS IN INCHES [mm]
 - TWO PLACE DECIMALS ±0.02 [0.5]
 - THREE PLACE DECIMALS ±0.005 [0.13]

DO NOT SCALE DRAWING

THIS DRAWING DESCRIBES A DESIGN CONSIDERED PROPRIETARY IN NATURE, DEVELOPED AND MANUFACTURED BY SWITCHCRAFT INC. AND IS RELEASED ON A CONFIDENTIAL BASIS FOR IDENTIFICATION PURPOSES ONLY.									
SIZE	WIDTH	MULT	LBS/M	TEMPER					
FINISH SPEC No.					MATERIAL SPEC No.				
FIRST USED ON					SCALE 2:1				
DATE DRAWN	BY	CHKD	APVD						
5-13-19	SRC	SRC	TJK						
			6-29-22	7/26/22					
NAME					PART No.		REV		
15 AMP SEALED PLUG, RoHS					S15KS SERIES		A		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Switchcraft:](#)

[S15KS20](#) [S15KS23](#) [S15KS26](#)