



EMPTY ENCLOSURE

AKL 2-t



AKL 2-t

Empty enclosure

CUSTOMIZABLE

300 x 300 x 132 mm
Article number: 74400201

Empty enclosure, with attachment bushes, sealing and insulating plugs, base: polystyrene, grey similar to RAL 7035, cover: polycarbonate, transparent



Technical data

Measures

Width:	300 mm
Length:	300 mm
Height:	132 mm
Inner height:	114 mm

Material

Base:	Polystyrene, grey, similar to RAL 7035
Cover:	Polycarbonate, transparent
Sealing:	Polyurethane
Cover screw:	Polyamide 6, fiber-glass reinforced

Other attributes

Ingress protection:	IP65 - acc. EN
---------------------	----------------

Accessory

- AK MPI 2
- AK NS35-250
- NS35-216/3
- AK ABL-ES
- ASS-gro
- AK ABF 2
- AK TW



EMPTY ENCLOSURE

AKL 2-t

60529 / DIN VDE
0470-1

Impact resistance: IK07 acc. DIN EN
5012 / VDE 0470
Part 100

Rated insulation voltage AC: 690 V V

Rated insulation voltage DC: 1000 V

PVC-free: Yes

Heavy metals-free: Yes

Silicone-free: Yes

Combustion behaviour to UL: HB acc. UL94

Combustion behaviour to VDE: 650°C acc. VDE
0471/ EN 60695

Knockouts: Yes

sealable: Yes

Environmental attributes

Ambient temperature (min.): -25 °C

Ambient temperature (max.): 40 °C

Ambient temperature (24 h): 35 °C

Max. rel. humidity at 25° C (short
Therm): 95%

Max. rel. humidity at 40° C: 50%