

Han-Eco 16B-HSM1-with SL-M25-glanded



Part number	19 43 116 0251
Specification	Han-Eco 16B-HSM1-with SL-M25- glanded
HARTING eCatalogue	https://b2b.harting.com/19431160251
Identification	
Category	Hoods/Housings
Category Series of hoods/housing	
0,	

Version

Locking type	Single locking lever
Size	16 B
Version	Side entry
Cable entry	1x M25
Technical characteristics	
Limiting temperature	-40 +125 °C
Degree of protection acc. to IEC 60529	IP66
Clamping range	9 17 mm
Material properties	
Material (hood/housing)	Polyamide Fibre-glass reinforced
Colour (hood/housing)	RAL 9005 (jet black)
Material (seal)	NBR
Colour (seal)	RAL 9005 (jet black)
Material (locking)	Polyamide Fibre-glass reinforced
Colour (locking)	RAL 9005 (jet black)
Material flammability class acc. to UL 94	V-0
Material flammability class acc. to UL 94 (locking levers)	V-0

Page 1 / 2 | Creation date 2018-12-07 | Please note that the data specified here were taken as extracts from the online catalogue. Please refer to the user documentation for the complete and up-to-date information and data. Please also note that the user is responsible for validating functionality, conformity with applicable laws and directives, as well as for the electrical safety in the particular application. HARTING Electric GmbH & Co. KG | Wilhelm-Harting-Straße 1 | 32339 Espelkamp | Germany Phone +49 5772 47-97100 | electric@HARTING.com | www.HARTING.com



Specifications and approvals

Specifications	IEC 61984
	EN 45545-2 R22: HL1, HL2, HL3
	EN 45545-2 R23: HL1, HL2, HL3
	EN 45545-2 R24: HL1, HL2, HL3
Commercial data	
Packaging size	1
Country of origin	Germany
European customs tariff number	85389099