




BOTTOM VIEW





SIDE VIEW



ANGLED VIEW



Specifications			Notes	Revision History													
Description	Value	Unit		Version	Description	Date	Approved										
Directivity	Omnidirectional		1) All dimensions are in mm unless otherwise noted 2) All parts meet RoHS 	1	Released from Engineering	10/21/2013	J.S										
Technology	Electret Condenser																
Sensitivity	-44	(dB)															
Frequency Range	40 ~ 20,000	(Hz)															
Rated Voltage	2	(V)															
Output Impedance	2,200	(Ohm)															
Connection Method	Solder Pads																
Voltage Range	1 ~ 10	(V)															
Max Rated Current	0.45	(mA)															
Minimum Signal to Noise Ratio	>60	(dB)															
Operating Temperature	-40 ~ +85	°C															
Storage Temperature	-40 ~ +85	°C															
				Electret Condenser Microphone	MO064402-1												
					<table border="1"> <thead> <tr> <th>Drawn by</th> <th>Date</th> <th>Checked by</th> <th>Date</th> <th>Approved by</th> <th>Date</th> </tr> </thead> <tbody> <tr> <td>A.B.</td> <td>10/21/2013</td> <td>C.E.</td> <td>10/21/2013</td> <td>J.S</td> <td>10/21/2013</td> </tr> </tbody> </table>	Drawn by	Date	Checked by	Date	Approved by	Date	A.B.	10/21/2013	C.E.	10/21/2013	J.S	10/21/2013
Drawn by	Date	Checked by	Date	Approved by	Date												
A.B.	10/21/2013	C.E.	10/21/2013	J.S	10/21/2013												

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[DB Unlimited:](#)

[MO064402-1](#)