



DMXDIM – 12~36Vdc, 5A, DMX Dimmer



DMXDIM is a DMX Dimmer from PowerLED

SKU: DMXDIM

Categories: [CONTROLLERS & REPEATERS](#) [LED DRIVERS](#)

DMXDIM is part of our comprehensive range for LED lighting performing at 12~36Vdc and a max load current of 3/4/5 x 5A. Capable of RGB adjustment and 256 levels of grey scales with smooth dimming control, you are able to use our LED Controller in conjunction with all PowerLED CV drivers. Power repeaters are available for increased lengths of LED tape. Features

- A comprehensive dimmer suitable for indoor LED Lighting.
- Intelligent fimmer capable of RGB colour adjustment.
- 0-100% dimming range via logarithmic characteristic, perfect for human vision.
- 256 levels of grey scales with smooth dimming control.
- Power repeater available for increased lengths of tape.

Perfect for indoor strip lighting

Specifications

Input Voltage	12~36VDC
Max Load Current	3/4/5 x 5A
Max Output Power	3/4/5 x (60-180W)
Load Type	Regular LED (0.04-0.1W)
Ta	-20 ~ +50°C
Tc	+75°C
Remarks	Visible Address
Dimensions (L x W x H)	160 x 57 x 21mm