


ACTUAL SIZE

Notes:
 Material:
 Shell: Brass, Nickel Plate.
 Insulator: LCP
 Contacts: Phosphor Bronze
 Finish:
 Contact Area: Gold Plate over Nickel Plate
 on Solder Tail: Tin Plate over Nickel Plate

Electrical Specifications
 Rated Voltage: 30V AC (rms)
 Contact Current Rating: 1 A Max.
 Contact Resistance: 30 milliohms Max.
 Dielectric Withstanding: 500V AC
 Operating Temperature: -55°C to 85°C

DATE	DESCRIPTION	REV.
12.16.09	CHANGE AS PER ECN 09-187	A
3.10.11	CHANGE AS PER ECN 11-037	B
6.07.18	CHANGE AS PER ECN 18-023 INSULATOR WAS PBT	C
11.04.19	CHANGE AS PER ECN 19-084 UPDATE PER SAMPLE	D



KEYSTONE ELECTRONICS CORP.

www.keystone.com • NEW HYDE PARK, NY 11040 • Tel (516) 328-7500

PART NAME

USB A-TYPE HORIZONTAL SMT SOCKET

MATERIAL

AS NOTED

FINISH

AS NOTED

TOLERANCES	INCH	[MM]	CODE	DWG NO.
DECIMAL	± .010	[± 0.25]	C	920
ANGULAR	± 1°			

DRN BY	DATE
BOONE	5.30.06

App'D **RH** SCALE 3X

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Keystone Electronics:](#)

[920](#)