

Model	NF-5320D
DC Voltage	6V-1000V \pm (0.5%+4)
AC Voltage	6V-750V \pm (0.8%+3)
DC Current	6A-10A \pm (0.8%+8)
AC Current	6A-10A \pm (1.0%+8)
Resistance	600 Ω ~60M Ω \pm (1.0%+8)
Capacitance	60nF~6mF \pm (2.5%+60) 30mF \pm (5.0%+10)
Frequency	/
Duty Cycle	/
Display counts	6000 counts
Auto/Manual range	Manual
LCD Display	\surd
Live Test	\surd
NCV	\surd
Diode test	\surd
Continuity	\surd
MAXMINhold	MAX
Data Hold	\surd
True RMS	\surd
Battery test(1.5 V/9 V)	\surd
Low battery indication	\surd
AUTO power off	\surd
Double color backlight	\surd
Flashlight	\surd
Power	2x1.5V AA