


MA212 PCB Terminal Block, Modular



MA

DIMENSIONS/POSITIONS

MA212-350M

間距	Pitch	3.50mm
位數	Poles	2 ~ 3Poles
塑膠本體	Housing Material	PA 66
彈片	Spring	Stainless Strip Steel
端子	Contact	Brass, Tin Plated
螺紋	Screw Thread	M2.0, Steel, Zinc Plated
電線線徑	Wire Size	16 ~ 26AWG
剝線長度	Wire Strip Length	5mm ~ 6mm
PCB孔徑	PCB Hole Diameter	1.2mm
最大緊固扭矩	Tightening Torque, Max.	2.0 Lb-in
環境作業溫度	Operating Temperature	-40°C to +105°C

TECHNICAL DATA

連接符合標準	Connection in acc. with standard EN-VDE	
額定電流 I _n	Nominal Current I _n	6A
額定橫截面	Nominal Cross Section	-
最大負載電流	Maximum load current	6A
絕緣材料	Insulating Material	PA
阻燃等級,符合UL94	Inflammability class acc. to UL94	V0
額定電壓,UL/CUL	Nominal voltage, UL/CUL	300V
額定電流,UL/CUL	Nominal current, UL/CUL	6A

