

Circular Plastic Connectors, Series 1, VDE Tested


CPC Connectors, Series 1, for Cable or Panel Mount (Accepts Type III+, High-Current Power, Type II and Subminiature Coax Contacts)



- Designed to meet requirements of VDE as shown in DIN Specification 57627
- Recognized under the Component Program of Underwriters Laboratories Inc. for 600 VAC and 600 VDC service, File No. E28476



■ Certified by Canadian Standards Association, File No. LR 7189



Material

Housing—Thermoplastic, 94V-0 rated, black

Related Product Data

Contacts—Pages 17-23

Contact Arrangement—Page 24 Component Dimensions—Page 25*


Accessories—Pages 38-42, 52-54 Performance Characteristics—

Application Tooling—Pages 76-79 Technical Documents—Page 80

Replacement Coupling Rings


Shell Size	Part No.	
13	213813-1	
17	213810-1	
23	213812-1	


.125 [3.18] Max. *D ‡ Thread Size (See chart) *B ±.015 [±0.38] *C ±.010 [±0.25]



Free-Hanging Receptacle

Square Flange Receptacle





*Note: See page 25 for callout dimensions

Plug *M Max *Thread Size

Standard Sex Connectors (Receptacles accept pin contacts, Plugs accept socket contacts)

Arrangement	Square Flange Receptacle			
Shell No. of Size Positions	Keying	With Threaded Inserts ¹	With Mounting Holes	Plug
13-7	Α	211401-4	211401-1	211399-1
17-9	Α	211767-2	211767-1	211766-1
23-19	Α	211771-2	211771-1	211770-2
23-19 -	В	_	213870-1	213853-1

¹Four 4-40 threaded inserts per receptacle.

Reverse Sex Connectors (Receptacles accept socket contacts, Plugs accept pin contacts)

Arrangement	Square Flange Receptacle			Free Henring	
Shell No. of Size Positions	Keying	With Threaded Inserts ¹	With Mounting Holes	Free-Hanging Receptacle	Plug
13-7	Α	211398-4	211398-1	211398-2	211400-1
17-9 ———	Α	_	211769-1	211769-3	211768-1
	В	_	796439-2	_	796450-1
23-19 -	Α	_	211773-1	_	211772-1
	В	_	213868-1	_	213852-1

¹Four 4-40 threaded inserts per receptacle.

Key Style "A" is the Standard 5 Locating Key arrangement. Key Style "B" is the 4 Locating Key arrangement.

A-Standard Configuration: 5 Keys **B**—Optional Configuration: 4 Keys

11

