

PIEZO TRANSDUCER (Pin Type)

External Circuitry Type

Shape


KPE-153



RoHS Compliant Available (eg KPEG153)

Model Number	KPE-153
Rated Voltage (Vp-p)	Max. 30
Current Consumption (mA)	Max. 7@10Vp-p, Square Wave, 4.0KHz
Sound Pressure Level (dB)	Min. 82dB@10cm@10Vp-p, Square Wave, 4.0KHz
Electrostatic Capacity (pF)	14,000 ± 30%@1.0KHz@1V
Operating Temperature (°C)	-30 ~ +105
Storage Temperature (°C)	-40 ~ +105
Weight (Gram)	3.4
Material	PBT+15%GF (Black)

Dimension



Tol : ±0.5 Unit : mm

Characteristic

