

Professional Office / Contact Centre Headsets



TECHNICAL DATA

Microphone:
 Directivity: Unidirectional
 Impedance: 1.0kΩ
 Sensitivity: -49±3dB (0dB=1V/Pa)
 Frequency Range: 100-16,000Hz
 Operating Temp: -20°C~+60°C
 Storage Temp: -25°C~+70°C

Speaker:
 Size: ø30 mm
 Input Power: 50 mW (1.26V)
 Max Power: 100 mW (1.79V)
 Impedance: 32Ω ±10% at 1kHz, 0.18V
 Sound Pressure: 122±3dB at 1kHz
 Resonance Frequency: 150±30 (20%) Hz
 Frequency Range: 20Hz ~ 20,000Hz
 Operating Temp: -25°C ~ +50°C
 Storage Temp: -25°C ~ +50°C



PLX COMPATIBLE QD



LEATHERETTE CUSHION



Commander

Fitted with 60mm leatherette ear cushions and padded T-bar and premium audio speakers designed for music and speech, ideal for users moving to PC telephony for webinars, conference calls, music and other multimedia applications.

Overview

Features	Single or dual speakers Left / right speaker side compatible Premium audio speakers designed for music and speech Surround Shield™ noise cancelling microphone Fully flexible microphone for exact positioning 270° adjustable microphone boom 'Put and stay' ratchet microphone boom arm Swivel T-bar with padded leatherette cushion Overhead, sure-fit fully adjustable headband
What's included	Headset fitted with 60mm leatherette ear cushions and supplied with Quick Start Guide
Headset Weight	~ 62g / ~ 82g
Connection	PLX fitted as standard or GN** compatible QD options
Compatibility	For full range of bottom leads* and compatibility information - Go to Jpltele.com
Certifications	UKCA, CE, FCC, RoHS, REACH
Warranty	2 Years repair or replacement warranty
MOQ	Master Shipping Carton: 40
EAN:	Commander-PM: 5060126959083, Commander-PB: 5060126959106
SKU:	Commander-PM: 575-365-003, Commander-PB: 575-365-004

