

Product

TK PS 3625-11-o



Empty enclosure, base and cover: polystyrene, grey, similar to RAL 7035

without knockouts

Article: TK PS 3625-11-o

Technical Data

Dimensions:

Width: 360 mm
Length: 254 mm

material:

Base: Polystyrene, grey, similar to RAL 7035
Cover: Polystyrene, grey, similar to RAL 7035
Sealing: Polyurethane
Cover screw: Polyamide 6, fiber-glass reinforced

Properties:

Ingress protection: IP66 - acc. EN 60529 / DIN VDE 0470-1
Ambient temperature (min.): -25 °C
Ambient temperature (max.): 40 °C
Ambient temperature (24 h): 35 °C
Max. rel. humidity at 40° C: 50%
Max. rel. humidity at 25° C (short Therm): {100%}
Rated insulation voltage AC: 690V
Impact resistance: IK07 acc. DIN EN 5012 / VDE 0470 Part 100
Protection class: II - isolate protection acc. VDE 0106 Protective insulation as per VDE 0106
Halogen-free: √
Heavy metals-free: √

PVC-free:	√
Silicone-free:	√
UV resistance:	-
Weatherproof:	-
Combustion behaviour to UL:	HB acc. UL94
Combustion behaviour to VDE:	650°C acc. VDE 0471/ EN 60695
Fitted for outdoor application:	-
Knockouts:	-
