

Self-aligning ball bearings, cylindrical and tapered bore, cylindrical bore, unsealed

Product information


Tolerances , see also text

Radial internal clearance , see also text

Recommended fits

Shaft and housing tolerances

Principal dimensions			Basic load ratings		Fatigue load limit	Speed ratings		Mass	Designation
d	D	B	dynamic C	static C_0	P_u	Reference speed	Limiting speed	kg	-
mm			kN		kN	r/min			
50	90	20	26,5	9,15	0,48	16000	10000	0,53	1210 ETN9



Calculation factors

e 0,21

Y_1 3

Y_2 4,6

Y_0 3,2