

MNX ABS 125/50 LT



Sample photo

Order symbol: ABS 125/50 LT
Product nbr: 6082908
Description: Enclosure, ABS
Remarks: Smoked transparent cover

EAN: 6418074014078
El. number:
 Finland 3420604
 Denmark 8212023657
 Italy 7362043

Including: Base with TPE gasket, screws for mounting plate/DIN-rail and cover with polyamide cover screws.

Dimensions:	L	W	H	Rating:
mm:	130	130	50	Electrical insulation: Totally insulated
inch:	5.1	5.1	2	Halogen free (DIN/VDE 0472, Part 815): Yes

Materials:	Material:	Material:	Material:	Material:	Material:	Material:	Material:	Material:	Material:
Material:	ABS	Gasket material:	TPE	Base colour:	RAL 7035	Cover colour:	Grey	Cover screws material:	Polyamide
Base colour:	RAL 7035	Cover screws material:	Polyamide	Cover colour:	Grey	Cover screws material:	Polyamide	Cover screws colour:	Black

Temperatures:	Short term:	Continuous:	Short term:	Continuous:	
Short term:	-40 ... 80 °C	Continuous:	-40 ... 60 °C	Short term:	-40 ... 175 °F
Continuous:	-40 ... 60 °C	Short term:	-40 ... 175 °F	Continuous:	-40 ... 140 °F

Accessories:	Accessories:
MIV 125	Mounting plate (Galvanized steel)
MIN 10	DIN-15 Mounting rail
MIV 10	DIN-35 Mounting rail
FP A 125/130	Front plate (Aluminium)
HFP 130	Front plate hinge series (2 pcs)
FP 22046	Wall fastening lug (4 pcs)

Electrical insulation: Totally insulated
Halogen free (DIN/VDE 0472, Part 815): Yes
Flammability Rating (UL 746 C 5): UL 94 HB
Glow Wire Test (IEC 695-2-1) °C: 650
NEMA Class: NEMA 1, 4, 4X, 6
Ingress Protection (EN 60529): IP 66/67
Impact Resistance (EN 50102): IK 07

Certificates:
 Fimko
 Europe EN 50298: 1998
 Gost R

