

FEATURES

- Voltage rating of 6.5V
- Current rating of 300mA
- 4000 hours lifetime

E10 Indicator Light, Clear, 6.5 V, 300 mA, 4000h

RS Stock No.: 104-806



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description ATTRIBUTE 1

It is interesting how the bulb industry has changed during the last two centuries. Even though there are great light bulbs available on the market, there is still a requirement for Filament Bulbs lighting that brings reliability and a bit of history.

General Specifications

Lamp Base	E10
Lamp Size	T3 ¼
Lens Colour	Clear
Luminosity	12lm
Life hours	4000h
Filament Type	Vacuum Type
Applications	Automotive industry; Gambling machine industry; Car indicator; Garden lights; Paper lanterns; Battery-powered flashlights

Electrical Specifications

Voltage Rating	6.5V
Current Rating	300mA
Light Output	MSCP x 12.6, MSCP = Lumens / 12.6.

Mechanical Specifications

Diameter	10mm
Length	28mm


Operation Environment Specifications

Ambient Operating Temperature	20 to 25°C
-------------------------------	------------

Approvals

Compliance/Certifications	RoHS
---------------------------	------



RS Stock No.		104806
<i>DRAWING - I</i>		
		
Unit : mm		
1. Structure	Bulb Type	T3 1/4 Clear
	Bulb Diameter	Ø10.0Max.
	Length	28.0Max
	Base Type	E10
2. Design Characteristics	Voltage	6.5V
	Amperage	300mA±10%
	Filament Type	Vacuum type
	Luminous Flux	12.0Lm±20%
	Life Hours	4,000Hrs